

NEMA PREMIUM™ UNIMOUNT
 NEMA PREMIUM™ HOSTILE DUTY
 NEMA PREMIUM™ CORRO-DUTY
 NEMA PREMIUM™ 841 PLUS
 NEMA PREMIUM™ e-LINE
 NEMA PREMIUM™ OPEN DRIIPROOF
 NEMA PREMIUM™ HAZARDOUS LOCATION
 NEMA PREMIUM™ COOLING TOWER DUTY
 NEMA PREMIUM™ CLOSE COUPLED PUMP
 PREMIUM EFFICIENT AUTOMOTIVE DUTY
 GENERAL PURPOSE THREE PHASE
 HAZARDOUS LOCATION

General Purpose Three Phase, Totally Enclosed Fan Cooled (TEFC) Unimount® Energy Efficient



APPLICATIONS:

For pumps, fans, compressors, material handling and other general purpose applications in damp, dusty or dirty environments.

FEATURES:

- World Motor® Features Except Where Noted
- Class F Insulation, Class B Rise at Full Load On 60 Hertz Sine Wave Power
- Aluminum Frame (180-280) Except Where Noted
- Rolled Steel Frame (56-140)
- Aluminum, End Shields with Steel Bearing Inserts
- Conduit Box Shipped Loose (180 Frame & Up Only)
- Full 50 & 60 Hertz Operating Data on Nameplate
- 40°C Ambient, NEMA® Design B Performance On 60 Hertz Sine Wave Power
- Full HP @ 50 Hz
- Regreaseable Bearings 250 Frame & Up
- Doubled Shielded Bearings 180-280
- Suitable For Wye-Delta Start 250 Frame & Larger
- Dual Voltage Ratings Suitable For Part Winding Start (PWS) On Low Voltage
- CE Mark On Nameplate 140 Frame & Larger
- Lifting Provisions 180 Frame & Up
- Removable Base 180 Frame & Up
- Conversion Kits: C&D Flanges, Drip Cover, Brakes (56-210 Frames); See Pages 304-312

HP	RPM	Voltage	Frame	Catalog Number	List	Discount Symbol	SF	"C" Dim. (inches)	Ship Wt. (lbs.)	Full Load Eff.	Full Load Amps	Notes
1/4	1800	208-230/460	56	T14S2A	\$378	DS-3F	1.15	10.9	17	-	1.1-1.1/1.5	19
	1200	208-230/460	56	T14S3A	\$575	DS-3F	1.15	11.9	17	-	1.4-1.5/1.76	
1/3	1800	208-230/460	56	T13S2A	\$389	DS-3F	1.15	11.4	20	-	1.3-1.3/0.6	
1/2	3600	208-230/460	48	T12S1D4	\$432	DS-3FMP	1.00	10.7	19	-	1.8-1.8/0.90	
	3600	208-230/460	56	T12S1A	\$390	DS-3F	1.15	10.9	20	-	2.0-2.0/1.0	
	1800	208-230/460	56	T12S2A	\$482	DS-3F	1.15	11.9	21	-	1.8-1.8/0.9	
	1800	575	56	T12S2G	\$482	DS-3F	1.15	11.3	23	-	0.80	
	1200	208-230/460	56	T12S3A	\$552	DS-3F	1.15	11.9	23	-	2.2-2.3/1.1	
	1200	575	56	T12S3G	\$552	DS-3F	1.15	11.9	26	-	0.85	
3/4	3600	208-230/460	56	T34S1A	\$474	DS-3F	1.15	11.9	22	-	2.5-2.5/1.2	
	1800	208-230/460	56	T34S2A	\$518	DS-3F	1.15	11.9	23	-	3.0-3.0/1.5	
	1800	575	56	T34S2G	\$518	DS-3F	1.15	12.5	25	-	1.1	37
	1200	208-230/460	143T	T34S3B14	\$713	DS-3FMP	1.15	12.8	30	75.5	3.4-3.5/1.7	
	1200	208-230/460	56H	T34S3AH	\$644	DS-3F	1.15	12.9	31	-	3.1-3.2/1.6	
1	3600	208-230/460	56	U1E1D	\$415	DS-3F	1.25	12.5	32	-	3.1-2.7/1.4	03
	3600	575	56	U1E1G	\$415	DS-3F	1.25	12.5	32	-	1.2	
	1800	200	143T	U1E2H	\$437	DS-3FTE	1.25	12.8	35	82.5	3.4	
	1800	208-230/460	143T	U1E2D	\$437	DS-3FTE	1.25	12.8	35	82.5	3.1-3/1.5	03
	1800	208-230/460	56H	T1S2AH	\$504	DS-3F	1.15	12.4	30	-	3.3-3.2/1.5	
	1800	575	143T	U1E2G	\$437	DS-3FTE	1.25	12.8	35	82.5	1.2	
	1800	575	56H	T1S2GH	\$428	DS-3F	1.15	12.4	26	-	1.3	
	1200	200	145T	U1E3H	\$683	DS-3FTE	1.25	12.8	40	80.0	4.2	
	1200	208-230/460	145T	U1E3D	\$683	DS-3FTE	1.25	12.8	40	80.0	3.7-3.5/1.8	03
	1200	208-230/460	56H	T1S3A	\$725	DS-3F	1.15	13.4	32	-	3.7-3.8/1.9	
	1200	575	145T	U1E3G	\$683	DS-3FTE	1.25	12.8	40	80.0	1.5	
	900	208-230/460	182T	U1E4D	\$1,260	DS-3FTE	1.25	12.8	60	74.0	4.4-4.7/2.4	03
	1-1/2	3600	200	143T	U32E1H	\$567	DS-3FTE	1.25	12.8	35	82.5	4.5
3600		208-230/460	143T	U32E1D	\$567	DS-3FTE	1.25	12.8	35	82.5	4.2-4/2	03
3600		208-230/460	56H	T32S1AH	\$554	DS-3F	1.15	12.3	26	-	4.7-4.5/2.2	
3600		575	143T	U32E1G	\$567	DS-3FTE	1.25	12.8	35	82.5	1.6	

Note 03 60/50 Hz rated with no derate on horsepower, 230/460 volt 60 Hz ratings operate on 190/380 volt 50 Hz. 460 Volt 60 Hz ratings operate on 380 volt 50 Hz power. Full 60 Hz and 50 Hz data is displayed on N/P

Note 19 Also rated for 190/380, 220/415 volt 50 Hz at 1.0 Service Factor

Note 37 Q-3 leads for across-the-line start

† All non-Emerson Electric Co. marks shown within this document are properties of their other respective owners



General Purpose Three Phase, Totally Enclosed Fan Cooled (TEFC) Unimount® Energy Efficient



NEMA PREMIUM™
UNIMOUNT™
NEMA PREMIUM™
HOSTILE DUTY™
NEMA PREMIUM™
CORRO-DUTY™
NEMA PREMIUM™
S&I PLUS™
NEMA PREMIUM™
e-LINE™
NEMA PREMIUM™
OPEN DRIPPROOF™
NEMA PREMIUM™
HAZARDOUS LOCATION™
NEMA PREMIUM™
COOLING TOWER DUTY™
NEMA PREMIUM™
CLOSE COUPLED PUMP™
PREMIUM EFFICIENT™
AUTOMOTIVE DUTY™
GENERAL PURPOSE™
THREE PHASE™
HAZARDOUS™
LOCATION™

HP	RPM	Voltage	Frame	Catalog Number	List	Discount Symbol	SF	"C" Dim. (inches)	Ship Wt. (lbs.)	Full Load Eff.	Full Load Amps	Notes
1-1/2	1800	200	145T	U32E2H	\$446	DS-3FTE	1.25	12.8	40	84.0	5	
	1800	208-230/460	145T	U32E2D	\$446	DS-3FTE	1.25	12.8	40	84.0	4.6-4.4/2.2	03
	1800	208-230/460	56H	T32S2AH	\$481	DS-3F	1.15	12.9	34	-	5.1-5.2/2.6	
	1800	575	145T	U32E2G	\$446	DS-3FTE	1.25	12.8	40	84.0	1.8	
	1200	200	182T	U32E3H	\$788	DS-3FTE	1.25	16.1	64	85.5	6.1	
	1200	208-230/460	182T	S32E3D	\$788	DS-3FTE	1.25	14.9	64	85.5	5.5-5.4/2.7	04, 16, 26
	1200	208-230/460	182T	U32E3D	\$788	DS-3FTE	1.25	16.1	64	85.5	5.3-5.3/2.7	03
	1200	208-230/460	56	T32S3AH	\$832	DS-3FMP	1.15	14.4	41	-	5.4-5.3/2.6	
	1200	575	182T	U32E3G	\$788	DS-3FTE	1.25	16.1	64	85.5	2.1	
2	900	208-230/460	184T	U32E4D	\$1,491	DS-3FTE	1.25	12.8	70	78.5	6.2-6.6/3.3	03
	3600	200	145T	U2E1H	\$653	DS-3FTE	1.25	12.8	40	84.0	5.8	
	3600	208-230/460	145T	U2E1D	\$653	DS-3FTE	1.25	12.75	40	84.0	5.6-5/2.5	03
	3600	208-230/460	56H	T2S1AH	\$622	DS-3F	1.15	12.4	33	-	6.0-5.4/2.7	
	3600	208-230/460	56HZ	T2E1AHZ	\$677	DS-3F	1.25	13.3	32	-	6.3-6.1/3.1	
	3600	575	145T	U2E1G	\$653	DS-3FTE	1.25	12.8	40	84.0	2	
	3600	575	56H	T2S1G	\$622	DS-3F	1.15	12.4	31	-	2.3	
	1800	200	145T	U2E2H	\$470	DS-3FTE	1.25	12.8	45	84.0	6.8	
	1800	208-230/460	145T	U2E2D	\$470	DS-3FTE	1.25	12.8	45	84.0	5.8-5.7/2.8	03
	1800	208-230/460	56H	T2S2AH	\$520	DS-3F	1.15	12.9	36	-	7.2-7.1/3.4	
	1800	208-230/460	56HZ	T2E2AHZ	\$544	DS-3F	1.25	13.8	36	-	6-5.9/3	
	1800	575	145T	U2E2G	\$470	DS-3FTE	1.25	12.8	45	84.0	2.4	
	1200	200	184T	U2E3H	\$848	DS-3FTE	1.25	16.9	74	86.5	7.7	
	1200	208-230/460	184T	S2E3D	\$848	DS-3FTE	1.15	15.9	74	86.5	7-6.8/3.4	04, 16, 26
	1200	208-230/460	184T	U2E3D	\$848	DS-3FTE	1.25	16.9	84	86.5	6.8-6.6/3.3	03
	1200	575	184T	U2E3G	\$848	DS-3FTE	1.25	16.9	74	86.5	2.7	
	900	200	213T	U2E4H	\$1,893	DS-3FTE	1.25	18.6	90	82.5	8.7	
	900	208-230/460	213T	U2E4D	\$1,893	DS-3FTE	1.25	18.6	90	82.5	7.9-7.6/3.8	03
900	575	213T	U2E4G	\$1,893	DS-3FTE	1.25	18.6	90	82.5	3		
3	3600	200	145T	U3E1HF	\$719	DS-3FTE	1.25	13.8	53	85.5	8.3	
	3600	200	182T	U3E1H	\$797	DS-3FTE	1.25	16.1	60	85.5	9.2	
	3600	208-230/460	145T	U3E1DF	\$719	DS-3FTE	1.25	13.8	73	85.5	8.2-7.2/3.6	03
	3600	208-230/460	182T	S3E1D	\$797	DS-3FTE	1.15	14.9	50	85.5	8.6-8/4	04, 16, 26
	3600	208-230/460	182T	U3E1D	\$797	DS-3FTE	1.25	16.1	60	85.5	8.7-8/4	03
	3600	208-230/460	56HZ	U3E1AHZ	\$776	DS-3F	1.25	13.8	45	-	8.5-7.3/3.6	
	3600	575	145T	U3E1GF	\$719	DS-3FTE	1.25	13.8	63	85.5	2.9	
	3600	575	182T	U3E1G	\$797	DS-3FTE	1.25	16.1	60	85.5	3.2	
	1800	200	182T	U3E2H	\$554	DS-3FTE	1.25	16.1	60	87.5	9.1	
	1800	208-230/460	182T	S3E2D	\$554	DS-3FTE	1.15	16.1	55	87.5	8.5-7.9/3.9	04, 16, 26
	1800	208-230/460	182T	U3E2D	\$554	DS-3FTE	1.15	16.1	60	87.5	8.6-8.1/4.1	03
	1800	575	182T	U3E2G	\$554	DS-3FTE	1.25	16.1	60	87.5	3.2	

Note 03 60/50 Hz rated with no derate on horsepower, 230/460 volt 60 Hz ratings operate on 190/380 volt 50 Hz. 460 Volt 60 Hz ratings operate on 380 volt 50 Hz power. Full 60 Hz and 50 Hz data is displayed on N/P
Note 04 On 60 Hertz Sine Wave power

Note 16 Motors marked 208-230/460 volts may not meet all NEMA® (MG-1) performance standards when operated at 208 volts
Note 26 Does not include World Motor® features

† All non-Emerson Electric Co. marks shown within this document are properties of their other respective owners

NEMA PREMIUM™ UNIMOUNT
 NEMA PREMIUM™ HOSTILE DUTY
 NEMA PREMIUM™ CORRO-DUTY
 NEMA PREMIUM™ 841 PLUS
 NEMA PREMIUM™ e-LINE
 NEMA PREMIUM™ OPEN DRIPPROOF
 NEMA PREMIUM™ HAZARDOUS LOCATION
 NEMA PREMIUM™ COOLING TOWER DUTY
 NEMA PREMIUM™ CLOSE COUPLED PUMP
 PREMIUM EFFICIENT AUTOMOTIVE DUTY
 GENERAL PURPOSE THREE PHASE
 HAZARDOUS LOCATION

General Purpose Three Phase, Totally Enclosed Fan Cooled (TEFC) Unimount® Energy Efficient



HP	RPM	Voltage	Frame	Catalog Number	List	Discount Symbol	SF	"C" Dim. (inches)	Ship Wt. (lbs.)	Full Load Eff.	Full Load Amps	Notes
3	1200	200	213T	U3E3H	\$1,068	DS-3FTE	1.25	18.6	105	87.5	10.4	
	1200	208-230/460	213T	S3E3D	\$1,068	DS-3FTE	1.15	18.9	130	87.5	9.7-9.1/4.5	04, 16, 26
	1200	208-230/460	213T	U3E3D	\$1,068	DS-3FTE	1.25	18.6	105	87.5	9.8-9.3/4.6	03
	1200	575	213T	U3E3G	\$1,068	DS-3FTE	1.25	18.6	105	87.5	3.6	
	900	200	215T	U3E4H	\$2,069	DS-3FTE	1.25	20.1	125	84.0	12.8	
	900	208-230/460	215T	U3E4D	\$2,069	DS-3FTE	1.25	20.1	125	84.0	11.7-11.1/5.5	03
	900	575	215T	U3E4G	\$2,069	DS-3FTE	1.25	20.1	125	84.0	4.5	
5	3600	200	184T	U5E1H	\$917	DS-3FTE	1.25	16.9	70	87.5	14.2	
	3600	208-230/460	184T	S5E1D	\$917	DS-3FTE	1.15	15.9	65	87.5	13.7-12.3/6.1	04, 16, 26
	3600	208-230/460	184T	U5E1D	\$917	DS-3FTE	1.25	16.1	70	87.5	13.8-12.3/6.1	03
	3600	575	184T	U5E1G	\$917	DS-3FTE	1.25	16.9	70	87.5	4.9	
	1800	200	184T	U5E2H	\$638	DS-3FTE	1.25	16.9	70	87.5	14.4	
	1800	208-230/460	184T	S5E2D	\$638	DS-3FTE	1.15	15.9	65	86.5	14.2-12.8/6.4	04, 16, 26
	1800	208-230/460	184T	U5E2D	\$638	DS-3FTE	1.25	16.9	70	87.5	14.1-13/6.5	03
	1800	575	184T	U5E2G	\$638	DS-3FTE	1.25	16.9	70	87.5	5.2	
	1200	200	215T	U5E3H	\$1,286	DS-3FTE	1.25	20.1	135	87.5	16.5	
	1200	208-230/460	215T	S5E3D	\$1,286	DS-3FTE	1.15	18.9	115	87.5	15.6-14.5/7.2	04, 16, 26
	1200	208-230/460	215T	U5E3D	\$1,286	DS-3FTE	1.25	20.1	135	87.5	15.6-14.5/7.3	03
	1200	575	215T	U5E3G	\$1,286	DS-3FTE	1.25	20.1	135	87.5	5.8	
	900	200	254T	U5E4H	\$2,558	DS-3FTE	1.25	23.9	180	85.5	17.3	02
	900	208-230/460	254T	U5E4D	\$2,558	DS-3FTE	1.25	23.9	180	85.5	16.4-15.4/7.7	02, 03
	900	575	254T	U5E4G	\$2,558	DS-3FTE	1.25	23.9	180	86.5	6.1	02
7 1/2	3600	200	213T	U7E1H	\$1,350	DS-3FTE	1.25	18.6	105	88.5	21.2	
	3600	208-230/460	184T	U7E1A	\$1,350	DS-3FTE	1.15	16.9	70	88.5	20.4-17.9/9	
	3600	208-230/460	213T	S7E1D	\$1,350	DS-3FTE	1.15	18.9	85	88.5	20.6-18.4/9.2	04, 16, 26
	3600	208-230/460	213T	U7E1D	\$1,350	DS-3FTE	1.25	18.6	205	88.5	20.4-18.4/9.2	03
	3600	575	213T	U7E1G	\$1,350	DS-3FTE	1.25	18.6	105	88.5	7.4	
	1800	200	213T	U7E2H	\$815	DS-3FTE	1.25	18.6	105	89.5	21.5	
	1800	208-230/460	213T	S7E2D	\$815	DS-3FTE	1.15	18.9	95	89.5	20.1-18.3/9.1	04, 16, 26
	1800	208-230/460	213T	U7E2D	\$815	DS-3FTE	1.25	18.6	105	89.5	20.8-18.9/9.4	03
	1800	575	213T	U7E2G	\$815	DS-3FTE	1.25	18.6	105	89.5	7.5	
	1200	200	254T	U7E3H	\$1,823	DS-3FTE	1.25	23.9	180	89.5	21.8	
	1200	208-230/460	254T	U7E3D	\$1,823	DS-3FTE	1.25	23.9	180	89.5	20.8-18.8/9.4	02, 03
	900	200	256T	U7E4H	\$3,449	DS-3FTE	1.25	25.6	300	86.5	25.4	02
	900	208-230/460	256T	U7E4D	\$3,449	DS-3FTE	1.25	25.6	300	86.5	23.8-22.2/11.1	02, 03
	900	575	256T	U7E4G	\$3,449	DS-3FTE	1.25	25.6	300	86.5	8.8	02
	10	3600	200	215T	U10E1H	\$1,415	DS-3FTE	1.25	20.1	120	89.5	27.3
3600		208-230/460	215T	S10E1D	\$1,415	DS-3FTE	1.15	18.9	110	89.5	26.5-23.5/11.7	04, 16, 26
3600		208-230/460	215T	U10E1D	\$1,415	DS-3FTE	1.25	20.1	120	89.5	26.7-23.8/11.9	03
3600		575	215T	U10E1G	\$1,415	DS-3FTE	1.25	20.1	120	89.5	9.4	

Note 02 Suitable for Wye-Delta start on voltages shown
 Note 03 60/50 Hz rated with no derate on horsepower, 230/460 volt 60 Hz ratings operate on 190/380 volt 50 Hz. 460 Volt 60 Hz ratings operate on 380 volt 50 Hz power. Full 60 Hz and 50 Hz data is displayed on N/P
 Note 04 On 60 Hertz Sine Wave power
 Note 16 Motors marked 208-230/460 volts may not meet all NEMA® (MG-1) performance standards when operated at 208 volts
 Note 26 Does not include World Motor® features

† All non-Emerson Electric Co. marks shown within this document are properties of their other respective owners



General Purpose Three Phase, Totally Enclosed Fan Cooled (TEFC) Unimount® Energy Efficient



HP	RPM	Voltage	Frame	Catalog Number	List	Discount Symbol	SF	"C" Dim. (inches)	Ship Wt. (lbs.)	Full Load Eff.	Full Load Amps	Notes
10	1800	200	215T	U10E2H	\$992	DS-3FTE	1.25	20.1	135	89.5	28.4	
	1800	208-230/460	215T	U10E2D	\$992	DS-3FTE	1.25	20.1	135	89.5	27.5-24.8/12.4	03
	1800	575	215T	U10E2G	\$992	DS-3FTE	1.25	20.1	135	89.5	9.9	
	1200	200	256T	U10E3H	\$2,028	DS-3FTE	1.25	25.6	210	89.5	28.8	02
	1200	208-230/460	256T	U10E3D	\$2,028	DS-3FTE	1.25	25.6	210	89.5	27.5-25/12.5	02, 03
	1200	575	256T	U10E3G	\$2,028	DS-3FTE	1.25	25.6	210	89.5	10	02
15	3600	200	254T	U15E1H	\$2,127	DS-3FTE	1.25	23.9	190	90.2	40	02
	3600	208-230/460	215T	U15E1AF	\$1,797	DS-3FTE	1.25	21.6	140	90.2	40-35/17.7	03
	3600	208-230/460	254T	U15E1D	\$2,127	DS-3FTE	1.25	23.9	190	90.2	40-35/17.7	02, 03
	3600	575	254T	U15E1G	\$2,127	DS-3FTE	1.25	23.9	190	90.2	14	02
	1800	200	254T	U15E2H	\$1,653	DS-3FTE	1.25	23.9	190	91.0	43	02
	1800	208-230/460	254T	U15E2D	\$1,653	DS-3FTE	1.25	23.9	300	91.0	41-38/18.9	02, 03
20	3600	200	256T	U20E1H	\$2,337	DS-3FTE	1.25	25.6	210	90.2	53	02
	3600	208-230/460	256T	U20E1D	\$2,337	DS-3FTE	1.25	25.6	210	90.2	54-47/23.5	02, 03
	3600	575	256T	U20E1G	\$2,337	DS-3FTE	1.25	25.6	210	90.2	18.7	02
	1800	200	256T	U20E2H	\$1,998	DS-3FTE	1.25	25.6	230	91.0	56	02
	1800	208-230/460	256T	U20E2D	\$1,998	DS-3FTE	1.25	25.6	330	91.0	55-51/25.7	02, 03
	1800	575	256T	U20E2G	\$1,998	DS-3FTE	1.25	25.6	230	91.0	19.5	02
25	3600	200	284T	U25E1H	\$2,973	DS-3FTE	1.25	28.3	250	91.0	66.0	02
	3600	200	284TS	U25E1HS	\$2,973	DS-3FTE	1.25	26.9	250	91.0	66	02
	3600	208-230/460	284T	U25E1D	\$2,973	DS-3FTE	1.25	28.3	250	91.0	64-56/28.2	02, 03
	3600	208-230/460	284TS	U25E1DS	\$2,973	DS-3FTE	1.25	26.9	250	91.0	64-56/28.2	02, 03
	3600	575	284T	U25E1G	\$2,973	DS-3FTE	1.25	28.3	250	91.0	22.9	02
	3600	575	284TS	U25E1GS	\$2,973	DS-3FTE	1.25	26.9	250	91.0	22.6	02
	1800	200	284T	U25E2H	\$2,474	DS-3FTE	1.25	28.3	290	92.4	69	02
	1800	200	284TS	U25E2HS	\$2,474	DS-3FTE	1.25	26.9	290	92.4	69	02
	1800	208-230/460	284T	U25E2D	\$2,474	DS-3FTE	1.25	28.3	250	92.4	67-59/29.6	02, 03
	1800	208-230/460	284TS	U25E2DS	\$2,474	DS-3FTE	1.25	26.9	290	92.4	67-59/29.6	02, 03
	1800	575	284T	U25E2G	\$2,474	DS-3FTE	1.25	28.3	290	92.4	23.7	02
	1800	575	284TS	U25E2GS	\$2,474	DS-3FTE	1.25	26.9	290	92.4	23.7	02
30	1800	200	286T	U30E2H	\$2,921	DS-3FTE	1.25	28.3	325	92.4	82	02
	1800	200	286TS	U30E2HS	\$2,921	DS-3FTE	1.25	26.9	325	92.4	82	02
	1800	208-230/460	286T	U30E2D	\$2,921	DS-3FTE	1.25	28.3	325	92.4	80-72/36	02, 03
	1800	208-230/460	286TS	U30E2DS	\$2,921	DS-3FTE	1.25	26.9	325	92.4	80-72/36	02, 03
	1800	575	286T	U30E2G	\$2,921	DS-3FTE	1.25	28.3	325	92.4	28.6	02
	1800	575	286TS	U30E2GS	\$2,921	DS-3FTE	1.25	26.9	325	92.4	28.6	02

Note 02 Suitable for Wye-Delta start on voltages shown

Note 03 60/50 Hz rated with no derate on horsepower, 230/460 volt 60 Hz ratings operate on 190/380 volt 50 Hz. 460 Volt 60 Hz ratings operate on 380 volt 50 Hz power. Full 60 Hz and 50 Hz data is displayed on N/P

† All non-Emerson Electric Co. marks shown within this document are properties of their other respective owners

NEMA PREMIUM™
UNIMOUNT™
NEMA PREMIUM™
HOSTILE DUTY
NEMA PREMIUM™
CORRO-DUTY™
NEMA PREMIUM™
S&I PLUS™
NEMA PREMIUM™
e-LINE™
NEMA PREMIUM™
OPEN DRIPPROOF™
NEMA PREMIUM™
HAZARDOUS LOCATION™
NEMA PREMIUM™
COOLING TOWER DUTY™
NEMA PREMIUM™
CLOSE COUPLED PUMP™
PREMIUM EFFICIENT™
AUTOMOTIVE DUTY™
GENERAL PURPOSE™
THREE PHASE™
HAZARDOUS™
LOCATION™