

General Purpose Three Phase, Open Drip Proof (ODP) Resilient Base NEMA®† Premium Efficient

APPLICATIONS:

For use on pumps, fans, compressors, material handling and other general purpose applications where contaminants are minimal.

FEATURES:

- Rolled Steel Frame
- Aluminum End Shields
- 40°C Ambient
- F1 Assembly Position
- Resilient Base

| HP | RPM | Voltage | Frame | Catalog Number | Discount Symbol | SF | "C" Dim. (inches) | Ship Wt. (lbs) | NEMA Nom. Eff. | Full Load Amps | Notes |
|-------|------|-------------|-------|----------------|-----------------|------|-------------------|----------------|----------------|----------------|--------|
| 1/3 | 1800 | 208-230/460 | 56H | D13P2AH9 | DS-3F | 1.35 | 11.8 | 24 | 73.4 | 1.4-1.4/0.7 | |
| 1/2 | 1800 | 208-230/460 | 56H | D12P2AH9 | DS-3F | 1.25 | 11.8 | 25 | 78.2 | 1.98-1.9/1.98 | |
| 3/4 | 1800 | 208-230/460 | 56H | D34P2AH9 | DS-3F | 1.25 | 12.3 | 26 | 82.2 | 2.8-2.7/1.4 | |
| 1 | 1800 | 208-230/460 | 56H | D1P2DH9 | DS-3F | 1.15 | 12.8 | 32 | 83.5 | 3.2-3.0/1.5 | |
| 1 1/2 | 3600 | 208-230/460 | 56H | D32PA1AH9 | DS-3F | 1.15 | 12.3 | 32 | 84.0 | 4.7-4.4/2.2 | LA |
| | 3600 | 208-230/460 | 56H | D32SA1AH9 | DS-3F | 1.15 | 12.8 | 32 | 82.0 | 4.7-4.4/ 2.2 | NNP,LA |
| | 1800 | 208-230/460 | 56H | D32P2AH9 | DS-3F | 1.15 | 13.3 | 33 | 86.5 | 5.0- 4.8/2.4 | |

Note LA Limited Availability

Note NNP Non-NEMA®† Premium Rating