

General Purpose Three Phase, Totally Enclosed Fan Cooled (TEFC) World Motor 841 Plus® NEMA®+ Premium Efficient

APPLICATIONS:

For constant speed and inverter duty applications in petro-chemical, pulp & paper, automotive, mining and waste treatment industries.

FEATURES:

- Inverter Grade® Insulation System (Meets NEMA® MG-1 Part 31)
- Class F Insulation, Class B Rise At Full Load (Sine Wave Power)
- All Cast Iron Construction
- Corrosion Resistant Mill & Chem Duty Paint (500 Hour Salt Spray Test)
- Stainless Steel Nameplate (with CE Mark) & Zinc Plated Hardware
- 40°C Ambient, NEMA® Design B Performance (Sine Wave Power)
- VBXX® Bearing Isolators By Inpro/Seal On Both Ends For IP55 Bearing Protection
- Same Size Regreasable Open Bearings, Brass Breathers/Drains
- 5 Year Warranty (3 Years on Inverter Power)
- External Grounding Provision, Epoxy Coated Rotor
- 20:1 (3-60hz) Variable Torque; 5:1 (12-60hz) Constant Torque On Inverter Power
- Precision Balance (< 0.05 In/Sec Vibration)
- 1.15 SF On Sine Wave / 1.0 SF On Inverter Power
- Meets or Exceeds IEEE 841 Standard 2009
- Conversion Kits: C&D Flange, Drip Cover Kit, Shaft Grounding Ring (Non-hazardous Locations only)
- Self-Certified Class I, Division 2, Groups A, B, C, & D

HP	RPM	Voltage	Frame	Catalog Number	Discount Symbol	SF	"C" Dim. (inches)	Ship Wt. (lbs)	Full Load Eff.	Full Load Amps	Notes
1	1800	460	143T	8D1P2C	DS-841W	1.15	13.7	70	85.5	1.5	
	1800	575	143T	8D1P2G	DS-841W	1.15	13.7	70	86.5	1.2	
	1200	460	145T	8D1P3C	DS-841W	1.15	13.7	80	82.5	1.8	
	1200	575	145T	8D1P3G	DS-841W	1.15	13.7	80	82.5	1.4	
1 1/2	3600	460	143T	8D32P1C	DS-841W	1.15	13.7	65	84.0	1.9	
	3600	575	143T	8D32P1G	DS-841W	1.15	13.7	65	84.0	1.6	
	1800	460	145T	8D32P2C	DS-841W	1.15	13.7	80	86.5	2.1	
	1800	575	145T	8D32P2G	DS-841W	1.15	13.7	80	87.5	1.6	
	1200	460	182T	8D32P3C	DS-841W	1.15	16.4	100	87.5	2.2	
	1200	575	182T	8D32P3G	DS-841W	1.15	16.4	100	87.5	1.8	
2	3600	460	145T	8D2P1C	DS-841W	1.15	13.7	70	85.5	2.5	
	3600	575	145T	8D2P1G	DS-841W	1.15	13.7	70	86.5	2	
	1800	460	145T	8D2P2C	DS-841W	1.15	13.7	80	86.5	2.7	
	1800	575	145T	8D2P2G	DS-841W	1.15	13.7	80	87.5	2.1	
	1200	460	184T	8D2P3C	DS-841W	1.15	16.4	110	88.5	3.1	
	1200	575	184T	8D2P3G	DS-841W	1.15	16.4	110	88.5	2.5	
3	3600	460	182T	8D3P1C	DS-841W	1.15	16.4	80	86.5	4.1	
	3600	575	182T	8D3P1G	DS-841W	1.15	16.4	80	86.5	3.3	
	1800	460	182T	8D3P2C	DS-841W	1.15	16.4	100	89.5	3.9	
	1800	575	182T	8D3P2G	DS-841W	1.15	16.4	100	89.5	3.1	
	1200	460	213T	8D3P3C	DS-841W	1.15	19.7	170	89.5	4.3	
	1200	575	213T	8D3P3G	DS-841W	1.15	19.7	170	89.5	3.5	
5	3600	460	184T	8D5P1C	DS-841W	1.15	16.4	100	88.5	6.1	
	3600	575	184T	8D5P1G	DS-841W	1.15	16.4	100	88.5	4.9	
	1800	460	184T	8D5P2C	DS-841W	1.15	16.4	110	89.5	6.3	
	1800	575	184T	8D5P2G	DS-841W	1.15	16.4	110	89.5	5.1	
	1200	460	215T	8D5P3C	DS-841W	1.15	19.7	180	89.5	7.1	
	1200	575	215T	8D5P3G	DS-841W	1.15	19.7	180	89.5	5.7	
7 1/2	3600	460	213T	8D7P1C	DS-841W	1.15	19.7	140	89.5	9	
	3600	575	213T	8D7P1G	DS-841W	1.15	19.7	140	89.5	7.2	
	1800	460	213T	8D7P2C	DS-841W	1.15	19.7	170	91.7	9.6	
	1800	575	213T	8D7P2G	DS-841W	1.15	19.7	170	91.7	7.8	
	1200	460	254T	8D7P3C	DS-841W	1.15	25.1	250	91.0	9.4	
	1200	575	254T	8D7P3G	DS-841W	1.15	25.1	250	91.0	7.6	

GENERAL PURPOSE UNIMOUNT®
GENERAL PURPOSE C-FACE
GENERAL PURPOSE HOSTILE DUTY
GENERAL PURPOSE CORRO-DUTY™
GENERAL PURPOSE 841 PLUS®
GENERAL PURPOSE OPEN DRIP PROOF
GENERAL PURPOSE HAZARDOUS LOCATION
GENERAL PURPOSE AUTOMOTIVE DUTY
COOLING TOWER DUTY
HAZARDOUS LOCATION
C-FACE MOTORS
VARIABLE SPEED MOTORS AND DRIVES

General Purpose Three Phase, Totally Enclosed Fan Cooled (TEFC) World Motor 841 Plus® NEMA®+ Premium Efficient

(continued)

HP	RPM	Voltage	Frame	Catalog Number	Discount Symbol	SF	"C" Dim. (inches)	Ship Wt. (lbs)	Full Load Eff.	Full Load Amps	Notes
10	3600	460	215T	8D10P1C	DS-841W	1.15	19.7	160	90.2	11.8	
	3600	575	215T	8D10P1G	DS-841W	1.15	19.7	160	90.2	9.4	
	1800	460	215T	8D10P2C	DS-841W	1.15	19.7	180	91.7	12.8	
	1800	575	215T	8D10P2G	DS-841W	1.15	19.7	180	91.7	10.3	
	1200	460	256T	8D10P3C	DS-841W	1.15	25.0	280	91.0	12.4	
	1200	575	256T	8D10P3G	DS-841W	1.15	25.0	280	91.0	10	
15	3600	460	254T	8D15P1C	DS-841W	1.15	25.1	270	91.0	17.4	
	3600	575	254T	8D15P1G	DS-841W	1.15	25.1	270	91.0	13.9	
	1800	460	254T	8D15P2C	DS-841W	1.15	25.1	270	92.4	18	
	1800	575	254T	8D15P2G	DS-841W	1.15	25.1	270	92.4	14.5	
	1200	460	284T	8D15P3C	DS-841W	1.15	27.7	340	91.7	18.5	
	1200	575	284T	8D15P3G	DS-841W	1.15	27.7	340	91.7	14.7	
20	3600	460	256T	8D20P1C	DS-841W	1.15	25.1	280	91.0	23	
	3600	575	256T	8D20P1G	DS-841W	1.15	25.1	280	91.0	18.4	
	1800	460	256T	8D20P2C	DS-841W	1.15	25.1	300	93.0	23.7	
	1800	575	256T	8D20P2G	DS-841W	1.15	25.1	300	93.0	18.9	
	1200	460	286T	8D20P3C	DS-841W	1.15	27.7	370	91.7	24.4	
	1200	575	286T	8D20P3G	DS-841W	1.15	27.7	370	91.7	19.6	
25	3600	460	284TS	8D25P1CS	DS-841W	1.15	26.3	330	91.7	28.8	
	3600	575	284TS	8D25P1GS	DS-841W	1.15	26.3	330	91.7	23	
	1800	460	284T	8D25P2C	DS-841W	1.15	27.7	360	93.6	29.2	
	1800	575	284T	8D25P2G	DS-841W	1.15	27.7	360	93.6	23.3	
	1200	460	324T	8D25P3C	DS-841W	1.15	30.3	540	93.0	29.3	
	1200	575	324T	8D25P3G	DS-841W	1.15	30.3	540	93.0	23.4	
30	3600	460	286TS	8D30P1CS	DS-841W	1.15	26.0	330	91.7	35	
	3600	575	286TS	8D30P1GS	DS-841W	1.15	26.0	330	91.7	27.7	
	1800	460	286T	8D30P2C	DS-841W	1.15	28.0	370	93.6	35	
	1800	575	286T	8D30P2G	DS-841W	1.15	28.0	370	93.6	28.1	
	1200	460	326T	8D30P3C	DS-841W	1.15	30.3	560	93.0	35	
	1200	575	326T	8D30P3G	DS-841W	1.15	30.3	560	93.0	28	
40	3600	460	324TS	8D40P1CS	DS-841W	1.15	28.8	460	92.4	46	
	3600	575	324TS	8D40P1GS	DS-841W	1.15	28.8	460	92.4	37	
	1800	460	324T	8D40P2C	DS-841W	1.15	30.3	490	94.1	46	
	1800	575	324T	8D40P2G	DS-841W	1.15	30.3	490	94.1	37	
	1200	460	364T	8D40P3C	DS-841W	1.15	32.4	690	94.1	47	
	1200	575	364T	8D40P3G	DS-841W	1.15	32.4	690	94.1	37	
50	3600	460	326TS	8D50P1CS	DS-841W	1.15	28.8	520	93.0	56	
	3600	575	326TS	8D50P1GS	DS-841W	1.15	28.8	520	93.0	45	
	1800	460	326T	8D50P2C	DS-841W	1.15	30.3	600	94.5	56	
	1800	575	326T	8D50P2G	DS-841W	1.15	30.3	600	94.5	45	
	1200	460	365T	8D50P3C	DS-841W	1.15	32.4	730	94.1	59	
	1200	575	365T	8D50P3G	DS-841W	1.15	32.4	730	94.1	47	
60	3600	460	364TS	8D60P1CS	DS-841W	1.15	30.3	620	93.6	69	
	3600	575	364TS	8D60P1GS	DS-841W	1.15	30.3	620	93.6	55	
	1800	460	364T	8D60P2C	DS-841W	1.15	32.4	700	95.0	68	
	1800	575	364T	8D60P2G	DS-841W	1.15	32.4	700	95.0	55	
	1200	460	404T	8D60P3C	DS-841W	1.15	37.8	1020	94.5	71	
	1200	575	404T	8D60P3G	DS-841W	1.15	37.8	1020	94.5	57	

General Purpose Three Phase, Totally Enclosed Fan Cooled (TEFC) World Motor 841 Plus® NEMA®+ Premium Efficient

(continued)

HP	RPM	Voltage	Frame	Catalog Number	Discount Symbol	SF	"C" Dim. (inches)	Ship Wt. (lbs)	Full Load Eff.	Full Load Amps	Notes
75	3600	460	365TS	8D75P1CS	DS-841W	1.15	30.3	710	94.1	83	
	3600	575	365TS	8D75P1GS	DS-841W	1.15	30.3	710	93.6	66	
	1800	460	365T	8D75P2C	DS-841W	1.15	32.4	750	95.4	85	
	1800	460	365T	8D75P2CB	DS-841W	1.15	32.4	750	95.4	85	
	1800	575	365T	8D75P2G	DS-841W	1.15	32.4	750	95.4	68	
	1200	460	405T	8D75P3C	DS-841W	1.15	37.8	1040	94.5	89	
	1200	460	405T	8D75P3CB	DS-841W	1.15	37.8	1040	94.5	89	09
	1200	575	405T	8D75P3G	DS-841W	1.15	37.8	1040	94.5	71	
	1200	575	405T	8D75P3GB	DS-841W	1.15	37.8	1040	94.5	71	09
100	3600	460	405TS	8D100P1CS	DS-841W	1.15	34.8	970	94.1	114	
	3600	575	405TS	8D100P1GS	DS-841W	1.15	34.8	970	94.1	91	
	1800	460	405T	8D100P2C	DS-841W	1.15	37.8	1060	95.4	115	
	1800	460	405T	8D100P2CB	DS-841W	1.15	37.8	1060	95.4	115	09
	1800	460	405TS	8D100P2CS	DS-841W	1.15	34.8	1060	95.4	115	
	1800	575	405T	8D100P2G	DS-841W	1.15	37.8	1060	95.4	91	
	1800	575	405T	8D100P2GB	DS-841W	1.15	37.8	1060	95.4	91	09
	1800	575	405TS	8D100P2GS	DS-841W	1.15	34.8	1060	95.4	91	
	1200	460	444T	8D100P3C	DS-841W	1.15	44.5	1570	95.0	120	11
	1200	460	444T	8D100P3CB	DS-841W	1.15	44.5	1570	95.0	120	09
	1200	575	444T	8D100P3G	DS-841W	1.15	44.5	1570	95.0	95	11
	125	3600	460	444TS	8D125P1CS	DS-841W	1.15	40.8	1430	95.0	142
3600		575	444TS	8D125P1GS	DS-841W	1.15	40.8	1430	95.0	113	
1800		460	444T	8D125P2C	DS-841W	1.15	44.5	1390	95.4	141	11
1800		460	444T	8D125P2CB	DS-841W	1.15	44.5	1390	95.4	141	09
1800		460	444TS	8D125P2CS	DS-841W	1.15	40.8	1390	95.4	141	
1800		575	444T	8D125P2G	DS-841W	1.15	44.5	1390	95.4	114	11
1800		575	444T	8D125P2GB	DS-841W	1.15	44.5	1390	95.4	114	09
1800		575	444TS	8D125P2GS	DS-841W	1.15	40.8	1390	95.4	114	
1200		460	445T	8D125P3C	DS-841W	1.15	44.5	1620	95.0	153	11
1200		460	445T	8D125P3CB	DS-841W	1.15	44.5	1620	95.0	153	09
1200		575	445T	8D125P3G	DS-841W	1.15	44.5	1620	95.0	125	11
1200		575	445T	8D125P3GB	DS-841W	1.15	44.5	1620	95.0	125	09
150	3600	460	445TS	8D150P1CS	DS-841W	1.15	40.8	1530	95.0	167	
	3600	575	445TS	8D150P1GS	DS-841W	1.15	40.8	1530	95.0	133	
	1800	460	445T	8D150P2C	DS-841W	1.15	44.5	1610	95.8	171	11
	1800	460	445T	8D150P2CB	DS-841W	1.15	44.5	1610	95.8	171	09
	1800	460	445TS	8D150P2CS	DS-841W	1.15	40.8	1610	95.8	171	
	1800	575	445T	8D150P2G	DS-841W	1.15	44.5	1610	95.8	137	11
	1800	575	445T	8D150P2GB	DS-841W	1.15	44.5	1610	95.8	137	09
	1200	460	447T	8D150P3C	DS-841W	1.15	48.0	1890	95.8	179	
	1200	460	447T	8D150P3CB	DS-841W	1.15	48.0	1890	95.8	179	09
200	3600	460	447TS	8D200P1CS	DS-841W	1.15	44.3	1730	95.4	222	
	3600	575	447TS	8D200P1GS	DS-841W	1.15	44.3	1760	95.4	178	
	1800	460	447T	8D200P2C	DS-841W	1.15	48.0	1840	96.2	226	
	1800	460	447T	8D200P2CB	DS-841W	1.15	48.0	1840	96.2	226	09
	1800	460	447TS	8D200P2CS	DS-841W	1.15	48.0	1840	96.2	226	
	1800	575	447T	8D200P2G	DS-841W	1.15	48.0	1840	96.2	181	
	1800	575	447T	8D200P2GB	DS-841W	1.15	48.0	1840	96.2	181	09
	1200	460	449T	8D200P3C	DS-841W	1.15	53.0	2500	95.8	224	

Note 09 Cylindrical Roller Bearing
Note 11 6318/6313 Bearing System

General Purpose Three Phase, Totally Enclosed Fan Cooled (TEFC) World Motor 841 Plus® NEMA®† Premium Efficient

(continued)

HP	RPM	Voltage	Frame	Catalog Number	Discount Symbol	SF	"C" Dim. (inches)	Ship Wt. (lbs)	Full Load Eff.	Full Load Amps	Notes
250	3600	460	449TS	8D250P1CS	DS-841W	1.15	49.3	2500	95.4	273	
	1800	460	449T	8D250P2C	DS-841W	1.15	53.0	2500	96.2	273	
	1800	460	449T	8D250P2CB	DS-841W	1.15	53.0	2500	96.2	273	09
300	3600	460	449TS	8D300P1CS	DS-841W	1.15	49.3	2500	95.4	327	
	1800	460	449T	8D300P2C	DS-841W	1.15	53.0	2500	96.2	326	
	1800	460	449T	8D300P2CB	DS-841W	1.15	53.0	2500	96.2	326	09
350	3600	460	449TS	8P350P1CS	DS-841	1.15	51.4	2800	95.8	374	AP,NWM
	1800	460	449T	8P350P2C	DS-841	1.15	55.1	2950	96.2	381	AP,NWM
	1800	460	449T	8P350P2CB	DS-841	1.15	55.1	2950	96.2	381	09,AP,NWM
400	3600	460	449TS	8P400P1CS	DS-841	1.15	51.4	2900	95.8	426	AP,NWM
	1800	460	449T	8P400P2C	DS-841	1.15	55.1	3025	96.2	434	09,AP,NWM

Note 09 Cylindrical Roller Bearing

Note AP No F2 convertibility

Note NWM Non-World Motor Construction