

General Purpose Three Phase, Totally Enclosed Fan Cooled (TEFC) World Motor HOSTILE DUTY® NEMA® Premium Efficient

APPLICATIONS:

For pulp & paper plants, saw mills, mines, foundries, chemical plants, waste management facilities, and other process-related industries requiring protection within harsh operating conditions.

FEATURES:

- Class F Insulation, Class B Rise At Full Load On 60 Hertz Sine Wave Power
- Corrosion Resistant Mill & Chemical Duty Paint
- Cast Iron Frame, Cast Iron End Brackets
- Stainless Steel Nameplate (with CE Mark) & Zinc Plated Hardware
- Shaft Slinger On Pulley End For IP54 Protection
- Dual Voltage 230/460 Volts (1-100 HP)
- 40°C Ambient, NEMA® Design B Performance On 60 Hz Sine Wave Power
- Torque On Regreasable Ball Bearings 250 Frame & Up, Lifting Provisions
- Self-Certified Class I, Division 2, Groups A, B, C, & D Double Shielded Bearings 140-360, Open on 400-440
- Steel Fan Cover & Conduit Box
- 1.15 Service Factor @ 60 Hz
- Field Convertible To F2 Mounting
- Condensation Drains With Plastic Plugs
- Conversion Kits: All Cast Iron Upgrade, C&D Flanges, Canopy Kits
- Bearing Caps On 400-440
- Suitable for 20:1 (3-60hz) Variable Torque; 5:1 (12-60hz) Constant Torque On Inverter Power

HP	RPM	Voltage	Frame	Catalog Number	Discount Symbol	SF	"C" Dim. (inches)	Ship Wt. (lbs)	Full Load Eff.	Full Load Amps	Notes
1	1800	200	143T	HD1P2H	DS-3HDW	1.15	13.5	60	85.5	3.4/3.4	
	1800	230/460	143T	HD1P2E	DS-3HDW	1.15	13.5	60	85.5	3/1.5	105,G
	1800	575	143T	HD1P2G	DS-3HDW	1.15	13.5	60	85.5	1.2	
	1200	200	145T	HD1P3H	DS-3HDW	1.15	13.5	70	82.5	4.1/4.1	
	1200	230/460	145T	HD1P3E	DS-3HDW	1.15	13.5	70	82.5	3.7/1.8	105,G
	1200	575	145T	HD1P3G	DS-3HDW	1.15	13.5	70	82.5	1.4	
	900	230/460	182T	HD1P4E	DS-3HDW	1.15	16.3	80	75.5	4.5/2.3	105,G
1 1/2	3600	200	143T	HD32P1H	DS-3HDW	1.15	13.5	50	84.0	4.5/4.4	
	3600	230/460	143T	HD32P1E	DS-3HDW	1.15	13.5	50	84.0	4.2-3.9/1.9	105,G
	3600	575	143T	HD32P1G	DS-3HDW	1.15	13.5	50	84.0	1.6	
	1800	200	145T	HD32P2H	DS-3HDW	1.15	13.5	70	86.5	4.7/4.7	
	1800	230/460	145T	HD32P2E	DS-3HDW	1.15	13.5	70	86.5	4.1/2.1	105,G
	1800	575	145T	HD32P2G	DS-3HDW	1.15	13.5	70	86.5	1.6	
	1200	200	182T	HD32P3H	DS-3HDW	1.15	16.3	90	87.5	5.1/5.1	
	1200	230/460	182T	HD32P3E	DS-3HDW	1.15	16.3	90	87.5	4.5/2.2	105,G
	1200	575	182T	HD32P3G	DS-3HDW	1.15	16.3	90	87.5	1.8	
	900	230/460	184T	HD32P4E	DS-3HDW	1.15	16.3	100	78.5	6.3/3.1	105,G
2	3600	200	145T	HD2P1H	DS-3HDW	1.15	13.5	50	85.5	5.7/5.6	
	3600	230/460	145T	HD2P1E	DS-3HDW	1.15	13.5	50	85.5	5/2.5	105,G
	3600	575	145T	HD2P1G	DS-3HDW	1.15	13.5	50	86.5	2	
	1800	200	145T	HD2P2H	DS-3HDW	1.15	13.5	70	86.5	6.2/6.1	
	1800	230/460	145T	HD2P2E	DS-3HDW	1.15	13.5	70	86.5	5.3/2.7	105,G
	1800	575	145T	HD2P2G	DS-3HDW	1.15	13.5	70	86.5	2.1	
	1200	200	184T	HD2P3H	DS-3HDW	1.15	16.3	100	88.5	7-Jul	
	1200	230/460	184T	HD2P3E	DS-3HDW	1.15	16.3	100	88.5	6.2/3.1	105,G
	1200	575	184T	HD2P3G	DS-3HDW	1.15	16.3	100	88.5	2.5	
	900	230/460	213T	HD2P4E	DS-3HDW	1.15	19.6	120	84.0	6.6/3.3	105,G
3	3600	200	182T	HD3P1H	DS-3HDW	1.15	16.3	70	86.5	9.3	
	3600	230/460	182T	HD3P1E	DS-3HDW	1.15	16.3	70	86.5	8.2/4.1	105,G
	3600	575	182T	HD3P1G	DS-3HDW	1.15	16.3	80	86.5	3.3	
	1800	200	182T	HD3P2H	DS-3HDW	1.15	16.3	90	89.5	8.8/8.6	
	1800	230/460	182T	HD3P2E	DS-3HDW	1.15	16.3	90	89.5	7.8/3.9	105,G
	1800	575	182T	HD3P2G	DS-3HDW	1.15	16.3	100	89.5	3.1	
	1200	200	213T	HD3P3H	DS-3HDW	1.15	19.6	150	89.5	9.8/9.6	
	1200	230/460	213T	HD3P3E	DS-3HDW	1.15	19.6	150	89.5	8.6/4.3	105,G
	1200	575	213T	HD3P3G	DS-3HDW	1.15	19.6	150	90.2	3.5	
	900	230/460	215T	HD3P4E	DS-3HDW	1.15	19.6	150	85.5	10.4/5.2	105,G

Note 105 208 Volt Suitable

Note G 60/50 Hz rated with no derate on HP; 230/460 volt 60 Hz ratings operate on 200/400 volt 50 Hz, 460V 60 Hz ratings operate on 400V 50 Hz; Full 60 & 50 Hz data on Nameplate

General Purpose Three Phase, Totally Enclosed Fan Cooled (TEFC) World Motor HOSTILE DUTY® NEMA® Premium Efficient

(continued)

HP	RPM	Voltage	Frame	Catalog Number	Discount Symbol	SF	"C" Dim. (inches)	Ship Wt. (lbs)	Full Load Eff.	Full Load Amps	Notes
5	3600	200	184T	HD5P1H	DS-3HDW	1.15	16.3	90	88.5	14.1/13.8	
	3600	230/460	184T	HD5P1E	DS-3HDW	1.15	16.3	90	88.5	12.3/6.1	105,G
	3600	575	184T	HD5P1G	DS-3HDW	1.15	16.3	90	88.5	4.9	
	1800	200	184T	HD5P2H	DS-3HDW	1.15	16.3	100	89.5	14.5/14.2	
	1800	230/460	184T	HD5P2E	DS-3HDW	1.15	16.3	100	89.5	12.7/6.3	105,G
	1800	575	184T	HD5P2G	DS-3HDW	1.15	16.3	110	89.5	5.1	
	1200	200	215T	HD5P3H	DS-3HDW	1.15	19.6	170	89.5	16.4/16.3	
	1200	230/460	215T	HD5P3E	DS-3HDW	1.15	19.6	170	89.5	14.2/7.1	105,G
	1200	575	215T	HD5P3G	DS-3HDW	1.15	19.6	170	89.5	5.7	
	900	230/460	254T	HD5P4E	DS-3HDW	1.15	24.9	220	86.5	15/7.5	02,105,G
7 1/2	3600	200	213T	HD7P1H	DS-3HDW	1.15	19.6	130	89.5	20.8/20.1	
	3600	230/460	213T	HD7P1E	DS-3HDW	1.15	19.6	130	89.5	18.1/9	105,G
	3600	575	213T	HD7P1G	DS-3HDW	1.15	19.6	130	89.5	7.2	
	1800	200	213T	HD7P2H	DS-3HDW	1.15	19.6	150	91.7	22/21.6	
	1800	230/460	213T	HD7P2E	DS-3HDW	1.15	19.6	150	91.7	19.1/9.6	105,G
	1800	575	213T	HD7P2G	DS-3HDW	1.15	19.6	160	91.7	7.8	
	1200	230/460	254T	HD7P3E	DS-3HDW	1.15	24.9	300	91.0	18.8/9.4	02,105,G
	1200	575	254T	HD7P3G	DS-3HDW	1.15	24.9	240	91.0	7.6	02
	900	230/460	256T	HD7P4E	DS-3HDW	1.15	24.9	250	86.5	22.3/11.1	02,105,G
	10	3600	200	215T	HD10P1H	DS-3HDW	1.15	19.6	140	90.2	27/25.9
3600		230/460	215T	HD10P1E	DS-3HDW	1.15	19.6	140	90.2	23.5/11.8	105,G
3600		575	215T	HD10P1G	DS-3HDW	1.15	19.6	140	90.2	9.3	
1800		200	215T	HD10P2H	DS-3HDW	1.15	19.6	170	91.7	29.3/29	
1800		230/460	215T	HD10P2E	DS-3HDW	1.15	19.6	160	91.7	27.5-25.7/12.8	105,G
1800		575	215T	HD10P2G	DS-3HDW	1.15	19.6	170	91.7	10.3	
1200		230/460	256T	HD10P3E	DS-3HDW	1.15	24.9	340	91.0	24.9/12.4	02,105,G
1200		575	256T	HD10P3G	DS-3HDW	1.15	24.9	260	91.0	10	02
900		230/460	284T	HD10P4E	DS-3HDW	1.15	27.5	310	89.5	28.3/14.2	02,105,G
15		3600	200	254T	HD15P1H	DS-3HDW	1.15	24.9	250	91.0	40/38
	3600	230/460	254T	HD15P1E	DS-3HDW	1.15	24.9	250	91.0	35/17.4	02,105,G
	3600	575	254T	HD15P1G	DS-3HDW	1.15	24.9	260	91.0	13.9	02
	1800	200	254T	HD15P2H	DS-3HDW	1.15	24.9	250	92.4	41	02
	1800	230/460	254T	HD15P2E	DS-3HDW	1.15	24.9	250	92.4	40-36/18	02,105,G
	1800	575	254T	HD15P2G	DS-3HDW	1.15	24.9	290	92.4	14.5	02
	1200	230/460	284T	HD15P3E	DS-3HDW	1.15	27.5	310	91.7	37/18.5	02,105,G
	1200	575	284T	HD15P3G	DS-3HDW	1.15	27.5	310	91.7	14.7	02
	900	230/460	286T	HD15P4E	DS-3HDW	1.15	27.5	370	89.5	42/20.9	02,105,G
	20	3600	200	256T	HD20P1H	DS-3HDW	1.15	24.9	260	91.0	53/51
3600		230/460	256T	HD20P1E	DS-3HDW	1.15	24.9	260	91.0	46/23	02,105,G
3600		575	256T	HD20P1G	DS-3HDW	1.15	24.9	270	91.0	18.4	02
1800		200	256T	HD20P2H	DS-3HDW	1.15	24.9	280	93.0	55/53	02
1800		230/460	256T	HD20P2E	DS-3HDW	1.15	24.9	280	93.0	47/23.7	02,105,G
1800		575	256T	HD20P2G	DS-3HDW	1.15	24.9	290	93.0	18.9	02
1200		230/460	286T	HD20P3E	DS-3HDW	1.15	27.5	350	91.7	49/24.4	02,105,G
1200		575	286T	HD20P3G	DS-3HDW	1.15	27.5	350	91.7	19.6	02
900		230/460	324T	HD20P4E	DS-3HDW	1.15	30.1	600	91.0	59-53/26.6	02,105,G
25		3600	200	284TS	HD25P1HS	DS-3HDW	1.15	26.1	325	91.7	66/63
	3600	230/460	284T	HD25P1E	DS-3HDW	1.15	27.5	310	91.7	58/28.8	02,105,G
	3600	230/460	284TS	HD25P1ES	DS-3HDW	1.15	26.1	310	91.7	58/28.8	02,105,G

Note 02 Suitable for Wye-Delta start on voltages shown
 Note 105 208 Volt Suitable

Note G 60/50 Hz rated with no derate on HP; 230/460 volt 60 Hz ratings operate on 200/400 volt 50 Hz, 460V 60 Hz ratings operate on 400V 50 Hz; Full 60 & 50 Hz data on Nameplate

General Purpose Three Phase, Totally Enclosed Fan Cooled (TEFC) World Motor HOSTILE DUTY® NEMA® Premium Efficient

(continued)

HP	RPM	Voltage	Frame	Catalog Number	Discount Symbol	SF	"C" Dim. (inches)	Ship Wt. (lbs)	Full Load Eff.	Full Load Amps	Notes	
	3600	575	284TS	HD25P1GS	DS-3HDW	1.15	26.1	310	91.7	23	02	
	1800	200	284T	HD25P2H	DS-3HDW	1.15	27.5	335	93.6	67/66	02	
	1800	230/460	284T	HD25P2E	DS-3HDW	1.15	27.5	330	93.6	58/29.2	02,105,G	
	1800	230/460	284TS	HD25P2ES	DS-3HDW	1.15	26.1	330	93.6	58/29.2	02,105,G	
	1800	575	284T	HD25P2G	DS-3HDW	1.15	27.5	330	93.6	23.3	02	
	1200	230/460	324T	HD25P3E	DS-3HDW	1.15	30.1	490	93.0	59/29.3	02,105,G	
	1200	575	324T	HD25P3G	DS-3HDW	1.15	30.1	490	93.0	23.4	02	
	900	230/460	326T	HD25P4E	DS-3HDW	1.15	30.1	625	91.0	74-66/33	02,105,G	
	30	3600	200	286TS	HD30P1HS	DS-3HDW	1.15	26.1	325	91.7	80/77	02
3600		230/460	286T	HD30P1E	DS-3HDW	1.15	27.5	310	91.7	69/35	02,105,G	
3600		230/460	286TS	HD30P1ES	DS-3HDW	1.15	26.1	310	91.7	69/35	02,105,G	
3600		575	286TS	HD30P1GS	DS-3HDW	1.15	26.1	310	91.7	27.7	02	
1800		200	286T	HD30P2H	DS-3HDW	1.15	27.5	345	93.6	82/81	02	
1800		230/460	286T	HD30P2E	DS-3HDW	1.15	27.5	340	93.6	70/35	02,105,G	
1800		230/460	286TS	HD30P2ES	DS-3HDW	1.15	26.1	340	93.6	70/35	02,105,G	
1800		575	286T	HD30P2G	DS-3HDW	1.15	27.5	340	93.6	28.1	02	
1200		230/460	326T	HD30P3E	DS-3HDW	1.15	30.1	520	92.4	70/35	02,105,G	
1200		575	326T	HD30P3G	DS-3HDW	1.15	30.1	520	93.0	28	02	
900		230/460	364T	HD30P4E	DS-3HDW	1.15	32.3	740	91.7	87-81/40	02,105,G	
40		3600	200	324TS	HD40P1HS	DS-3HDW	1.15	28.6	410	92.4	107/102	02
		3600	230/460	324TS	HD40P1ES	DS-3HDW	1.15	28.6	410	92.4	92/46	02,105,G
	3600	575	324TS	HD40P1GS	DS-3HDW	1.15	28.6	410	92.4	37	02	
	1800	200	324T	HD40P2H	DS-3HDW	1.15	30.1	450	94.1	106/104	02	
	1800	230/460	324T	HD40P2E	DS-3HDW	1.15	30.1	450	94.1	92/46	02,105,G	
	1800	230/460	324TS	HD40P2ES	DS-3HDW	1.15	28.6	450	94.1	92/46	02,105,G	
	1800	575	324T	HD40P2G	DS-3HDW	1.15	30.1	450	94.1	37	02	
	1200	200	364T	HD40P3H	DS-3HDW	1.15	32.3	630	94.1	108/106	02	
	1200	230/460	364T	HD40P3E	DS-3HDW	1.15	32.3	630	94.1	94/47	02,105,G	
	1200	575	364T	HD40P3G	DS-3HDW	1.15	32.3	630	94.1	37	02	
	900	230/460	365T	HD40P4E	DS-3HDW	1.15	32.3	910	92.4	116-105/53	02,105,G	
	900	230/460	365T	HD40P4E	DS-3HDW	1.15	32.3	910	92.4	105/53	02,105,G	
	50	3600	200	326TS	HD50P1HS	DS-3HDW	1.15	28.6	480	93.0	129/123	02
		3600	230/460	326TS	HD50P1ES	DS-3HDW	1.15	28.6	480	93.0	112/56	02,105,G
		3600	575	326TS	HD50P1GS	DS-3HDW	1.15	28.6	480	93.0	45	02
1800		200	326T	HD50P2H	DS-3HDW	1.15	30.1	550	94.5	128/123	02	
1800		230/460	326T	HD50P2E	DS-3HDW	1.15	30.1	550	94.5	112/56	02,105,G	
1800		230/460	326TS	HD50P2ES	DS-3HDW	1.15	28.6	550	94.5	112/56	02,105,G	
1800		575	326T	HD50P2G	DS-3HDW	1.15	30.1	550	94.5	45	02	
1200		200	365T	HD50P3H	DS-3HDW	1.15	32.3	680	94.1	134/130	02	
1200		230/460	365T	HD50P3E	DS-3HDW	1.15	32.3	680	94.1	117/59	02,105,G	
1200		575	365T	HD50P3G	DS-3HDW	1.15	32.3	680	94.1	47	02	
1200		575	365T	HD50P3G	DS-3HDW	1.15	32.3	680	94.1	47	02	
60		3600	200	364TS	HD60P1HS	DS-3HDW	1.15	30.2	560	93.6	158/154	02
		3600	230/460	364TS	HD60P1ES	DS-3HDW	1.15	30.2	560	93.6	136/69	02,105,G
	3600	575	364TS	HD60P1GS	DS-3HDW	1.15	30.2	560	93.6	55	02	
	1800	200	364T	HD60P2H	DS-3HDW	1.15	32.3	640	95.0	158/153	02	
	1800	230/460	364T	HD60P2E	DS-3HDW	1.15	32.3	640	95.0	137/68	02,105,G	
	1800	230/460	364TS	HD60P2ES	DS-3HDW	1.15	30.2	640	95.0	137/68	02,105,G	
	1800	575	364T	HD60P2G	DS-3HDW	1.15	32.3	640	95.0	55	02	
	1200	230/460	404T	HD60P3E	DS-3HDW	1.15	37.6	940	94.5	141/71	02,105,G	
	1200	575	404T	HD60P3G	DS-3HDW	1.15	37.6	940	94.5	57	02	

Note 02 Suitable for Wye-Delta start on voltages shown
Note 105 208 Volt Suitable

Note G 60/50 Hz rated with no derate on HP; 230/460 volt 60 Hz ratings operate on 200/400 volt 50 Hz, 460V 60 Hz ratings operate on 400V 50 Hz; Full 60 & 50 Hz data on Nameplate

GENERAL PURPOSE UNIMOUNT™
GENERAL PURPOSE C-FACE
GENERAL PURPOSE HOSTILE DUTY
GENERAL PURPOSE CORRO-DUTY
GENERAL PURPOSE 84 PLUS™
GENERAL PURPOSE OPEN DRIPPROOF
GENERAL PURPOSE HAZARDOUS LOCATION
GENERAL PURPOSE AUTOMOTIVE DUTY
COOLING TOWER DUTY
HAZARDOUS LOCATION
C-FACE MOTORS
VARIABLE SPEED MOTORS AND DRIVES

General Purpose Three Phase, Totally Enclosed Fan Cooled (TEFC) World Motor HOSTILE DUTY® NEMA® Premium Efficient

(continued)

HP	RPM	Voltage	Frame	Catalog Number	Discount Symbol	SF	"C" Dim. (inches)	Ship Wt. (lbs)	Full Load Eff.	Full Load Amps	Notes	
75	3600	200	365TS	HD75P1HS	DS-3HDW	1.15	30.2	650	93.6	190/184	02	
	3600	230/460	365TS	HD75P1ES	DS-3HDW	1.00	30.2	650	94.1	165/83	02,105,G	
	3600	575	365TS	HD75P1GS	DS-3HDW	1.15	30.2	650	94.1	66	02	
	1800	200	365T	HD75P2H	DS-3HDW	1.15	32.3	700	95.4	196/190	02	
	1800	230/460	365T	HD75P2E	DS-3HDW	1.15	32.3	700	95.4	170/85	02,105,G	
	1800	230/460	365T	HD75P2EB	DS-3HDW	1.15	32.3	560	95.4	170/85	02,09	
	1800	230/460	365TS	HD75P2ES	DS-3HDW	1.15	30.2	700	95.4	170/85	02,105,G	
	1800	575	365T	HD75P2G	DS-3HDW	1.15	32.3	700	95.4	68	02	
	1200	230/460	405T	HD75P3E	DS-3HDW	1.15	37.6	970	94.5	178/89	02,105,G	
	1200	230/460	405T	HD75P3EB	DS-3HDW	1.15	37.6	970	94.5	178/89	105,G	
	1200	575	405T	HD75P3G	DS-3HDW	1.15	37.6	970	94.5	71	02	
	100	3600	230/460	405TS	HD100P1ES	DS-3HDW	1.15	34.6	900	94.1	228/114	02,105,G
3600		575	405TS	HD100P1GS	DS-3HDW	1.15	34.6	920	94.1	91	02	
1800		200	405T	HD100P2H	DS-3HDW	1.15	37.7	1040	95.4	259/251	02	
1800		200	405TS	HD100P2HS	DS-3HDW	1.15	34.6	1040	95.4	259/251	02	
1800		230/460	405T	HD100P2E	DS-3HDW	1.15	37.7	980	95.4	229/115	02,105,G	
1800		230/460	405T	HD100P2EB	DS-3HDW	1.15	37.7	980	95.4	229/115	02,09,105,G	
1800		230/460	405TS	HD100P2ES	DS-3HDW	1.15	34.6	980	95.4	229/115	02,105,G	
1800		575	405T	HD100P2G	DS-3HDW	1.15	37.6	1010	95.4	91	02	
1200		230/460	444T	HD100P3E	DS-3HDW	1.15	44.4	1450	95.0	240/120	02,105,G	
1200		230/460	444T	HD100P3EB	DS-3HDW	1.15	44.4	1450	95.0	240/120	02,09,105,G	
1200		575	444T	HD100P3G	DS-3HDW	1.15	44.4	1500	95.0	95	02	
125		3600	460	444TS	HD125P1FS	DS-3HDW	1.15	40.6	1300	95.0	142	02,G
	3600	575	444TS	HD125P1GS	DS-3HDW	1.15	40.6	1360	95.0	113	02	
	1800	460	444T	HD125P2F	DS-3HDW	1.15	44.4	1260	95.8	141	02,G	
	1800	460	444T	HD125P2FB	DS-3HDW	1.15	44.4	1260	95.8	141	02,09,G	
	1800	460	444TS	HD125P2FS	DS-3HDW	1.15	40.6	1260	95.8	141	02,G	
	1800	575	444T	HD125P2G	DS-3HDW	1.15	44.4	1310	95.4	114	02	
	1200	460	445T	HD125P3F	DS-3HDW	1.15	44.4	1500	95.0	153	02,G	
	1200	460	445T	HD125P3FB	DS-3HDW	1.15	44.4	1500	95.0	153	02,09,G	
	1200	575	445T	HD125P3G	DS-3HDW	1.15	44.4	1550	95.0	125	02	
	150	3600	460	445TS	HD150P1FS	DS-3HDW	1.15	40.6	1410	95.0	167	02,G
		3600	575	445TS	HD150P1GS	DS-3HDW	1.15	40.6	1460	95.0	133	02
		1800	460	445T	HD150P2F	DS-3HDW	1.15	44.4	1480	95.8	171	02,G
1800		460	445T	HD150P2FB	DS-3HDW	1.15	44.4	1480	95.8	171	02,09,G	
1800		460	445TS	HD150P2FS	DS-3HDW	1.15	40.6	1480	95.8	171	02,G	
1800		575	445T	HD150P2G	DS-3HDW	1.15	44.4	1530	95.8	136	02	
1200		460	447T	HD150P3F	DS-3HDW	1.15	47.9	1760	95.8	179	02,G	
1200		460	447T	HD150P3FB	DS-3HDW	1.15	47.9	1760	95.8	179	02,09,G	
1200		575	447T	HD150P3G	DS-3HDW	1.15	47.9	1650	95.8	143	02	
200		3600	460	447TS	HD200P1FS	DS-3HDW	1.15	44.1	1600	95.4	222	02,G
		3600	575	447TS	HD200P1GS	DS-3HDW	1.15	44.1	1540	95.4	178	02
		1800	460	447T	HD200P2F	DS-3HDW	1.15	47.9	1710	96.2	225	02,G
	1800	460	447T	HD200P2FB	DS-3HDW	1.15	47.9	1710	96.2	225	02,09,G	
	1800	460	447TS	HD200P2FS	DS-3HDW	1.15	44.1	1710	96.2	225	02,G	
	1800	575	447T	HD200P2G	DS-3HDW	1.15	47.9	1630	96.2	181	02	

Note 02 Suitable for Wye-Delta start on voltages shown
 Note 09 Cylindrical Roller Bearing
 Note 105 208 Volt Suitable

Note G 60/50 Hz rated with no derate on HP; 230/460 volt 60 Hz ratings operate on 200/400 volt 50 Hz, 460V 60 Hz ratings operate on 400V 50 Hz; Full 60 & 50 Hz data on Nameplate