

Split Phase Belted Fan & Blower

Open Drip Proof, NEMA^{®†} 56 Frame, Single & Two Speed




APPLICATIONS:

Designed to meet manufacturer's requirements for belted fans and blowers.

FEATURES:

- Resilient Base
- Class B Insulation Unless Otherwise Noted
- With Threaded Conduit Hole
- Reversible Rotation
- Automatic Reset Thermal Overload Protector
- **Discount Symbol: DS-3HAC**



Single Speed, NEMA^{®†} 56 Frame

HP	RPM	Voltage	Catalog Number	Bearings	NEMA Frame	Amps	Shaft N"	"Shaft U"	Protector	"Total C"	SF	Ship Wt.	Notes
1/3	1725	115/208-230	8438	Ball	56Z	6.8/3.1-3.4	2.0	.500	Auto	10.2	1.35	17	
1/2	1725	115/230	4114	SAB	56	8.0/4.0	1.9	.625	Auto	9.8	1.25	22	
3/4	1725	115/230	4115	SAB	56	11.2/5.6	1.9	.625	Auto	9.8	1.25	24	

Two Speed, NEMA^{®†} 56 Frame

HP	RPM	Voltage	Catalog Number	Bearings	NEMA Frame	Amps	"Shaft N"	"Shaft U"	Protector	"Total C"	SF	Ship Wt.	Notes
1/3	1725/1140	115	5793C	SAB	56Z	5.9/3.6	1.5	0.500	Auto	10.4	1.00	21	80
1/2	1725/1140	115	5794C	SAB	56Z	8.7/5.1	1.5	.500	Auto	10.4	1.00	25	80
	1725/1140	115	4293	SAB	56	9.2/6.0	1.9	0.625	Auto	10.8	1.25	26	A
3/4	1725/1140	115	5795C	SAB	56	11.5/6.4	1.9	.625	Auto	11.3	1.00	27	80

Note 80: Canadian Standard — Connected CCWLE (Reversible)

Note A: Class A Insulation