

# Painted Washdown Three Phase, Totally Enclosed Energy Efficient C-Face



## APPLICATIONS:

Designed to meet requirements for food processors, canners, meat packers, bakeries, dairies, drug and cosmetic manufacturers for sanitary, easily cleaned motors.

## C-Face Footed

HP	RPM	Voltage	Frame	Catalog Number	List	Discount Symbol	SF	"C" Dim. (inches)	Ship Wt. (lbs.)	Full Load Eff.	Full Load Amps	Notes
2	3600	208-230/460	145TC	WD2E1A14C	\$375	DS-3F	1.15	13.4	35	85.5	6.1-5.6/2.8	-
	3600	208-230/440	56HC	WD2S1AHC	\$542	DS-3F	1.15	13.3	34	80.0	6.0-5.4 / 2.7	-
	1800	208-230/460	145TC	WD2E2A14C	\$601	DS-3F	1.15	14.4	41	84.0	6.3-6.1/3.1	-
	1800	208-230/460	56HC	WD2S2AHC	\$531	DS-3F	1.00	14.4	41	84.0	6.3-6.1/3.1	-
3	3600	208-230/460	145TC	WD3E1A14C	\$709	DS-3F	1.15	14.4	46	85.5	8.8-7.3/3.6	-
	1800	208-230/460	182TC	WD3E2DC	\$740	DS-3FTE	1.15	16.8	58	87.5	8.6-8.1/4	-
5	1800	208-230/460	184TC	WD5E2DC	\$837	DS-3FTE	1.15	16.8	87	87.5	14-12.6/6.3	-
7-1/2	1800	208-230/460	213TC	WD7E2DC	\$1,063	DS-3FTE	1.15	19.4	117	91.0	20.1-18.3/9.1	-
10	1800	208-230/460	215TC	WD10E2DC	\$1,177	DS-3FTE	1.15	20.4	128	91.0	26.6-23.8/11.9	-

## C-Face Footless

HP	RPM	Voltage	Frame	Catalog Number	List	Discount Symbol	SF	"C" Dim. (inches)	Ship Wt. (lbs.)	Full Load Eff.	Full Load Amps	Notes
1/3	1800	208-230/460	56C	WD13S2ACR	\$347	DS-3F	1.35	11.3	28	-	1.9-1.8/0.9	28
1/2	1800	208-230/460	56C	WD12S2ACR	\$383	DS-3F	1.15	11.3	29	-	1.9-1.8/0.9	28
3/4	1800	230/460	56C	WD34S2BCR	\$443	DS-3F	1.15	12.3	37	-	2.6/1.3	28
1	3600	208-230/460	56C	WD1S1ACR	\$379	DS-3F	1.15	12.3	37	-	3.4-3.2 / 1.6	28
	1800	208-230/460	143TC	WD1S2A14CR	\$464	DS-3F	1.15	12.8	41	77.4	3.4-3.3/1.7	28
	1800	230/460	56C	WD1S2BCR	\$464	DS-3F	1.15	12.8	41	-	3.6/1.8	28
1-1/2	3600	208-230/460	56C	WD32S1ACR	\$495	DS-3F	1.15	12.8	45	-	4.3-4.1/2.1	28
	1800	208-230/460	145TC	WD32S2A14CR	\$483	DS-3F	1.00	14.4	51	80.0	4.6-4.4/2/2	28
	1800	208-230/460	56C	WD32S2ACR	\$483	DS-3F	1.00	14.4	51	-	4.6-4.4/2.2	28
2	3600	208-230/460	56C	WD2S1ACR	\$560	DS-3FMP	1.15	13.4	34	-	6.0-5.4/2.7	-
	1800	208-230/460	145C	WD2E2A14CR	\$551	DS-3F	1.00	14.4	40	84.0	6.3-6.1/3.1	-
	1800	208-230/460	56C	WD2S2ACR	\$551	DS-3F	1.00	14.4	40	-	6.3-6.1/3.1	-
3	3600	208-230/460	56C	WD3S1ACR	\$662	DS-3F	1.15	14.4	47	-	8.8-7.3/3.6	-
	1800	208-230/460	182TC	WD3E2DCR	\$740	DS-3FTE	1.15	16.8	73	87.5	8.5-7.9/3.9	-
5	1800	208-230/460	184TC	WD5E2DCR	\$837	DS-3FTE	1.15	16.8	89	87.5	14-12.6/6.3	-
7-1/2	1800	208-230/460	213TC	WD7E2DCR	\$1,063	DS-3FTE	1.15	19.4	115	91.0	20.1-18.3/9.1	-
10	1800	208-230/460	215TC	WD10E2DCR	\$1,177	DS-3FTE	1.15	20.4	125	91.0	26.6-23.8/11.9	-

Note 28 TENV Enclosure

Note 96 Feather Picker Features = F0 Mounting Position