

**GENERAL PURPOSE
THREE PHASE, OPEN DRIPPROOF (ODP)
ENERGY EFFICIENT**



APPLICATIONS:

Pumps, Fans, Compressors, Material Handling and other general purpose applications where contaminants are minimal.

FEATURES:

- * Class F Insulation, Class B Rise At Service Factor
- * Rolled Steel Frame 56-320, Cast Iron Frame 360-440
- * Aluminum End Shields 56-250, Cast Iron End Shields 280-440
- * "CE" Mark On Nameplate
- * Full 50 & 60 Hertz Operating Data On Nameplate (3)
- * 40C Ambient, NEMA Design B Performance (4)
- * Full HP @ 50 Hz.
- * Regreasable Bearings 180 Frame & Up
- * Sealed Bearings 56-140, Double Shielded 180-400, Open On 440
- * Suitable For Wye-Delta Start 250 Frame & Larger
- * Dual Voltage Ratings Suitable For Part Winding Start (PWS) On Low Voltage
- * F1 Assembly Position
- * Conversion Kits: Canopy Kits (140-320 Frame)
- * Lifting Provisions 210 Frame & Up

HP	RPM	FRAME	VOLTS	CATALOG NUMBER	TYPE	LIST \$	DS SYM	SF	FULL LOAD		SHIP WGT	NOTES
									EFF	PF		
1/3	1800	56	208-230/460	D13S2A	POR	\$180	DS-3F	1.35	66.0	60.6	25	26
	1800	56	230/460	4314	FHP	\$159	DS-3FMP	1.35	-	-	17	
	1800	56H	208-230/460	8749	FHP	\$210	DS-3FMP	1.35	-	-	18	35
1/2	3600	56	208-230/460	D12S1A	POR	\$164	DS-3F	1.25	71.6	85.7	25	26
	1800	56	208-230/460	8746	FHP	\$209	DS-3FMP	1.25	-	-	22	35
	1800	56	208-230/460	8759	FHP	\$181	DS-3FMP	1.25	-	-	20	
	1800	56	208-230/460	D12S2A	POR	\$222	DS-3F	1.25	71.8	65.6	25	26
	1800	56	575	4388	FHP	\$190	DS-3FMP	1.25	-	-	21	
	1800	56HZ	230/460	7910	FHP	\$199	DS-3FMP	1.15	-	-	30	
3/4	3600	56	208-230/460	D34S1A	POR	\$200	DS-3F	1.25	77.8	90.7	25	26
	1800	56	208-230/460	8760	FHP	\$202	DS-3FMP	1.25	-	-	23	
	1800	56	208-230/460	D34S2A	POR	\$248	DS-3F	1.25	77.2	66.4	27	26
	1800	56	575	4361	FHP	\$215	DS-3FMP	1.25	-	-	24	
	1800	56H	208-230/460	8750	FHP	\$222	DS-3FMP	1.25	-	-	24	35
1	3600	56	208-230/460	D1S1A	POR	\$228	DS-3F	1.15	78.6	90.5	27	26
	1800	143T	200	D1E2H	FD	\$215	DS-3FOP	1.15	82.5	75.8	30	
	1800	143T	200	D1S2H	D	\$187	DS-3OP	1.15	80.0	71.0	30	
	1800	143T	208-230/460	D1E2D	FD	\$215	DS-3FOP	1.15	82.5	75.8	30	3
	1800	143T	575	D1E2G	FD	\$215	DS-3FOP	1.15	82.5	75.7	30	
	1800	56	208-230/460	8747	FHP	\$233	DS-3FMP	1.25	-	-	27	35
	1800	56H	208-230/460	7904	FHP	\$215	DS-3FMP	1.25	-	-	25	
	1800	56H	575	4370	FHP	\$223	DS-3FMP	1.15	-	-	25	
	1200	145T	200	D1E3H	FD	\$277	DS-3FOP	1.15	80.0	62.7	35	
	1200	145T	208-230/460	D1E3D	FD	\$277	DS-3FOP	1.25	80.0	66.5	35	3
	1200	145T	575	D1E3G	FD	\$277	DS-3FOP	1.15	80.0	64.5	35	
	900	182T	200	D1E4H	FD	\$390	DS-3FOP	1.15	74.0	59.6	50	
	900	182T	208-230/460	D1E4D	FD	\$390	DS-3FOP	1.15	74.0	54.0	50	3
	900	182T	575	D1E4G	FD	\$390	DS-3FOP	1.15	74.0	54.1	50	

**GENERAL PURPOSE
THREE PHASE, OPEN DRIPPROOF (ODP)
ENERGY EFFICIENT**



APPLICATIONS:

Pumps, Fans, Compressors, Material Handling and other general purpose applications where contaminants are minimal.

HP	RPM	FRAME	VOLTS	CATALOG NUMBER	TYPE	LIST \$	DS SYM	SF	FULL LOAD		SHIP WGT	NOTES
									EFF	PF		
1-1/2	3600	143T	200	D32E1H	FD	\$236	DS-3FOP	1.15	82.5	85.8	30	
	3600	143T	208-230/460	D32E1D	FD	\$236	DS-3FOP	1.15	82.5	86.0	30	3
	3600	143T	575	D32E1G	FD	\$236	DS-3FOP	1.15	82.5	85.8	30	
	1800	145T	200	D32E2H	FD	\$236	DS-3FOP	1.15	84.0	77.0	35	
	1800	145T	200	D32S2H	D	\$205	DS-3OP	1.15	80.0	74.6	35	
	1800	145T	208-230/460	D32E2D	FD	\$236	DS-3FOP	1.15	84.0	71.0	35	3
	1800	145T	575	D32E2G	FD	\$236	DS-3FOP	1.15	84.0	78.7	35	
	1800	56	208-230/460	8748	FHP	\$250	DS-3FMP	1.20	-	-	29	35
	1200	182T	200	D32E3H	FD	\$305	DS-3FOP	1.15	84.0	63.3	50	
	1200	182T	208-230/460	D32E3D	FD	\$305	DS-3FOP	1.15	84.0	63.4	50	3
	1200	182T	575	D32E3G	FD	\$305	DS-3FOP	1.15	84.0	64.2	50	
	900	184T	200	D32E4H	FD	\$473	DS-3FOP	1.15	77.0	56.8	60	
	900	184T	208-230/460	D32E4D	FD	\$473	DS-3FOP	1.15	77.0	55.5	60	3
	900	184T	575	D32E4G	FD	\$473	DS-3FOP	1.15	77.0	54.6	60	
2	3600	145T	200	D2E1H	FD	\$277	DS-3FOP	1.15	84.0	88.1	35	
	3600	145T	208-230/460	D2E1D	FD	\$277	DS-3FOP	1.15	84.0	87.9	35	3
	3600	145T	575	D2E1G	FD	\$277	DS-3FOP	1.15	84.0	87.8	35	
	1800	145T	200	D2E2H	FD	\$260	DS-3FOP	1.15	84.0	74.4	35	
	1800	145T	200	D2S2H	D	\$226	DS-3OP	1.15	82.5	71.7	35	
	1800	145T	208-230/460	D2E2D	FD	\$260	DS-3FOP	1.15	84.0	71.6	35	3
	1800	145T	575	D2E2G	FD	\$260	DS-3FOP	1.15	84.0	75.4	35	
	1200	184T	200	D2E3H	FD	\$312	DS-3FOP	1.15	85.5	65.0	60	
	1200	184T	208-230/460	D2E3D	FD	\$312	DS-3FOP	1.15	85.5	66.3	60	3
	1200	184T	575	D2E3G	FD	\$312	DS-3FOP	1.15	85.5	66.7	60	
	900	213T	200	D2E4H	FD	\$636	DS-3FOP	1.15	85.5	58.8	90	
	900	213T	208-230/460	D2E4D	FD	\$636	DS-3FOP	1.15	85.5	59.1	90	3
	900	213T	575	D2E4G	FD	\$636	DS-3FOP	1.15	85.5	58.2	90	
	3	3600	145T	200	D3E1H	FD	\$312	DS-3FOP	1.15	84.0	89.4	35
3600		145T	208-230/460	D3E1D	FD	\$312	DS-3FOP	1.15	84.0	89.4	35	3
3600		145T	575	D3E1G	FD	\$312	DS-3FOP	1.15	84.0	89.3	35	
1800		182T	200	D3E2H	FD	\$270	DS-3FOP	1.15	86.5	77.6	50	
1800		182T	200	D3S2H	D	\$252	DS-3OP	1.15	78.5	78.4	50	
1800		182T	208-230/460	D3E2D	FD	\$270	DS-3FOP	1.15	86.5	74.4	50	3
1800		182T	575	D3E2G	FD	\$270	DS-3FOP	1.15	86.5	75.4	50	
1200		213T	200	D3E3H	FD	\$432	DS-3FOP	1.15	86.5	72.8	90	
1200		213T	208-230/460	D3E3D	FD	\$432	DS-3FOP	1.15	86.5	71.2	90	3
1200		213T	575	D3E3G	FD	\$432	DS-3FOP	1.15	86.5	71.2	90	
900		215T	200	D3E4H	FD	\$815	DS-3FOP	1.15	86.5	59.6	100	
900		215T	208-230/460	D3E4D	FD	\$815	DS-3FOP	1.15	86.5	59.9	100	3
900		215T	575	D3E4G	FD	\$815	DS-3FOP	1.15	86.5	59.1	100	

**GENERAL PURPOSE
THREE PHASE, OPEN DRIPPROOF (ODP)
ENERGY EFFICIENT**



APPLICATIONS:

Pumps, Fans, Compressors, Material Handling and other general purpose applications where contaminants are minimal.

HP	RPM	FRAME	VOLTS	CATALOG NUMBER	TYPE	LIST \$	DS SYM	SF	FULL LOAD		SHIP WGT	NOTES
									EFF	PF		
5	3600	182T	200	D5E1H	FD	\$378	DS-3FOP	1.15	85.5	85.2	50	
	3600	182T	200	D5S1H	D	\$329	DS-3OP	1.15	85.5	82.9	50	
	3600	182T	208-230/460	D5E1D	FD	\$378	DS-3FOP	1.15	85.5	85.3	50	3
	3600	182T	575	D5E1G	FD	\$378	DS-3FOP	1.15	85.5	85.2	50	
	1800	184T	200	D5E2H	FD	\$327	DS-3FOP	1.15	87.5	84.9	60	
	1800	184T	200	D5S2H	D	\$284	DS-3OP	1.15	81.5	80.1	60	
	1800	184T	208-230/460	D5E2D	FD	\$327	DS-3FOP	1.15	87.5	80.1	60	3
	1800	184T	575	D5E2G	FD	\$327	DS-3FOP	1.15	88.5	83.9	60	
	1200	215T	200	D5E3H	FD	\$599	DS-3FOP	1.15	87.5	74.6	100	
	1200	215T	208-230/460	D5E3D	FD	\$599	DS-3FOP	1.15	87.5	73.5	100	3
	1200	215T	575	D5E3G	FD	\$599	DS-3FOP	1.15	87.5	73.8	100	
	900	254T	200	D5E4H	FD	\$1,045	DS-3FOP	1.15	88.5	69.4	150	2
	900	254T	208-230/460	D5E4D	FD	\$1,045	DS-3FOP	1.15	88.5	69.6	150	2,3
	900	254T	575	D5E4G	FD	\$1,045	DS-3FOP	1.15	87.5	70.2	150	2
7-1/2	3600	184T	200	D7E1H	FD	\$451	DS-3FOP	1.15	87.5	89.2	60	
	3600	184T	208-230/460	D7E1D	FD	\$451	DS-3FOP	1.15	87.5	88.5	60	3
	3600	184T	575	D7E1G	FD	\$451	DS-3FOP	1.15	87.5	88.5	60	
	1800	213T	200	D7E2H	FD	\$492	DS-3FOP	1.15	88.5	83.1	90	
	1800	213T	208-230/460	D7E2D	FD	\$492	DS-3FOP	1.15	88.5	79.4	90	3
	1800	213T	575	D7E2G	FD	\$492	DS-3FOP	1.15	88.5	83.0	90	
	1200	254T	200	D7E3H	FD	\$744	DS-3FOP	1.15	88.5	77.9	150	2
	1200	254T	208-230/460	D7E3D	FD	\$744	DS-3FOP	1.15	88.5	82.4	150	2,3
	1200	254T	575	D7E3G	FD	\$744	DS-3FOP	1.15	88.5	82.0	150	2
	900	256T	200	D7E4H	FD	\$1,329	DS-3FOP	1.15	88.5	68.7	160	2
	900	256T	208-230/460	D7E4D	FD	\$1,329	DS-3FOP	1.15	88.5	69.9	160	2,3
900	256T	575	D7E4G	FD	\$1,329	DS-3FOP	1.15	88.5	70.5	160	2	
10	3600	213T	200	D10E1H	FD	\$581	DS-3FOP	1.15	88.5	83.4	90	
	3600	213T	208-230/460	D10E1D	FD	\$581	DS-3FOP	1.15	88.5	83.7	90	3
	3600	213T	575	D10E1G	FD	\$581	DS-3FOP	1.15	88.5	83.1	90	
	1800	215T	200	D10E2H	FD	\$593	DS-3FOP	1.15	89.5	84.7	100	
	1800	215T	208-230/460	D10E2D	FD	\$593	DS-3FOP	1.15	89.5	82.7	100	3
	1800	215T	575	D10E2G	FD	\$593	DS-3FOP	1.15	89.5	84.8	100	
	1200	256T	200	D10E3H	FD	\$864	DS-3FOP	1.15	90.2	82.9	160	2
	1200	256T	208-230/460	D10E3D	FD	\$864	DS-3FOP	1.15	90.2	82.9	160	2,3
	1200	256T	575	D10E3G	FD	\$864	DS-3FOP	1.15	90.2	82.9	160	2
	900	284T	200	D10E4H	FD	\$1,577	DS-3FOP	1.15	89.5	72.9	210	2
	900	284T	208-230/460	D10E4D	FD	\$1,577	DS-3FOP	1.15	89.5	71.6	210	2,3
	900	284T	575	D10E4G	FD	\$1,577	DS-3FOP	1.15	89.5	72.8	210	2

**GENERAL PURPOSE
THREE PHASE, OPEN DRIPPROOF (ODP)
ENERGY EFFICIENT**



APPLICATIONS:

Pumps, Fans, Compressors, Material Handling and other general purpose applications where contaminants are minimal.

HP	RPM	FRAME	VOLTS	CATALOG NUMBER	TYPE	LIST \$	DS SYM	SF	FULL LOAD		SHIP WGT	NOTES
									EFF	PF		
15	3600	215T	200	D15E1H	FD	\$768	DS-3FOP	1.15	89.5	88.0	100	
	3600	215T	208-230/460	D15E1D	FD	\$768	DS-3FOP	1.15	89.5	86.5	100	3
	3600	215T	575	D15E1G	FD	\$768	DS-3FOP	1.15	89.5	86.5	100	
	1800	254T	200	D15E2H	FD	\$758	DS-3FOP	1.15	91.0	81.1	150	2
	1800	254T	208-230/460	D15E2D	FD	\$758	DS-3FOP	1.15	91.0	79.0	150	2,3
	1800	254T	575	D15E2G	FD	\$758	DS-3FOP	1.15	91.0	82.0	150	2
	1200	284T	200	D15E3H	FD	\$1,104	DS-3FOP	1.15	90.2	82.7	225	2
	1200	284T	208-230/460	D15E3D	FD	\$1,104	DS-3FOP	1.15	90.2	82.8	225	2,3
	1200	284T	575	D15E3G	FD	\$1,104	DS-3FOP	1.15	90.2	83.1	225	2
	900	286T	200	D15E4H	FD	\$2,072	DS-3FOP	1.15	89.5	73.7	230	2
	900	286T	208-230/460	D15E4D	FD	\$2,072	DS-3FOP	1.15	89.5	73.3	230	2,3
	900	286T	575	D15E4G	FD	\$2,072	DS-3FOP	1.15	89.5	74.0	230	2
20	3600	254T	200	D20E1H	FD	\$903	DS-3FOP	1.15	90.2	88.8	150	2
	3600	254T	208-230/460	D20E1D	FD	\$903	DS-3FOP	1.15	90.2	87.9	150	2,3
	3600	254T	575	D20E1G	FD	\$903	DS-3FOP	1.15	90.2	87.8	150	2
	1800	256T	200	D20E2H	FD	\$944	DS-3FOP	1.15	91.0	83.2	160	2
	1800	256T	208-230/460	D20E2D	FD	\$944	DS-3FOP	1.15	91.0	80.3	160	2,3
	1800	256T	575	D20E2G	FD	\$944	DS-3FOP	1.15	91.0	81.9	160	2
	1200	286T	200	D20E3H	FD	\$1,416	DS-3FOP	1.15	91.0	82.5	275	2
	1200	286T	208-230/460	D20E3D	FD	\$1,416	DS-3FOP	1.15	91.0	82.2	275	2,3
	1200	286T	575	D20E3G	FD	\$1,416	DS-3FOP	1.15	91.0	82.9	275	2
	900	324T	200	D20E4H	FD	\$2,452	DS-3FOP	1.15	90.2	76.6	420	2
	900	324T	208-230/460	D20E4D	FD	\$2,452	DS-3FOP	1.15	90.2	77.1	420	2,3
	900	324T	575	D20E4G	FD	\$2,452	DS-3FOP	1.15	90.2	77.0	420	2
25	3600	256T	200	D25E1H	FD	\$1,101	DS-3FOP	1.15	91.0	88.8	160	2
	3600	256T	208-230/460	D25E1D	FD	\$1,101	DS-3FOP	1.15	91.0	88.5	160	
	3600	256T	575	D25E1G	FD	\$1,101	DS-3FOP	1.15	91.0	88.8	160	2
	1800	284T	200	D25E2H	FD	\$1,112	DS-3FOP	1.15	91.7	84.0	225	2
	1800	284T	208-230/460	D25E2D	FD	\$1,112	DS-3FOP	1.15	91.7	85.1	225	2,3
	1800	284T	575	D25E2G	FD	\$1,112	DS-3FOP	1.15	91.7	83.8	225	2
	1800	284TS	200	D25E2HS	FD	\$1,112	DS-3FOP	1.15	91.7	84.0	225	2
	1800	284TS	208-230/460	D25E2DS	FD	\$1,112	DS-3FOP	1.15	91.7	85.1	225	2,3
	1800	284TS	575	D25E2GS	FD	\$1,112	DS-3FOP	1.15	91.7	83.8	225	2
	1200	324T	200	D25E3H	FD	\$1,662	DS-3FOP	1.15	91.7	85.8	420	2
	1200	324T	208-230/460	D25E3D	FD	\$1,662	DS-3FOP	1.15	91.7	85.8	420	2,3
	1200	324T	575	D25E3G	FD	\$1,662	DS-3FOP	1.15	91.7	86.0	420	2
	900	326T	200	D25E4H	FD	\$2,904	DS-3FOP	1.15	90.2	76.0	460	2
	900	326T	208-230/460	D25E4D	FD	\$2,904	DS-3FOP	1.15	91.0	76.9	460	2,3
	900	326T	575	D25E4G	FD	\$2,904	DS-3FOP	1.15	90.2	77.0	460	2

**GENERAL PURPOSE
THREE PHASE, OPEN DRIPPROOF (ODP)
ENERGY EFFICIENT**



APPLICATIONS:

Pumps, Fans, Compressors, Material Handling and other general purpose applications where contaminants are minimal.

HP	RPM	FRAME	VOLTS	CATALOG NUMBER	TYPE	LIST \$	DS SYM	SF	FULL LOAD		SHIP WGT	NOTES
									EFF	PF		
30	3600	284TS	200	D30E1HS	FD	\$1,251	DS-3FOP	1.15	91.0	88.3	225	2
	3600	284TS	208-230/460	D30E1DS	FD	\$1,251	DS-3FOP	1.15	91.0	88.6	225	2,3
	3600	284TS	575	D30E1GS	FD	\$1,251	DS-3FOP	1.15	91.0	88.6	225	2
	1800	286T	200	D30E2H	FD	\$1,299	DS-3FOP	1.15	92.4	86.3	250	2
	1800	286T	208-230/460	D30E2D	FD	\$1,299	DS-3FOP	1.15	92.4	85.7	250	2,3
	1800	286T	575	D30E2G	FD	\$1,299	DS-3FOP	1.15	92.4	85.7	250	2
	1800	286TS	200	D30E2HS	FD	\$1,299	DS-3FOP	1.15	92.4	86.3	250	2
	1800	286TS	208-230/460	D30E2DS	FD	\$1,299	DS-3FOP	1.15	92.4	85.7	250	2,3
	1800	286TS	575	D30E2GS	FD	\$1,299	DS-3FOP	1.15	92.4	85.7	250	2
	1200	326T	200	D30E3H	FD	\$1,863	DS-3FOP	1.15	92.4	86.0	460	2
	1200	326T	208-230/460	D30E3D	FD	\$1,863	DS-3FOP	1.15	92.4	85.9	460	2,3
	1200	326T	575	D30E3G	FD	\$1,863	DS-3FOP	1.15	92.4	85.9	460	2
	900	364T	230/460	D30E4E	FR	\$3,219	DS-3FOP	1.15	92.4	78.0	580	2,3
	900	364T	575	D30E4G	FR	\$3,219	DS-3FOP	1.15	92.4	78.0	580	2
40	3600	286TS	200	D40E1HS	FD	\$1,702	DS-3FOP	1.15	91.7	90.6	275	2
	3600	286TS	208-230/460	D40E1DS	FD	\$1,702	DS-3FOP	1.15	91.7	90.6	275	2,3
	3600	286TS	575	D40E1GS	FD	\$1,702	DS-3FOP	1.15	91.7	90.7	275	2
	1800	324T	200	D40E2H	FD	\$1,591	DS-3FOP	1.15	93.0	87.6	420	2
	1800	324T	200	D40S2H	D	\$1,446	DS-3OP	1.15	91.0	83.2	420	
	1800	324T	208-230/460	D40E2D	FD	\$1,591	DS-3FOP	1.15	93.0	87.5	420	2,3
	1800	324T	575	D40E2G	FD	\$1,591	DS-3FOP	1.15	93.0	87.7	420	2
	1800	324TS	200	D40E2HS	FD	\$1,591	DS-3FOP	1.15	93.0	87.6	420	2
	1800	324TS	208-230/460	D40E2DS	FD	\$1,591	DS-3FOP	1.15	93.0	87.5	420	2,3
	1800	324TS	575	D40E2GS	FD	\$1,591	DS-3FOP	1.15	93.0	87.7	420	2
	1200	364T	230/460	D40E3E	FR	\$2,556	DS-3FOP	1.15	93.0	86.5	580	2,3
	1200	364T	575	D40E3G	FR	\$2,556	DS-3FOP	1.15	93.6	86.2	580	2
	900	365T	230/460	D40E4E	FR	\$3,987	DS-3FOP	1.15	91.0	77.7	600	2,3
	900	365T	575	D40E4G	FR	\$3,987	DS-3FOP	1.15	91.7	78.4	600	2
50	3600	324TS	200	D50E1HS	FD	\$2,061	DS-3FOP	1.15	92.4	87.8	420	2
	3600	324TS	208-230/460	D50E1DS	FD	\$2,061	DS-3FOP	1.15	92.4	87.5	420	2,3
	3600	324TS	575	D50E1GS	FD	\$2,061	DS-3FOP	1.15	92.4	87.8	420	2
	1800	326T	200	D50E2H	FD	\$1,857	DS-3FOP	1.15	93.0	88.4	460	2
	1800	326T	208-230/460	D50E2D	FD	\$1,857	DS-3FOP	1.15	93.0	88.3	460	2,3
	1800	326T	575	D50E2G	FD	\$1,857	DS-3FOP	1.15	93.0	87.5	460	2
	1800	326TS	200	D50E2HS	FD	\$1,857	DS-3FOP	1.15	93.0	88.4	460	2
	1800	326TS	208-230/460	D50E2DS	FD	\$1,857	DS-3FOP	1.15	93.0	88.3	460	2,3
	1800	326TS	575	D50E2GS	FD	\$1,857	DS-3FOP	1.15	93.0	87.5	460	2
	1200	365T	230/460	D50E3E	FR	\$3,108	DS-3FOP	1.15	93.0	86.4	600	2,3
	1200	365T	575	D50E3G	FR	\$3,108	DS-3FOP	1.15	93.6	86.4	600	2
	900	404T	230/460	D50E4E	FR	\$4,750	DS-3FOP	1.15	91.7	77.0	750	2,3
	900	404T	575	D50E4G	FR	\$4,750	DS-3FOP	1.15	92.4	76.9	750	2

**GENERAL PURPOSE
THREE PHASE, OPEN DRIPPROOF (ODP)
ENERGY EFFICIENT**



APPLICATIONS:

Pumps, Fans, Compressors, Material Handling and other general purpose applications where contaminants are minimal.

HP	RPM	FRAME	VOLTS	CATALOG NUMBER	TYPE	LIST \$	DS SYM	SF	FULL LOAD		SHIP WGT	NOTES
									EFF	PF		
60	3600	326TS	200	D60E1HS	FD	\$2,470	DS-3FOP	1.15	93.0	88.7	460	2
	3600	326TS	208-230/460	D60E1DS	FD	\$2,470	DS-3FOP	1.15	93.0	88.7	460	2,3
	3600	326TS	575	D60E1GS	FD	\$2,470	DS-3FOP	1.15	93.0	88.8	460	2
	1800	364T	230/460	D60E2E	FR	\$2,284	DS-3FOP	1.15	93.6	87.0	580	2,3
	1800	364T	575	D60E2G	FR	\$2,284	DS-3FOP	1.15	94.1	86.4	580	2
	1800	364TS	230/460	D60E2ES	FR	\$2,284	DS-3FOP	1.15	93.6	85.9	580	2,3
	1800	364TS	575	D60E2GS	FR	\$2,284	DS-3FOP	1.15	94.1	86.4	580	2
	1200	404T	230/460	D60E3E	FR	\$3,592	DS-3FOP	1.15	93.6	86.7	750	2,3
	1200	404T	575	D60E3G	FR	\$3,592	DS-3FOP	1.15	93.6	86.0	750	2
	900	405T	230/460	D60E4E	FR	\$5,507	DS-3FOP	1.15	92.4	76.9	800	2,3
900	405T	575	D60E4G	FR	\$5,507	DS-3FOP	1.15	93.0	77.9	800	2	
75	3600	364TS	230/460	D75E1ES	FR	\$3,129	DS-3FOP	1.15	93.0	87.5	580	2,3
	3600	364TS	575	D75E1GS	FR	\$3,129	DS-3FOP	1.15	94.1	87.8	580	2
	1800	365T	230/460	D75E2E	FR	\$2,906	DS-3FOP	1.15	94.1	86.4	600	2,3
	1800	365T	575	D75E2G	FR	\$2,906	DS-3FOP	1.15	95.0	85.0	600	2
	1800	365TS	230/460	D75E2ES	FR	\$2,906	DS-3FOP	1.15	94.1	86.4	600	2,3
	1800	365TS	575	D75E2GS	FR	\$2,906	DS-3FOP	1.15	95.0	85.0	600	2
	1200	405T	230/460	D75E3E	FR	\$4,317	DS-3FOP	1.15	93.6	85.9	800	2,3
	1200	405T	575	D75E3G	FR	\$4,317	DS-3FOP	1.15	93.6	86.8	800	2
	900	444T	230/460	D75E4E	FR	\$6,625	DS-3FOP	1.15	93.6	79.7	1100	2,3
	900	444T	575	D75E4G	FR	\$6,625	DS-3FOP	1.15	94.1	80.4	1100	2
100	3600	365TS	230/460	D100E1ES	FR	\$4,302	DS-3FOP	1.15	93.0	89.0	600	2,3
	3600	365TS	575	D100E1GS	FR	\$4,302	DS-3FOP	1.15	94.1	89.2	600	2
	1800	404T	230/460	D100E2E	FR	\$3,744	DS-3FOP	1.15	94.1	87.5	750	2,3
	1800	404T	575	D100E2G	FR	\$3,744	DS-3FOP	1.15	95.0	87.8	750	2
	1800	404TS	230/460	D100E2ES	FR	\$3,744	DS-3FOP	1.15	94.1	87.5	750	2,3
	1800	404TS	575	D100E2GS	FR	\$3,744	DS-3FOP	1.15	95.0	87.8	750	2
	1200	444T	230/460	D100E3E	FR	\$5,470	DS-3FOP	1.15	94.1	81.7	1100	2,3
	1200	444T	575	D100E3G	FR	\$5,470	DS-3FOP	1.15	95.0	80.3	1100	2
	900	445T	230/460	D100E4E	FR	\$9,342	DS-3FOP	1.15	93.6	81.4	1200	2,3
	900	445T	575	D100E4G	FR	\$8,342	DS-3FOP	1.15	94.1	81.4	1200	2
125	3600	404TS	460	D125E1FS	FR	\$5,292	DS-3FOP	1.15	94.1	91.0	750	2,3
	3600	404TS	575	D125E1GS	FR	\$5,292	DS-3FOP	1.15	94.1	90.8	750	2
	1800	405T	460	D125E2F	FR	\$4,306	DS-3FOP	1.15	95.0	87.8	800	2,3
	1800	405T	575	D125E2G	FR	\$4,306	DS-3FOP	1.15	95.0	87.7	800	2
	1800	405TS	460	D125E2FS	FR	\$4,306	DS-3FOP	1.15	95.0	87.8	800	2,3
	1800	405TS	575	D125E2GS	FR	\$4,306	DS-3FOP	1.15	95.0	87.7	800	2
	1200	445T	460	D125E3F	FR	\$6,654	DS-3FOP	1.15	94.1	81.5	1200	2,3
	1200	445T	575	D125E3G	FR	\$6,654	DS-3FOP	1.15	95.0	80.9	1200	2
	900	445T	460	D125E4F	FR	\$9,701	DS-3FOP	1.15	93.6	80.7	1200	2,3
	900	445T	575	D125E4G	FR	\$9,701	DS-3FOP	1.15	93.6	80.4	1200	2

**GENERAL PURPOSE
THREE PHASE, OPEN DRIPPROOF (ODP)
ENERGY EFFICIENT**



APPLICATIONS:

Pumps, Fans, Compressors, Material Handling and other general purpose applications where contaminants are minimal.

HP	RPM	FRAME	VOLTS	CATALOG NUMBER	TYPE	LIST \$	DS SYM	SF	FULL LOAD		SHIP WGT	NOTES
									EFF	PF		
150	3600	405TS	460	D150E1FS	FR	\$6,845	DS-3FOP	1.15	93.6	91.0	800	2,3
	3600	405TS	575	D150E1GS	FR	\$6,845	DS-3FOP	1.15	93.6	91.0	800	2
	1800	444T	460	D150E2F	FR	\$6,192	DS-3FOP	1.15	95.4	85.6	1100	2,3
	1800	444T	575	D150E2G	FR	\$6,192	DS-3FOP	1.15	95.4	85.3	1100	2
	1800	444TS	460	D150E2FS	FR	\$6,192	DS-3FOP	1.15	95.4	85.6	1100	2,3
	1800	444TS	575	D150E2GS	FR	\$6,192	DS-3FOP	1.15	95.4	85.3	1100	2
	1200	445T	460	D150E3F	FR	\$7,329	DS-3FOP	1.15	95.4	79.4	1200	2,3
	1200	445T	575	D150E3G	FR	\$7,329	DS-3FOP	1.15	95.4	78.7	1200	2
	900	447T	460	D150E4F	FR	\$10,945	DS-3FOP	1.15	94.1	81.8	1700	2,3
900	447T	575	D150E4G	FR	\$10,945	DS-3FOP	1.15	94.1	81.8	1700	2	
200	3600	444TS	460	D200E1FS	FR	\$9,000	DS-3FOP	1.15	94.5	87.5	1100	2,3
	3600	444TS	575	D200E1GS	FR	\$9,000	DS-3FOP	1.15	94.5	87.5	1100	2
	1800	445T	460	D200E2F	FR	\$7,549	DS-3FOP	1.15	95.4	85.9	1200	2,3
	1800	445T	575	D200E2G	FR	\$7,549	DS-3FOP	1.15	95.8	85.2	1200	2
	1800	445TS	460	D200E2FS	FR	\$7,549	DS-3FOP	1.15	95.4	85.9	1200	2,3
	1800	445TS	575	D200E2GS	FR	\$7,549	DS-3FOP	1.15	95.8	85.2	1200	2
	1200	445T	460	D200E3F	FR	\$9,574	DS-3FOP	1.15	94.5	84.6	1200	2,3
	1200	445T	575	D200E3G	FR	\$9,574	DS-3FOP	1.15	94.5	85.3	1200	2
	900	449T	460	D200E4F	FR	\$11,132	DS-3FOP	1.15	93.6	78.5	2000	2,3,57
900	449T	575	D200E4G	FR	\$11,132	DS-3FOP	1.00	93.6	79.2	2000	2,57	
250	3600	445TS	460	D250E1FS	FR	\$10,784	DS-3FOP	1.15	95.0	87.7	1200	2,3
	3600	445TS	575	D250E1GS	FR	\$10,784	DS-3FOP	1.00	94.5	88.2	1200	2
	1800	445T	460	D250E2F	FR	\$9,528	DS-3FOP	1.15	95.4	88.4	1200	2,3
	1800	445T	575	D250E2G	FR	\$9,528	DS-3FOP	1.15	95.4	88.8	1200	2
	1800	445TS	460	D250E2FS	FR	\$9,528	DS-3FOP	1.15	95.4	88.4	1200	2,3
	1800	445TS	575	D250E2GS	FR	\$9,528	DS-3FOP	1.15	95.4	88.8	1200	2
	1200	447T	460	D250E3F	FR	\$10,546	DS-3FOP	1.15	95.4	86.4	1700	2,3
	1200	447T	575	D250E3G	FR	\$10,546	DS-3FOP	1.00	95.4	85.8	1700	2
	300	3600	445TS	460	D300E1FS	FR	\$12,665	DS-3FOP	1.15	95.4	90.2	1200
3600		445TS	575	D300E1GS	FR	\$12,665	DS-3FOP	1.00	95.4	91.8	1200	2
1800		447T	460	D300E2F	FR	\$10,569	DS-3FOP	1.15	95.4	89.5	1700	2,3
1800		447T	575	D300E2G	FR	\$10,569	DS-3FOP	1.15	95.4	89.9	1700	2
1800		447TS	460	D300E2FS	FR	\$10,569	DS-3FOP	1.15	95.4	89.5	1700	2,3
1800		447TS	575	D300E2GS	FR	\$10,569	DS-3FOP	1.15	95.4	89.5	1700	2
1200		449T	460	D300E3F	FR	\$12,246	DS-3FOP	1.15	95.0	84.7	2000	2,3,57
350	3600	447TS	460	D350E1FS	FR	\$14,506	DS-3FOP	1.15	95.0	91.1	1700	2,3
	3600	447TS	575	D350E1GS	FR	\$14,506	DS-3FOP	1.00	95.4	92.4	1700	2
	1800	447T	460	D350E2F	FR	\$11,665	DS-3FOP	1.15	95.8	89.3	1700	2,3
	1800	447T	575	D350E2G	FR	\$11,665	DS-3FOP	1.15	95.4	90.1	1700	2
	1800	447TS	460	D350E2FS	FR	\$11,665	DS-3FOP	1.15	95.8	89.3	1700	2,3
	1800	447TS	575	D350E2GS	FR	\$11,665	DS-3FOP	1.15	95.4	89.6	1700	2

**GENERAL PURPOSE
THREE PHASE, OPEN DRIPPROOF (ODP)
ENERGY EFFICIENT**



APPLICATIONS:

Pumps, Fans, Compressors, Material Handling and other general purpose applications where contaminants are minimal.

HP	RPM	FRAME	VOLTS	CATALOG NUMBER	TYPE	LIST \$	DS SYM	SF	FULL LOAD		SHIP WGT	NOTES
									EFF	PF		
400	3600	447TS	575	D400E1GS	FR	\$16,506	DS-3FOP	1.00	95.4	91.6	1700	2
	3600	449TS	460	D400E1FS	FR	\$16,506	DS-3FOP	1.15	95.4	90.5	2000	
	1800	449TM	460	D400E2F	FR	\$12,380	DS-3FOP	1.15	95.4	88.6	2000	2,3,57
	1800	449TM	575	D400E2GT	FR	\$12,380	DS-3FOP	1.15	95.8	89.7	2000	2,57