



US MOTORS

CAT NO. 9624

MODEL K33NVWLJ-1416 HP 1/50-1/70

VOLT 115 HZ 60 AMP 0.43-0.37 PH 1

R.P.M. 1550 THERMALLY PROTECTED

INS CL B 40° C AMB MFG. NO. (XXX)U

AIR OVER CONT

CW SHAFT END REV

BLK - LINE

BLK - LINE

YEL → INS

BLU → INS

RED → INS

ORG → INS

TO REVERSE ROTATION INTERCHANGE

BLU & ORG LEADS

CAP 1MFD 370 VAC

WARNING: FOLLOW ALL SAFETY INFORMATION TO REDUCE POTENTIAL ELECTRICAL SHOCK. DISCONNECT POWER BEFORE SERVICING. FOLLOW NATIONAL AND LOCAL CODES FOR GROUNDING AND INSULATE UNUSED LEAD WIRES INDIVIDUALLY.

MADE IN CHINA

US

ALL DIMENSIONS ARE IN INCHES

MODEL	REF	CUSTOMER	HP	VOLTS	AMPS	HZ	RPM	ROTATION	CUSTOMER PN	
K33NVWLJ-1416	--	WHOLESALE-HAC	1/50-1/70	115	0.43-0.37	60	1550	CW SHAFT END REV	9624	
SHEET NUMBER	REV	REVISION RECORD FOR: C4810-00					INFORMATION DISCLOSED ON THIS DOCUMENT IS CONSIDERED PROPRIETARY AND SHALL NOT BE REPRODUCED OR DISCLOSED WITHOUT WRITTEN CONSENT OF NIDEC MOTOR CORPORATION			NIDEC MOTOR CORPORATION
1 OF 1	C	REVISED CAPACITOR MOUNTING TO LEAD END.								
REVISION DATE	06-DEC-11									
ALL DIMENSIONS ARE FOR REFERENCE ONLY UNLESS TOLERANCE IS GIVEN										
ISSUED BY	REVIEWED BY	ENGINEER APPROVED	TITLE				CODE	ITEM NO.	SIZE	
J. CORONADO	M. COLLINS	M. COLLINS	ASSEMBLED VIEW				V01	778389	B	