



CAT NO. 9657

MODEL K33NVWLH-1415 HP 1/10

VOLT 230 HZ 60 AMP 1.0 A

R.P.M. 1550 THERMALLY PROTECTED

INS CL B 40° C AMB MFG. NO. (XXX)U PH 1

AIR OVER CONT

WARNING: FOLLOW ALL SAFETY INFORMATION. TO REDUCE POTENTIAL ELECTRICAL SHOCK DISCONNECT POWER BEFORE SERVICING. FOLLOW NATIONAL AND LOCAL CODES FOR GROUNDING AND INSULATE UNUSED LEAD WIRES INDIVIDUALLY. NIDEC MOTOR CORPORATION www.usmotors.com MADE IN CHINA

ROTATION: VIEW FROM SHAFT END

CCW CW

WHITE — INS WHITE — INS

BLUE — INS RED — INS

BLACK — LINE BLACK — LINE

RED — LINE BLUE — LINE

ORANGE — LINE ORANGE — LINE

BROWN — CAP BROWN — CAP

BROWN — CAP

CAP 5 MFD 450 VAC

90 mm

50 mm

ALL DIMENSIONS ARE IN INCHES

MODEL	REF	CUSTOMER	HP	VOLTS	AMPS	HZ	RPM	ROTATION	CUSTOMER PN					
K33NVWLH-1415	--	WHOLESALE-HAC	1/10	230	1.0	60	1550	CCW SHAFT END REVERSIBLE	9657					
SHEET NUMBER	REV	REVISION RECORD FOR: C4777-00			INFORMATION DISCLOSED ON THIS DOCUMENT IS CONSIDERED PROPRIETARY AND SHALL NOT BE REPRODUCED OR DISCLOSED WITHOUT WRITTEN CONSENT OF NIDEC MOTOR CORPORATION				NIDEC MOTOR CORPORATION					
1 OF 1	-	CREATED DRAWING												
REVISION DATE														
	29-NOV-11				ALL DIMENSIONS ARE FOR REFERENCE ONLY UNLESS TOLERANCE IS GIVEN									
ISSUED BY	M. COLLINS	REVIEWED BY	M. COLLINS	ENGINEER APPROVED	M. COLLINS	TITLE		ASSEMBLED VIEW	CODE	V01	ITEM NO.	789413	SIZE	B