



**Materials & Finishes - Standard:**

- **Base Metal:** Steel conforms to ASTM A1011 SS GR 33, A1011 HSLAS GR 45, A36, A575, A576, or A635.
- **Electrogalvanized (EG):** Conforms to ASTM B633, Type III SC1
- **Unistrut Defender (DF):** Conforms to ASTM A1059
- **Hot Dip Galvanized (HG):** Conforms to ASTM A123 or A153
- **Perma-Green (GR):** Conforms to commercial standards for powder coating
- **Perma-Gold (ZD):** Conforms to ASTM B633, Type II SC1 or SC3
- **Plain (PL):** No finish

**Materials & Finishes - Special Metals:**

- **Stainless Steel, Type 304 (SS):** Conforms to ASTM A240 or A276, Type 304 \*
- **Stainless Steel, Type 316 (ST):** Conforms to ASTM A240 or A276, Type 316 \*
- **Aluminum (AL):** Conforms to ASTM B209, Type 1100F or 5052-H32 \*

\* These materials have different physical properties and performance characteristics. Please [contact us](#) for design support.

Part No.	Nom. Pipe Size	Finish	Product Weight / Piece (lbs)
P1201	12" Wide	EG	1.86
P1201	12" Wide	HG	1.972
P1201	12" Wide	GR	1.86
P1202	15" Wide	HG	2.343
P1202	15" Wide	GR	2.21
P1203	18" Wide	HG	2.692
P1203	18" Wide	GR	2.54