



Materials & Finishes - Standard:

- **Base Metal:** Steel conforms to ASTM A1011 SS GR 33, A1011 HSLAS GR 45, A36, A575, A576, or A635.
- **Electrogalvanized (EG):** Conforms to ASTM B633, Type III SC1
- **Unistrut Defender (DF):** Conforms to ASTM A1059
- **Hot Dip Galvanized (HG):** Conforms to ASTM A123 or A153
- **Perma-Green (GR):** Conforms to commercial standards for powder coating
- **Perma-Gold (ZD):** Conforms to ASTM B633, Type II SC1 or SC3
- **Plain (PL):** No finish

Materials & Finishes - Special Metals:

- **Stainless Steel, Type 304 (SS):** Conforms to ASTM A240 or A276, Type 304 *
- **Stainless Steel, Type 316 (ST):** Conforms to ASTM A240 or A276, Type 316 *
- **Aluminum (AL):** Conforms to ASTM B209, Type 1100F or 5052-H32 *

* These materials have different physical properties and performance characteristics. Please [contact us](#) for design support.

Part No.	Nom. Pipe Size	Finish	Product Weight / Piece (lbs)
P2073A	STD	EG	4.08
P2073A	STD	HG	4.325
P2073A	STD	GR	4.08
P2073A	STD	SS	4.08
P2073A	STD	ST	4.08
P2073A	STD	AL	1.63
P2073ASQ	SQ	EG	4.08
P2073ASQ	SQ	HG	4.325
P2073ASQ	SQ	GR	4.08
P2073ASQ	SQ	SS	4.08
P2073ASQ	SQ	ST	4.08
P2073ASQ	SQ	AL	1.63