

2013

# WEG Automation Catalog

## Variable Frequency Drives, Soft Starters and Controls





# Variable Frequency Drives CFW09 DB Resistors

DB Resistors 20% Duty Cycle - NEMA 1 Enclosure



CFW09

Motor Volts	Motor HP	For Use with CFW-09 Model Number:	Catalog Number	OHMS	WATTS	Dimensions H x W x D	List Price	Multiplier Symbol
230 V	1.5	<a href="#">CFW-090006TDZ</a>	<a href="#">CFDB39-224*</a>	39	224	12 X 5 X 4	<b>\$183</b>	V1
	2	<a href="#">CFW-090007TDZ</a>	<a href="#">CFDB27-298*</a>	27	298	12 X 5 X 4	<b>\$183</b>	V1
	3	<a href="#">CFW-090010TDZ</a>	<a href="#">CFDB27-448*</a>	27	448	12 X 7 X 5	<b>\$319</b>	V1
	3	<a href="#">CFW-090013TDZ</a>	<a href="#">CFDB22-746</a>	22	746	12 X 7 X 5	<b>\$319</b>	V1
	5	<a href="#">CFW-090016TDZ</a>	<a href="#">CFDB22-746*</a>	22	746	12 X 7 X 5	<b>\$319</b>	V1
	7.5	<a href="#">CFW-090024TDZ</a>	<a href="#">CFDB15-1120</a>	15	1,120	12 X 10 X 5	<b>\$481</b>	V1
	10	<a href="#">CFW-090028TDZ</a>	<a href="#">CFDB10-1492</a>	10	1,492	12 X 16 X 5	<b>\$795</b>	V1
	15	<a href="#">CFW-090045TDZ</a>	<a href="#">CFDB8.6-2238</a>	8.6	2238	19 X 13 X 5	<b>\$1,092</b>	V1
	20	<a href="#">CFW-090054TDDDBZ</a>	<a href="#">CFDB4.7-2984</a>	4.7	2984	26.5 X 10 X 5	<b>\$1,215</b>	V1
	25	<a href="#">CFW-090070TDDDBZ</a>	<a href="#">CFDB3.3-4476</a>	3.3	4476	26.5 X 10 X 5	<b>\$1,403</b>	V1
	30	<a href="#">CFW-090086TDDDBZ</a>	<a href="#">CFDB3.3-4476</a>	3.3	4476	26.5 X 10 X 5	<b>\$1,403</b>	V1
	40	<a href="#">CFW-090105TDDDBZ</a>	<a href="#">CFDB2.2-7460</a>	2.2	7460	26.5 X 13 X 5	<b>\$1,870</b>	V1
50	<a href="#">CFW-090130TDDDBZ</a>	<a href="#">CFDB2.2-7460</a>	2.2	7460	26.5 X 13 X 5	<b>\$1,870</b>	V1	
460V	1.5	<a href="#">CFW-090003TGZ</a>	<a href="#">CFDB120-298*</a>	120	298	12 X 5 X 4	<b>\$183</b>	V1
	2	<a href="#">CFW-090004TGZ</a>	<a href="#">CFDB120-298*</a>	120	298	12 X 5 X 4	<b>\$183</b>	V1
	3	<a href="#">CFW-090005TGZ</a>	<a href="#">CFDB100-448*</a>	100	448	12 X 7 X 5	<b>\$319</b>	V1
	5	<a href="#">CFW-090009TGZ</a>	<a href="#">CFDB47-746*</a>	47	746	12 X 7 X 5	<b>\$319</b>	V1
	7.5	<a href="#">CFW-090013TGZ</a>	<a href="#">CFDB47-1120*</a>	47	1,120	12 X 10 X 5	<b>\$481</b>	V1
	10	<a href="#">CFW-090016TGZ</a>	<a href="#">CFDB33-1492*</a>	33	1,492	12 X 13 X 5	<b>\$638</b>	V1
	15	<a href="#">CFW-090024TGZ</a>	<a href="#">CFDB22-2238</a>	22	2238	19 X 10 X 5	<b>\$944</b>	V1
	20	<a href="#">CFW-090030TGZ</a>	<a href="#">CFDB18-2984</a>	18	2984	19 X 10 X 5	<b>\$944</b>	V1
	25	<a href="#">CFW-090038TGDBZ</a>	<a href="#">CFDB10-3730</a>	10	3730	26.5 X 10 X 5	<b>\$1,293</b>	V1
	30	<a href="#">CFW-090045TGDBZ</a>	<a href="#">CFDB10-4476</a>	10	4476	26.5 X 10 X 5	<b>\$1,385</b>	V1
	40	<a href="#">CFW-090060TGDBZ</a>	<a href="#">CFDB6.8-5968</a>	6.8	5968	26.5 X 13 X 5	<b>\$1,708</b>	V1
	50	<a href="#">CFW-090070TGDBZ</a>	<a href="#">CFDB6.8-7460</a>	6.8	7460	26.5 X 16 X 5	<b>\$2,032</b>	V1
	60	<a href="#">CFW-090086TGDBZ</a>	<a href="#">CFDB4.7-8952</a>	4.7	8952	26.5 X 13 X 10	<b>\$2,595</b>	V1
	75	<a href="#">CFW-090105TGDBZ</a>	<a href="#">CFDB4.7-11190</a>	4.7	11190	26.5 X 13 X 10	<b>\$2,957</b>	V1
	100	<a href="#">CFW-090142TGDBZ</a>	<a href="#">CFDB3.3-14920</a>	3.3	14920	26.5 X 13 X 10	<b>\$3,557</b>	V1
	150	<a href="#">CFW-090180TGZ**</a>	<a href="#">CFDB4-22380</a>	4	22380	26.5 X 13 X 15	<b>\$5,644</b>	V1
	150	<a href="#">CFW-090211TGZ**</a>	<a href="#">CFDB2.5-29840</a>	2.5	29840	30 X 24 X 18	<b>\$6,706</b>	V1
	200	<a href="#">CFW-090240TGZ**</a>	<a href="#">CFDB2.5-29840</a>	2.5	29840	30 X 24 X 18	<b>\$6,706</b>	V1
	250	<a href="#">CFW-090312TGZ**</a>	<a href="#">CFDB2-44760</a>	2	44760	30 X 24 X 30	<b>\$9,516</b>	V1
	300	<a href="#">CFW-090361TGZ**</a>	<a href="#">CFDB2-44760</a>	2	44760	30 X 24 X 30	<b>\$9,516</b>	V1
350	<a href="#">CFW-090450TGZ**</a>	<a href="#">CFDB2-52220</a>	2	52220	30 X 24 X 37	<b>\$13,717</b>	V1	
400	<a href="#">CFW-090515TGZ**</a>	<a href="#">CFDB2-74600</a>	2	74600	30 X 24 X 38	<b>\$14,084</b>	V1	
500	<a href="#">CFW-090600TGZ**</a>	<a href="#">CFDB2-74600</a>	2	74600	30 X 24 X 38	<b>\$14,084</b>	V1	

Note: These are non-stocked items, consult WEG for availability.  
\*\*External DB Transistor Module

