

Bearing cap
 Color RAL 5009
 Painting plan 207A
 Mounting B34R(D)

1.5 HP 04 Poles 60Hz

Dimensions in inches

ECM	LOC	SUMMARY OF MODIFICATIONS	EXECUTED	CHECKED	RELEASED	DATE	VER
EXECUTED	PIRWBUSER	THREE PHASE W22 MOTOR - NEMA PREMIUM EFF					
CHECKED		FRAME 145TC IP55 TEFC					
RELEASED							
REL DT.	WMO	Jaragua do Sul	Product Engineering				

PREVIEW
 WDD



SHEET 1 / 1

**W22**

CC029A

® Inverter Duty Motor
Severe Duty

11610562

MADE IN MEXICO MODEL 00158ET3E145TC-W22



PH 3 | FR 145TC | HP(kw) 1.5(1.1) | Hz 60 | SF 1.25 | PF 0.79

V 230/460 | A 4.04/2.02 | RPM 1755 | INS. CL. F Δ T 80 K | IP55

NEMA NOM EFF 86.5 % | DES B | DUTY CONT. | AMB 40°C

ENCL TEFC | SFA 5.05/2.52 | USABLE @208V 4.36 A | SF 1.15 | SFA 5.01

1.5HP 1.1kW 50Hz 380V 2.42A 1440RPM SF1.25 EFF 84.1% (IE3) | CODE L



→6205-ZZ

→6204-ZZ

MOBIL POLYREX EM

ALT 1000 m.a.s.l. | 53 Lbs

For 60Hz: Class I, Div 2, Gr. A, B, C and D - T3

Class I, Zone 2, IIC - T3

Class II, Div 2, Gr. F and G - T5

For use on PWM, Gr. A, B, C, D, F and G

VT1000:1, CT20:1, 1.0SF, T4A

C US
Energy Verified3PT9
US LISTEDFOR SAFE AREA
MOD.TE1BFOXON