

MCS – MULTI CONNECTION SYSTEM

Accessories

Snap-on type strain relief housing; for female/male connectors with CAGE CLAMP® connection

for 734 Series 3.5 mm pin spacing Pin spacing: 3.81 mm for 231 and 721 Series Pin spacing: 5 mm Pin spacing: 5.08 mm for 231, 721 and 731 Series Pin spacing: 7.5 mm Pin spacing: 7.62 mm



Pole No.	Color	Item No.	PU	Color	Item No.	PU	Color	Item No.	PU	Color	Item No.	PU	Color	Item No.	PU	Color	Item No.	PU
2	○	734-602	50	●	734-632	50	○	232-602	25	●	232-632	25	○	232-662	25	●	232-682	25
3	○	734-603	25	●	734-633	25	○	232-603	25	●	232-633	25	○	232-663	25	●	232-683	25
4	○	734-604	25	●	734-634	25	○	232-604	25	●	232-634	25	○	232-664	25	●	232-684	25
5	○	734-605	25	●	734-635	25	○	232-605	25	●	232-635	25	○	232-665	25	●	232-685	25
6	○	734-606	25	●	734-636	25	○	232-606	25	●	232-636	25						
7	○	734-607	25				○	232-607	25	●	232-637	25	○	232-667	25	●	232-687	25
8	○	734-608	25	●	734-638	25	○	232-608	25	●	232-638	25						
9	○	734-609	25	●	734-639	25	○	232-609	25	●	232-639	25						
10	○	734-610	25	●	734-640	25	○	232-610	25	●	232-640	25	○	232-670	25			
11	○	734-611	25															
12	○	734-612	25	●	734-642	25	○	232-612	25	●	232-642	25						
16										●	232-646	25						

Note: Only factory gluing possible!

Accessories; item-specific

Description:	Item No.	Pack. Unit
Cable clamp; for strain relief; 4 to 6 poles	209-177	25
Cable clamp; for strain relief; 7 or more poles	209-174	25
Mounting screw; for cable clamp; 4 to 6 poles	209-176	50
Mounting screw; for cable clamp; 7 or more poles	209-173	50

Strain relief plate; push-in type; for female connectors



Pin spacing: 2.5 mm									Pin spacing: 3.5 / 3.81 mm								
Pole No.	Width	Color	Item No.	Color	Item No.	Color	Item No.	PU	Pole No.	Width	Color	Item No.	Color	Item No.	Color	Item No.	PU
2 ... 4	6 mm	○	734-127	●	734-327	●	734-227	25	2 ... 3	6 mm	○	734-127	●	734-327	●	734-227	25
5 ... 9	12.5 mm	○	734-128	●	734-328	●	734-228	25	4 ... 8	12.5 mm	○	734-128	●	734-328	●	734-228	25
10 ... 12	25 mm	○	734-129	●	734-329	●	734-229	25	9 ... 12	25 mm	○	734-129	●	734-329	●	734-229	25
									13 ... 16	35 mm	○	734-126	●	734-326	●	734-226	25
									17 ... max.	55 mm	○	734-426	●	734-430	●	734-428	25

Pin spacing: 5 / 5.08 mm									Pin spacing: 7.5 / 7.62 mm								
Pole No.	Width	Color	Item No.	Color	Item No.	Color	Item No.	PU	Pole No.	Width	Color	Item No.	Color	Item No.	Color	Item No.	PU
2	6 mm	○	734-127	●	734-327	●	734-227	25	2	6 mm	○	734-127	●	734-327	●	734-227	25
3 ... 4	12.5 mm	○	734-128	●	734-328	●	734-228	25	2 ... 3	12.5 mm	○	734-128	●	734-328	●	734-228	25
5 ... 7	25 mm	○	734-129	●	734-329	●	734-229	25	4 ... 6	25 mm	○	734-129	●	734-329	●	734-229	25
8 ... 11	35 mm	○	734-126	●	734-326	●	734-226	25	7 ... 9	35 mm	○	734-126	●	734-326	●	734-226	25
12 ... 16	55 mm	○	734-426	●	734-430	●	734-428	25	10 ... 12	55 mm	○	734-426	●	734-430	●	734-428	25
17 ... 24	75 mm	○	734-427	●	734-431	●	734-429	25	13 ... 16	75 mm	○	734-427	●	734-431	●	734-429	25

Strain relief plate; push-in type; for male/female connectors with Push-in CAGE CLAMP® connection

Strain relief plate; snap-in type; for male/female connectors with Push-in CAGE CLAMP® connection

Strain relief plate; with strain relief plate; snap-in type; for male/female connectors with Push-in CAGE CLAMP® connection



Pin spacing: 7.62 mm					Pin spacing: 10.16 mm									
Pole No.	Width	Color	Item No.	PU	Pole No.	Width	Color	Item No.	PU	Pole No.	Width	Color	Item No.	PU
2 ... 3	15 mm	○	831-503	25	2	20.2 mm	○	832-532	25	2	20.2 mm	●	832-542	25
4 ... 6	30 mm	○	831-505	25	3	30.4 mm	○	832-533	25	3	30.4 mm	●	832-543	25
7 ... 9	51 mm	○	831-506	25	4	40.6 mm	○	832-534	25	4	40.6 mm	●	832-544	25
5	50.8 mm	○	832-535	25	5	50.8 mm	○	832-535	25	5	50.8 mm	●	832-545	25

For additional strain relief plates (e.g., factory-assembled, for male and female connectors with CAGE CLAMP® and Push-in CAGE CLAMP® connections), see Full Line Catalog, Volume 2.