



Pluggable Tap-Off Module 870 Series

Technical Data	
0.25 ... 2.5 mm ²	22 ... 14 AWG
500 V/6 kV/3 ①	
I _N 18 A	
Module width: 5 mm / 0.197 inch	
 10 mm / 0.38 inch	



Technical Data	
0.25 ... 2.5 mm ²	22 ... 14 AWG
500 V/6 kV/3 ①	
I _N 10 A	
Module width: 5 mm / 0.197 inch	
 10 mm / 0.38 inch	



- ① 500 V = rated voltage
6 kV = rated impulse voltage
3 = pollution degree
(see Section 15)

Approvals and corresponding ratings,
visit www.wago.com

Pluggable tap-off module; with anti-reverse mating protection; snaps together; for 870 Series Rail-Mount Terminal Blocks with jumper slots in the current bar

Color	Item No.	Pack. Unit
○ gray	870-425	100 (25)

Pluggable tap-off module; snaps together; for 870 Series Rail-Mount Terminal Blocks with jumper slots in the current bar

Color	Item No.	Pack. Unit
○ gray	870-426	100 (25)

Spacer module; snaps together; bridges terminal blocks

○ gray	870-427	100 (25)
--------	---------	----------

Accessories; for pluggable tap-off modules

Appropriate marking systems: Mini-WSB/Mini-WSB Inline/WMB/WMB Inline

Strain relief plate; gray



35 mm wide	734-326	100 (25)
6 mm wide	734-327	100 (25)
12.5 mm wide	734-328	100 (25)
25 mm wide	734-329	100 (25)

Mini-WSB marking card; white; 10 strips with 10 markers/card; 5 mm wide markers

plain	248-501	5
-------	---------	---

WMB marking card; white; 10 strips with 10 markers/card; stretchable 5 ... 5.2 mm

plain	793-5501	5
-------	----------	---

WMB marking card; white; 10 strips with 10 markers/card; for 5 ... 17.5 mm terminal block width

plain	793-501	5
-------	---------	---