

# Modular Terminal Block; with Mounting Flange or Snap-In Mounting Foot 2.5 mm<sup>2</sup>; 261 Series

Technical Data	
0.08 ... 2.5 mm <sup>2</sup>	28 ... 14 AWG
500 V/6 kV/3 ①	300 V, 15 A ②
I <sub>N</sub> 24 A	300 V, 20 A ③
Terminal block width: 6 mm / 0.236 inch	
8 ... 9 mm / 0.31 ... 0.35 inch	

Technical Data	
0.08 ... 2.5 mm <sup>2</sup>	28 ... 14 AWG
500 V/6 kV/3 ①	300 V, 15 A ②
I <sub>N</sub> 24 A	300 V, 20 A ③
Terminal block width: 10 mm / 0.394 inch	
8 ... 9 mm / 0.31 ... 0.35 inch	

- ① 500 V = rated voltage  
6 kV = rated impulse voltage  
3 = pollution degree  
(see Section 14)
  - ② Terminal blocks with a blue insulated housing are suitable for Ex i applications.
- See application notes for:  
Test plug module, page 474
- Approvals and corresponding ratings,  
visit [www.wago.com](http://www.wago.com)



### Accessories; 261 Series

Marking accessories, see Section 13

#### Test plug; with 500 mm cable; 2 mm Ø; max. 42 V

red	210-136	50
-----	---------	----



#### Test plug; with 500 mm cable; 2 mm Ø; max. 42 V

yellow	210-137	50
--------	---------	----



#### Aluminum mounting rail; 1000 mm long; 18 mm wide; 7 mm high

	210-154	1
--	---------	---



#### Plastic end stop; with WSB marker slot; for aluminum rail (210-154); 6 mm wide

	209-122	25
--	---------	----



#### Mounting foot; for DIN-35 rail; snaps onto terminal blocks with snap-in mounting foot; 6.4 mm wide

gray	209-120	25
------	---------	----



#### Mounting screw; for mounting foot (209-120)

	209-119	500 (50)
--	---------	----------

#### Mounting foot with screw; for DIN-35 rail; can be screwed on terminal blocks with mounting flange; 6.4 mm wide

gray	209-123	25
------	---------	----



#### Mounting adapter; for DIN-35 rail; can be used as end plate; 6.5 mm wide

gray	209-137	25
------	---------	----



#### Operating tool with a partially insulated shaft; Type 2; (3.5 x 0.5) mm blade

	210-720	1
--	---------	---



2-conductor terminal block; with mounting flange; for screw or similar mounting types; 3.2 mm mounting hole diameter; with mounting foot (209-123) also for DIN-35 rail

Color	Item No.	Pack. Unit
gray	261-301	200 (50)
light gray	261-303	200 (50)
blue	261-304 ②	200 (50)
orange	261-306	200 (50)
green-yellow	261-307	200 (50)

4-conductor terminal block; with mounting flange; for screw or similar mounting types; 3.2 mm mounting hole diameter; with mounting foot (209-123) also for DIN-35 rail

Color	Item No.	Pack. Unit
gray	261-331	200 (50)
light gray	261-333	200 (50)
blue	261-334 ②	200 (50)
orange	261-336	200 (50)
green-yellow	261-337	200 (50)

2-conductor terminal block; with snap-in mounting foot; for 0.6 ... 1.2 mm plate thickness; 3.5 mm mounting hole diameter; also for aluminum rail (210-154) or with mounting foot (209-120) for DIN-35 rail

Color	Item No.	Pack. Unit
gray	261-311	200 (50)
light gray	261-313	200 (50)
blue	261-314 ②	200 (50)
orange	261-316	200 (50)
green-yellow	261-317	200 (50)

4-conductor terminal block; with snap-in mounting foot; for 0.6 ... 1.2 mm plate thickness; 3.5 mm mounting hole diameter; also for aluminum rail (210-154) or with mounting foot (209-120) for DIN-35 rail

Color	Item No.	Pack. Unit
gray	261-341	200 (50)
light gray	261-343	200 (50)
blue	261-344 ②	200 (50)
orange	261-346	200 (50)
green-yellow	261-347	200 (50)

Space-saving 2-conductor end terminal block; without protruding snap-in mounting foot; for terminal strips with snap-in mounting feet

Color	Item No.	Pack. Unit
gray	261-321	200 (50)
light gray	261-323	200 (50)
blue	261-324 ②	200 (50)
orange	261-326	200 (50)
green-yellow	261-327	200 (50)

Space-saving 4-conductor end terminal block; without protruding snap-in mounting foot; for terminal strips with snap-in mounting feet

Color	Item No.	Pack. Unit
gray	261-351	200 (50)
light gray	261-353	200 (50)
blue	261-354 ②	200 (50)
orange	261-356	200 (50)
green-yellow	261-357	200 (50)

### Accessories; item-specific

#### Test plug module; snaps together; 6 mm wide

gray	249-136	100 (25)
------	---------	----------



#### Test plug module; with locking latches; snaps together; 6 mm wide

gray	261-404	100 (25)
------	---------	----------



### Accessories; item-specific

#### Test plug module; snaps together; 10 mm wide

gray	249-139	100 (25)
------	---------	----------



#### Test plug module; with locking latches; snaps together; 10 mm wide

gray	261-405	100 (25)
------	---------	----------



### Accessories; 261 Series

Marking accessories, see Section 13

#### End plate; with mounting flange

gray	261-361	300 (50)
------	---------	----------



#### Comb-style jumper bar; insulated; reduces maximum conductor size to 1.5 mm<sup>2</sup>; I<sub>N</sub> 16 A; gray

2-way	261-402	25
-------	---------	----



#### End plate; with snap-in mounting foot

gray	261-371	300 (50)
------	---------	----------



#### Operating tool; insulated; for comb-style jumper bar

2-way	209-132	1
-------	---------	---

