


Uninsulated Ferrule



Ferrule; uninsulated; electro-tin-plated; electrolytic copper; gastight crimped; per DIN 46288 (Part 4/09.09)						
Conductor Cross Section	Strip Length	L	D	D 2	Item No.	Pack. Unit
25 mm² / 4 AWG	25 mm / 0.98 inch	25	9,5	7,3	216-413	50
35 mm² / 2 AWG	25 mm / 0.98 inch	25	11	8,3	216-414	50
35 mm² / 2 AWG	30 mm / 1.18 inch	30	11	8,3	216-424	50
50 mm² / 1 AWG	30 mm / 1.18 inch	30	13	10,3	216-425	50
50 mm² / 1 AWG	35 mm / 1.38 inch	35	13	10,3	216-435	50