



Item description

Features:

- Easy mounting on 2857 Series devices
- Automatic module detection
- Capacitive user interface with slider function
- Intuitive menu navigation
- Color backlight for status indication
- Device configuration and process value visualization
- Easy copying of device configuration

Data

Technical Data

Operating data

Operating voltage	DC 3.3 V
Current consumption	≤ 60 mA

Geometrical Data

Width	22 mm / 0.866 inch
Height	13 mm / 0.512 inch
Depth	59 mm / 2.323 inch

Mechanical data

Type of mounting	Pluggable module
------------------	------------------

Material Data

Fire load	0 MJ
Weight	24.268 g

Environmental Requirements

Surrounding air (operating) temperature	-20 ... 70 °C
Surrounding air (storage) temperature	-30 ... 80 °C
Relative humidity	10 ... 95 % (no condensation)
Max. operating altitude	2000 m

Standards and specifications

Conformity marking	CE
EMC immunity to interference	EN 61000-6-2; EN 61326-2-3; EN 50121-3-2
EMC emission of interference	EN 61000-6-4; EN 61326-2-3; EN 50121-3-2
Standards/specifications	EN 61373

Commercial data

Product Group	6 (Interface Electronics)
Country of origin	DE
GTIN	4050821677017
Customs Tariff No.	90303380900

Downloads

Documentation

Bid Text

2857-900 Konfigurationsdisplay	Mar 9, 2016	doc 25.1 kB	Download
-----------------------------------	-------------	----------------	----------

Instruction Leaflet

Configuration Display		pdf 1.3 MB	Download
-----------------------	--	---------------	----------

Additional Information

Disposal; Electrical and electronic equipment, Packaging	V 1.0.0	pdf 265.8 kB	Download
--	---------	-----------------	----------



Subject to changes.
