



RoHS
Compliant

BOMcheck.net

Data

Connection data

Solid conductor	0.08 ... 2.5 mm ² / 28 ... 14 AWG
Strip length	5 ... 6 mm / 0.2 ... 0.24 inch

Geometrical Data

Width	17.5 mm / 0.689 inch
Height from upper-edge of DIN-35 rail	27.5 mm / 1.083 inch
Depth	35 mm / 1.378 inch

Material Data

Fire load	0 MJ
Weight	11.7 g

Environmental Requirements



Protection class	IP20
------------------	------

Commercial data

Product Group	6 (Interface Electronics)
Country of origin	DE
GTIN	4045454526382
Customs Tariff No.	85369010000

Approvals / Certificates

Ex-Approvals

Logo	Approval	Additional Approval Text	Certificate name
	ATEX TUEV Nord Cert GmbH	EN 60079-0	TÜV 07 ATEX 554086 X en.
	TUEV Nord TUEV Nord Cert GmbH	IEC 60079-0	IECEX TUN 09.0001 X

Downloads

Documentation

Additional Information

Disposal; Electrical and electronic equipment, Packaging	V 1.0.0	pdf 265.8 kB	Download
--	---------	-----------------	----------

Subject to changes.