

Data

Electrical data

Ratings per IEC/EN 60664-1

Rated voltage (III / 3)	500 V
Rated impulse voltage (III / 3)	4 kV
Rated current	10 A

Connection data

Connection technology	CAGE CLAMP®
Solid conductor	0.08 ... 4 mm ² / 28 ... 12 AWG
Fine-stranded conductor	0.08 ... 4 mm ² / 28 ... 12 AWG
Strip length	9 mm / 0.35 inch
Type of wiring	Front-entry wiring

Geometrical Data

Width	10.4 mm / 0.409 inch
Height	18.1 mm / 0.713 inch
Depth	20 mm / 0.787 inch

Material Data





Color	gray
Fire load	0.073 MJ
Weight	3.95 g

Commercial data

Product Group	12 (Matrix Patch Board)
Country of origin	DE
GTIN	4017332289306
Customs Tariff No.	85369010000

Approvals / Certificates

Country specific Approvals

Logo	Approval	Additional Approval Text	Certificate name
	CCA DEKRA Certification B.V.	EN 60998	NTR NL-7623
	CSA DEKRA Certification B.V.	C22.2	1101143
	CSA DEKRA Certification B.V.	C22.2 No. 158	1101143
	KEMA/KEUR DEKRA Certification B.V.	EN 60998	71-100850

Downloads

Documentation

Bid Text

726-904



doc
23.6 kB

[Download](#)

Subject to changes.
