

Data sheet | Item number: 756-1250/1023-030

ETHERNET cable; Cat. 6A; RJ45, axial locking; RJ45, axial locking; Length: 3 m



www.wago.com/756-1250_1023-030



i Picture differs from the item.

Color: ■

RJ-45-Stecker TIA/EIA 568B

1 ■	weiß/orange	■ 1
2 ■	orange	■ 2
3 ■	weiß/grün	■ 3
4 ■	blau	■ 4
5 ■	weiß/blau	■ 5
6 ■	grün	■ 6
7 ■	weiß/braun	■ 7
8 ■	braun	■ 8

Schirm

Subject to changes. Please also observe the further product documentation!

WAGO Corporation
Germantown, WI 53022
Phone: 1-800-DIN-RAIL (346-7245) | Fax: (262) 255-6222
Email: info.us@wago.com | Web: www.wago.us

Do you have any questions about our products?
We are always happy to take your call at (262) 255-6222 or 1 800-DIN-RAIL.



Item description

Short description:

- Halogen-free TPE
- Cat. 6A S/FTP
- Highly flexible
- 50 µinch gold plating in the contact area
- Mechanically/Electrically tested
- 4C Channel Link Test
- Wrap-around label for clear traceability
- Easy plug unlocking

Data

Technical data

Baud rate	10000Mbit/s
Operating voltage	80 V
Rated surge voltage	500 V (wire/wire/screen rms 50 Hz 1 min)
Insulation resistance	$\geq 1 \times 10^8 \Omega \times \text{km}$
Conductor resistance	$< 142 \Omega/\text{km}$
Cable length	3 m

Connection data

Contact type	Stecker RJ-45; Stecker RJ-45
Connection type	Stecker RJ-45 - Stecker RJ-45

Mechanical data

Conductor design	Cu-Litze blank (7 x 0,16 mm)
Conductor insulation	PE halogenfrei
Mating cycles (max.)	1,200
Sheathed cable diameter	6 ... 6.4 mm
Cable connection direction to mating direction	0°

Material data

Color	green
Contact material	CuZn

Subject to changes. Please also observe the further product documentation!

WAGO Corporation
 Germantown, WI 53022
 Phone: 1-800-DIN-RAIL (346-7245) | Fax: (262) 255-6222
 Email: info.us@wago.com | Web: www.wago.us

Do you have any questions about our products?
 We are always happy to take your call at (262) 255-6222 or 1 800-DIN-RAIL.



Contact plating	CuNi/Au, 50 µinch Goldauflage
Sheathed cable color	Grün, RAL 6018
Halogen-free	Yes
Weight	120.7 g
Sheath material	LSOH-TPE, halogenfrei nach IEC 60754-2, flammwidrig nach IEC 60332-1, raucharm nach IEC 61034
Shield	Alukaschierte, überlappende Folie und verzinnertes Cu-Geflecht (PiMF)

Environmental requirements

Surrounding air (operating) temperature (dynamic)	-40 ... +80 °C
Surrounding air (operating) temperature (static)	-40 ... +80 °C
Bending radius	min. 10 mm
Bending cycles	8,500 Mio.

Commercial data

Packaging type	bag
Country of origin	CN
GTIN	4055143763035
Customs tariff number	85444290900

Commercial data

Packaging type	bag
Customs tariff number	8544429090

Technical data

Connection type	RJ-45 plug - RJ-45 plug
Baud rate	10000 Mbit/s
Operating current	0.72 A
Rated surge voltage	500 V (wire/wire/shield rms 50 Hz 1 min)
Conductor resistance	< 142 Ω/km

Environmental requirements

Surrounding air (operating) temperature (dynamic)	-40 ... +80 °C
Surrounding air (operating) temperature (static)	-40 ... +80 °C

Subject to changes. Please also observe the further product documentation!

WAGO Corporation
 Germantown, WI 53022
 Phone: 1-800-DIN-RAIL (346-7245) | Fax: (262) 255-6222
 Email: info.us@wago.com | Web: www.wago.us

Do you have any questions about our products?
 We are always happy to take your call at (262) 255-6222 or 1 800-DIN-RAIL.



Mechanical data

Bending radius	10 mm (min.)
Sheathed cable color	green (RAL 6018)
Sheathed cable diameter	6 ... 6.4 mm
Sheath material	LSOH TPE, halogen-free per IEC 60754-2, flame-retardant per IEC 60332-1, low-smoke per IEC 61034
Shield	Overlapped aluminum-laminated foil and tinned copper braid (PiMF)
Conductor design	Bare copper wire (7 x 0.16 mm)
Conductor insulation	PE (halogen-free)
Contact plating	CuNi/Au; 50 µinch gold plating
Weight	120.7 g
Color	green

Downloads

Documentation

Bid Text

756-1250/1023-030 docx - Datei	Jan 8, 2019	docx 17.3 kB	Download
756-1250/1023-030 X81 - Datei	Feb 19, 2019	xml 4.6 kB	Download

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 756-1250/1023-030 ETHERNET cable; Cat. 6A; RJ45, axial locking; RJ45, axial locking; Length: 3 m	URL	Download
--	-----	----------

Installation Notes

Subject to changes. Please also observe the further product documentation!

WAGO Corporation
Germantown, WI 53022
Phone: 1-800-DIN-RAIL (346-7245) | Fax: (262) 255-6222
Email: info.us@wago.com | Web: www.wago.us

Do you have any questions about our products?
We are always happy to take your call at (262) 255-6222 or 1 800-DIN-RAIL.