



Data sheet | Item number: 756-3501/050-075

Power cable; M12L socket; straight; 5-pole; Length: 7.5 m

www.wago.com/756-3501_050-075



Pin 1 ... 4; FG: 1.5 mm²

1	⌋	brown	1
2	⌋	white	2
3	⌋	blue	3
4	⌋	black	4
FG	⌋	gray	FG

Subject to changes. Please also observe the further product documentation!

WAGO Corporation
Germantown, WI 53022
Phone: 1-800-DIN-RAIL (346-7245) | Fax: (262) 255-6222
Email: info.us@wago.com | Web: www.wago.us

Do you have any questions about our products?
We are always happy to take your call at (262) 255-6222 or 1 800-DIN-RAIL.



Item description

Short description:

These power cables are an accessory for the WAGO I/O System Field.

Use them as flexible, flame-retardant and halogen-free supply cables for industrial mechanical engineering applications – particularly those with high requirements, e.g., for use in cable chains (drag chains) and moving machine parts.

- Strong resistance to microbes and hydrolysis
- Good to very good weather resistance (UV and ozone)
- High resistance against welding sparks
- Excellent chemical and oil resistance
- Silicon- and PVC-free
- Free from paint-wetting impairment substances
- Flexible at low temperatures

Data

Technical data

Connection type	M12 socket - Free end
Pole No.	5
Cable connection direction to mating direction	0°
Connector interface coding (cable/adapter) 1 1	L-coded
Cable length	7.5 m
Operating voltage	63 VDC per IEC 60664-1
Operating current	16 A
Rated surge voltage	1.5 kV per IEC 61076-2-111
Contact resistance	5 mΩ
Insulation resistance	1000 MΩ
Conductor resistance	≤13,7 Ω/km

Mechanical data

Bending radius	Fixed: >4xØ; Flexible: >7.5xØ
Bending cycles	10 Mio.
Drag chain suitability	Yes
Sheathed cable color	Gray (~ RAL 7040)
Sheathed cable diameter	9.6 ... 10.2 mm
Type code	LiF9YH-11Y-0B 5x1.5mm ²
Conductor design	Bare copper wire (84 x 0.15 mm)
Conductor insulation	PP9Y (halogen-free)

Subject to changes. Please also observe the further product documentation!

WAGO Corporation
 Germantown, WI 53022
 Phone: 1-800-DIN-RAIL (346-7245) | Fax: (262) 255-6222
 Email: info.us@wago.com | Web: www.wago.us

Do you have any questions about our products?
 We are always happy to take your call at (262) 255-6222 or 1 800-DIN-RAIL.



Housing material	TPU/TPU, black (~ RAL 9005)
Tightening torque	1 Nm
Weight	1091 g

Environmental requirements

Surrounding air temperature (operation)	-40 ... 90 °C (UL max. +80 °C)
Surrounding air (operating) temperature (dynamic)	-30 ... +90 °C
Surrounding air (operating) temperature (static)	-40 ... +90 °C
Protection type	IP68
Pollution degree (5)	3 per IEC 60664-1

Commercial data

Packaging type	not packed
Country of origin	DE
GTIN	4055143974462
Customs tariff number	8544429090

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 756-3501/050-075 Power cable; M12L socket; straight; 5-pole; Length: 7.5 m	URL	Download
--	---------------------	--------------------------

Installation Notes

Subject to changes. Please also observe the further product documentation!

WAGO Corporation
Germantown, WI 53022
Phone: 1-800-DIN-RAIL (346-7245) | Fax: (262) 255-6222
Email: info.us@wago.com | Web: www.wago.us

Do you have any questions about our products?
We are always happy to take your call at (262) 255-6222 or 1 800-DIN-RAIL.