


Data sheet | Item number: 756-5201/030-010



Sensor/actuator cable; fitted on both ends; 3-pole; M8 socket, straight; M8 plug, straight; 1 m



756-5201/030-010



RoHS  Compliant [BOMcheck.net](https://www.bomcheck.net)



Item description

Short description:

- PUR, halogen-free
- Suitable for drag chains
- Good resistance to microbes, hydrolysis, oil, chemicals and UV radiation.
- Good chemical resistance.
- Cable used: UL listed

**Data****Technical Data**

Connection type	M8 socket - M8 plug
No. of poles	3
Leitungsanschlussrichtung zur Steckrichtung	0°
Leitungsanschlussrichtung zur Steckrichtung (2)	0°
Cable length	1 m
Operating voltage	AC/DC 60 V
Operating current	4 A
Rated surge voltage	1,5 kV

**Mechanical data**

Bending cycles	2 Mio.
Schleppkettentauglichkeit	yes
Color of sheathed cable	black
Durchmesser der Mantelleitung	3.9 ... 4.3 mm
Sheath material	Polyurethane (OPUR), halogen-free per DIN VDE 0472 Part 815, flame resistant per IEC 332-2, self-extinguishing
Halogen-free	Yes
Housing material	Polyurethan (PUR)
Contact material	CuSn
Contact plating	CuNi/Au
Tightening torque	0.6 Nm
Weight	40 g

**Environmental Requirements**

Umgebungstemperatur (Betrieb) bewegt	-25 ... +90 °C
Umgebungstemperatur (Betrieb) ruhend	-50 ... +90 °C
Protection class	IP67
Degree of pollution (5)	3 acc. to VDE 0110

**Commercial data**

Country of origin	DE
GTIN	4044918974547
Customs Tariff No.	85444290900



Downloads

**Documentation**

System Description

IP67 Cables and Pluggable Connectors

pdf  
293.9 kB

Download

---

Subject to changes.

---