





RoHS 
Compliant

[BOMcheck.net](https://www.bomcheck.net)





Conductor size

Ø 6 ... 8 mm / 0.14 - 0.5 mm²

Data

Technical Data

Connection type	M12 plug
No. of poles	5
Anschlusspunkt geschirmt	yes
Leistungsanschlussrichtung zur Steckrichtung	90°
Steckgesichtskodierung Leitung/Adapter 1 1	A coded

Connection data

Connection type (1)	Federtechnik
---------------------	--------------

Mechanical data

Connectable sheathed cable diameter	6 ... 8 mm
Weight	66.8 g

Environmental Requirements

Protection class	IP67
------------------	------

Commercial data

Country of origin	DE
GTIN	4045454686413
Customs Tariff No.	85369010000



Downloads

Documentation

System Description

IP67 Cables and Pluggable Connectors	pdf 293.9 kB	Download
767 Series, SPEEDWAY accessories, data sheet	pdf 1.0 MB	Download

Subject to changes.