



Data

Electrical data

Note on Contact Resistance

approx. 1m Ω contact resistance

approx. 0.25m Ω contact transition plug/socket

Mechanical data

Protection class

IP20

Note on protection class

Only in mated condition with strain relief housing (These compact connectors are not designed for use in open, easily accessible areas.)

Plug connection

Mismating protection

Yes

Locking of plug-in connection

locking lever

Material Data

Insulating material

Polyamide 66 (PA 66)

Flammability class per UL94

V0

Contact material

Copper or copper alloy, surface-treated

Weight

2.4 g



Environmental Requirements

Surrounding air (operating) temperature	-35 ... 85 °C
Processing temperature	-5 ... +40 °C
Continuous operating temperature	-35 ... +85 °C
Note on Continuous Service Temperature	Insulating parts for temperatures \leq 105 °C

Commercial data

Product Group	20 (WINSTA)
Country of origin	DE
GTIN	4045454662684
Customs Tariff No.	74099000000

Downloads

Documentation

Bid Text

770-523

doc
22.0 kB

[Download](#)

Subject to changes.