



Data sheet | Item number: 811-317

2-conductor fuse terminal block; for cylindrical fuses 10 x 38 mm; 13/32 x 11/2; 1-pole; with blown fuse indication; for DIN-rail 35 x 15 and 35 x 7.5; 16 mm²; CAGE CLAMP®



811-317



RoHS
Compliant ✓

BOMcheck.net

Color: ■

Item description

Safety information 1:

Electrical ratings are given by the fuse and blown fuse indication.

Safety information 2:

Temperature range handling from -35°C ... +85°C

Data

Electrical data

Voltage type (1)	DC
------------------	----

Ratings per IEC/EN 60664-1

Rated voltage (III / 3)	1000 V
Rated current	32 A

Connection data

Connection technology	CAGE CLAMP®
Actuation type	Operating tool
Connectable conductor materials	Copper
Solid conductor	2.5 ... 16 mm ² / 14 ... 6 AWG
Fine-stranded conductor	2.5 ... 16 mm ² / 16 ... 6 AWG

Strip length	12 ... 13 mm / 0.47 ... 0.51 inch
No. of poles	1
Total number of connection points	2
Total number of potentials	1
Number of levels	1
Type of wiring	Front-entry wiring

Geometrical Data

Width	17.5 mm / 0.689 inch
Height from upper-edge of DIN-35 rail	55 mm / 2.165 inch
Depth	105 mm / 4.134 inch

Mechanical data

Design	horizontal
Type of mounting	DIN-35 rail

Material Data






Color	light gray
Insulating material	Polyamide 66 (PA 66)
Weight	200 g

















Commercial data

GTIN	4050821499251
------	---------------

Compatible products

Jumper

	Item no.: 811-472 Push-in type jumper bar; insulated; 2-way; Nominal current 63 A	811-472
	Item no.: 811-473 Push-in type jumper bar; insulated; 3-way; Nominal current 63 A	811-473
	Item no.: 811-474 Push-in type jumper bar; insulated; 4-way; Nominal current 63 A	811-474
	Item no.: 811-475 Push-in type jumper bar; insulated; 5-way; Nominal current 63 A	811-475
	Item no.: 811-476 Push-in type jumper bar; insulated; 6-way; Nominal current 63 A	811-476

	Item no.: 811-477 Push-in type jumper bar; insulated; 7-way; Nominal current 63 A	811-477
	Item no.: 811-478 Push-in type jumper bar; insulated; 8-way; Nominal current 63 A	811-478
	Item no.: 811-479 Push-in type jumper bar; insulated; 9-way; Nominal current 63 A	811-479
	Item no.: 811-480 Push-in type jumper bar; insulated; 10-way; Nominal current 63 A	811-480
	Item no.: 811-481 Push-in type jumper bar; insulated; 11-way; Nominal current 63 A	811-481
	Item no.: 811-482 Push-in type jumper bar; insulated; 12-way; Nominal current 63 A	811-482
Marking accessories		
	Item no.: 285-442 Adaptor	285-442
	Item no.: 793-501 WMB marking card; as card; not stretchable; plain; snap-on type	793-501
	Item no.: 793-501/000-002 WMB marking card; as card; not stretchable; plain; snap-on type	793-501 /000-002
	Item no.: 793-501/000-005 WMB marking card; as card; not stretchable; plain; snap-on type	793-501 /000-005
	Item no.: 793-501/000-006 WMB marking card; as card; not stretchable; plain; snap-on type	793-501 /000-006
	Item no.: 793-501/000-007 WMB marking card; as card; not stretchable; plain; snap-on type	793-501 /000-007
	Item no.: 793-501/000-012 WMB marking card; as card; not stretchable; plain; snap-on type	793-501 /000-012
	Item no.: 793-501/000-017 WMB marking card; as card; not stretchable; plain; snap-on type	793-501 /000-017
	Item no.: 793-501/000-023 WMB marking card; as card; not stretchable; plain; snap-on type	793-501 /000-023
	Item no.: 793-501/000-024 WMB marking card; as card; not stretchable; plain; snap-on type	793-501 /000-024
	Item no.: 793-5501 WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on	793-5501



type

**Item no.: 793-5501/000-002**

WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type

/000-002

793-5501

**Item no.: 793-5501/000-005**

WMB marking card; as card; stretchable 5 - 5.2 mm; plain; snap-on type

/000-005

793-5501

**Item no.: 793-5501/000-006**

WMB marking card; as card; stretchable 5 - 5.2 mm; plain; snap-on type

/000-006

793-5501

**Item no.: 793-5501/000-007**

WMB marking card; as card; stretchable 5 - 5.2 mm; plain; snap-on type

/000-007

793-5501

**Item no.: 793-5501/000-012**

WMB marking card; as card; stretchable 5 - 5.2 mm; plain; snap-on type

/000-012

793-5501

**Item no.: 793-5501/000-014**

WMB marking card; as card; stretchable 5 - 5.2 mm; plain; snap-on type

/000-014

793-5501

**Item no.: 793-5501/000-017**

WMB marking card; as card; stretchable 5 - 5.2 mm; plain; snap-on type

/000-017

793-5501

**Item no.: 793-5501/000-023**

WMB marking card; as card; stretchable 5 - 5.2 mm; plain; snap-on type

/000-023

793-5501

**Item no.: 793-5501/000-024**

WMB marking card; as card; stretchable 5 - 5.2 mm; plain; snap-on type

/000-024

793-5501

Supply module**Item no.: 811-471**

Supply module

811-471

assembling**Item no.: 811-612**

Coupling kit; for 12 poles

811-612

Downloads**Documentation****Bid Text**

811-317

doc
27.6 kB

Download

Additional Information



pdf
2.1 MB

Download

Subject to changes.
