



Data sheet | Item number: 811-420

2-conductor fuse terminal block; for class CC fuses; 2-pole; without blown fuse indication; for DIN-rail 35 x 15 and 35 x 7.5; 16 mm²; CAGE CLAMP®



811-420



Item description

Safety information 1:

Electrical ratings are given by the fuse.

Safety information 2:

Temperature range handling from -35°C ... +85°C

Data

Electrical data

Ratings per IEC/EN 60664-1

Rated current	32 A
---------------	------

Connection data

Connection technology	CAGE CLAMP®
Actuation type	Operating tool
Connectable conductor materials	Copper
Solid conductor	2.5 ... 16 mm ² / 14 ... 6 AWG
Fine-stranded conductor	2.5 ... 16 mm ² / 16 ... 6 AWG
Strip length	12 ... 13 mm / 0.47 ... 0.51 inch
No. of poles	2

Total number of connection points	4
Total number of potentials	2
Number of levels	1
Type of wiring	Front-entry wiring

Geometrical Data

Width	35 mm / 1.378 inch
Height from upper-edge of DIN-35 rail	55 mm / 2.165 inch
Depth	105 mm / 4.134 inch

Mechanical data

Design	horizontal
Type of mounting	DIN-35 rail

Material Data

Color	light gray
Insulating material	Polyamide 66 (PA 66)
Weight	1.111 g

Commercial data

Product Group	1 (Rail Mounted Terminal Blocks)
GTIN	4050821508175


Compatible products


assembling


	Item no.: 811-612 Coupling kit; for 12 poles	811-612
--	---	---------















Marking accessories

	Item no.: 285-442 Adaptor	285-442
--	------------------------------	---------

	Item no.: 793-501 WMB marking card; as card; not stretchable; plain; snap-on type	793-501
--	--	---------

	Item no.: 793-501/000-002 WMB marking card; as card; not stretchable; plain; snap-on type	793-501 /000-002
--	--	---------------------

	Item no.: 793-501/000-005 WMB marking card; as card; not stretchable; plain; snap-on type	793-501 /000-005
--	--	---------------------

	Item no.: 793-501/000-006 WMB marking card; as card; not stretchable; plain; snap-on type	/000-006	793-501
	Item no.: 793-501/000-007 WMB marking card; as card; not stretchable; plain; snap-on type	/000-007	793-501
	Item no.: 793-501/000-012 WMB marking card; as card; not stretchable; plain; snap-on type	/000-012	793-501
	Item no.: 793-501/000-017 WMB marking card; as card; not stretchable; plain; snap-on type	/000-017	793-501
	Item no.: 793-501/000-023 WMB marking card; as card; not stretchable; plain; snap-on type	/000-023	793-501
	Item no.: 793-501/000-024 WMB marking card; as card; not stretchable; plain; snap-on type	/000-024	793-501
	Item no.: 793-5501 WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type		793-5501
	Item no.: 793-5501/000-002 WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type	/000-002	793-5501
	Item no.: 793-5501/000-005 WMB marking card; as card; stretchable 5 - 5.2 mm; plain; snap-on type	/000-005	793-5501
	Item no.: 793-5501/000-006 WMB marking card; as card; stretchable 5 - 5.2 mm; plain; snap-on type	/000-006	793-5501
	Item no.: 793-5501/000-007 WMB marking card; as card; stretchable 5 - 5.2 mm; plain; snap-on type	/000-007	793-5501
	Item no.: 793-5501/000-012 WMB marking card; as card; stretchable 5 - 5.2 mm; plain; snap-on type	/000-012	793-5501
	Item no.: 793-5501/000-014 WMB marking card; as card; stretchable 5 - 5.2 mm; plain; snap-on type	/000-014	793-5501
	Item no.: 793-5501/000-017 WMB marking card; as card; stretchable 5 - 5.2 mm; plain; snap-on type	/000-017	793-5501



Item no.: 793-5501/000-023
WMB marking card; as card; stretchable 5 - 5.2 mm; plain; snap-on type

793-5501
/000-023



Item no.: 793-5501/000-024
WMB marking card; as card; stretchable 5 - 5.2 mm; plain; snap-on type

793-5501
/000-024

Supply module



Item no.: 811-471
Supply module

811-471

Jumper



Item no.: 811-472
Push-in type jumper bar; insulated; 2-way; Nominal current 63 A

811-472



Item no.: 811-473
Push-in type jumper bar; insulated; 3-way; Nominal current 63 A

811-473



Item no.: 811-474
Push-in type jumper bar; insulated; 4-way; Nominal current 63 A

811-474



Item no.: 811-475
Push-in type jumper bar; insulated; 5-way; Nominal current 63 A

811-475



Item no.: 811-476
Push-in type jumper bar; insulated; 6-way; Nominal current 63 A

811-476



Item no.: 811-477
Push-in type jumper bar; insulated; 7-way; Nominal current 63 A

811-477



Item no.: 811-478
Push-in type jumper bar; insulated; 8-way; Nominal current 63 A

811-478



Item no.: 811-479
Push-in type jumper bar; insulated; 9-way; Nominal current 63 A

811-479



Item no.: 811-480
Push-in type jumper bar; insulated; 10-way; Nominal current 63 A

811-480



Item no.: 811-481
Push-in type jumper bar; insulated; 11-way; Nominal current 63 A

811-481



Item no.: 811-482
Push-in type jumper bar; insulated; 12-way; Nominal current 63 A

811-482

Downloads

Documentation

Bid Text

811-420	doc 25.6 kB	Download
---------	----------------	----------

Additional Information

pdf	Download
-----	----------



Subject to changes.
