



Color:  silver-colored

Similar to illustration

Technical data

Suitable	without button frame
Marking method	Thermal transfer
Marking	plain
Delivery form	Roll
Delivery form configuration	300 markers/reel; 1 line
Printing device	Smart Printer (thermal transfer printer)

Physical data

Height	22 mm
Width	22 mm
Depth	0.09 mm
Marking surface	22 x 22 mm

Mechanical Data

Mounting type	Sticking
Smear resistance	in conjunction with 258-5005 Ink Ribbon

Material Data

Color	silver-colored
Material	Polyester
UV resistance	EN 60068-2-5:2010 Procedure B
Adhesive information	Acrylic; permanent; foamed
Halogen-free	Yes
Weight	92 g
Fire load	0 MJ

Environmental requirements

Surrounding air temperature (storage)	≥+22 °C
Ambient temperature (operation)	-30 ... +130 °C
Relative humidity	40 ... 50 %

Commercial data

eCl@ss 10.0	27-40-06-29
eCl@ss 9.0	27-40-06-29
ETIM 8.0	EC001288
ETIM 7.0	EC001288
PU (SPU)	1 pcs
Packaging type	Box
Country of origin	DE
GTIN	4055143426442
Customs tariff number	39191080888