

LED machine luminaire

#112560001-00003166



FLAT LED - MYEL 6 S

lampping
work equipment
voltage
protection rating
class of protection


technology
usage
luminaire body
lens cover

weight (net)
cord length
mounting


6 x 2W LED
without
10-40V DC
IP67
III

switchable
without switch
anodized aluminum
borosilicate glass

approx. 1.3lb (.6kg)
approx. 10ft (3m) with 2 conductor stranded wire
screws



Emin: 49 lx
Em: 347 lx
Emax: 869 lx



measuring conditions: d=100cm

