



fitted with

work equipment
connected load
power consumption
system of protection
class of protection
technology
usage
luminaire body
material
lamp cover
weight (net)
mains supply

design
fastening
dimension
special features

48 x LED
daylight white, 5600-6000 K
Color Rendering Index (CRI)=80
without
22-26 V; DC
approx. 16W
IP 68 - 1m/ IPX9K; DIN 40050-9
III
switchable
without switch

anodized aluminum
glass screen
approx. 5.1 lbs. [2.3 kg]
built-in M12 plug

mounted version
mounting rail, tap hole 2xM6
A= 16.5" [420mm]
light forming, connection on the rear side




M12

illuminance

measuring conditions: d=100cm

Em: 341 lx
Emax: 454 lx
Emin: 218 lx



luminous intensity

