



fitted with

work equipment
 connected load
 power consumption
 light distribution
 beam angle
 light color
 color rendering index (CRI) glare-free
 system of protection
 class of protection
 technology
 usage
 luminaire body
 lamp cover
 tubular sections
 balance of articulation
 joints weight (net)
 mains lead
 optional mounting
 special features

LED

without
 12-28V AC and 12-40V DC
 approx. 8.5 W
 direct, wide-angled beam
 40°
 neutral white, approx. 5000 K
 > 80
 screen
 IP 67
 III
 switchable, continuously dimmable
 push button
 aluminium, anodized, black
 glass screen
 flexible metal tube, black
 friction
 approx. 1.8 kg (4 lbs)
 approx. 3,2 m (10.5 ft); with free stranded wires
 table clamp (accessory), wall bracket (accessory)
 flood with 40° angle of radiation

illuminance

distance: 50 cm

Em: 3255 lx
 Emax: 5600 lx
 Emin: 1138 lx

