



fitted with

work equipment
connected load
power consumption
luminous flux
luminous efficacy
light colour
color rendering index (CRI)
system of protection
class of protection
technology
usage
luminaire body
weight (net)
mains supply

fastening
dimension
light output
outside diameter
side part

LED
Energy efficiency category A+
without
16-32 V; DC
approx. 30 W
approx. 2750 lm
approx. 91 lm/W
daylight white, approx. 5700 K
> 80
IP 67
III
switchable
external
polycarbonate (PC), opal white,
approx. 3.0 kg (6.6 lb)
built-in plug
QUICKON 3
lamp bracket (accessory)
A=1362 mm (53.63 in)
D=1251 mm (49.25 in)
70 mm (2.75 in)
A with plug



QUICKON 3

illuminance

distance: 100 cm
Em: 361 lx
Emax: 437 lx
Emin: 259 lx

