



Bulb change via removal of lens
(LED bulb as accessory)



Accessories

Sizes of Permanent Beacons



- Optimised illumination
- 360° visibility
- Suitable for use in the 22 mm control panel/switchgear programme
- Simple connection by means of 6.3 mm spades
- Bulb change via removal of lens

TECHNICAL SPECIFICATIONS:

Dimensions (Ø x Height):	57 mm x 69 mm (Protrusion from panel)
Housing:	PA-GF, high impact
Lens:	PC, transparent
Connection:	Spades 6.3 mm x 0.8 mm Finger-proof model according to BGV A2, when used with insulated spades
Fixing:	Installation mounting for Ø22.5 mm (M22 x 1.5 mm) with anti-twist device
Operating voltage:	Max. 48 V
Bulb socket:	BA15d, 7 Watt max.
Bulb change:	Via removal of lens
Nut and seal included in assembly. Bulb not included in assembly.	

ORDER SPECIFICATIONS:

Voltage	12-48 V
red	216 100 00
green	216 200 00
yellow	216 300 00
clear	216 400 00
blue	216 500 00

ACCESSORIES:

Bulb BA15d, total length 54 mm

Voltage	12 V (7 W)	24 V (7 W)	30 V (5 W)
	955 015 34	955 015 35	955 840 32

LED bulb BA15d, total length 42 mm

Voltage	24 V AC/DC
Current consumption	< 45 mA
red	956 100 75
green	956 200 75
yellow	956 300 75
white	956 400 75
blue	956 500 75

TECHNICAL DIAGRAMS:

see page 301

See note
on page 347

