



- Safe CAGE CLAMP® technology
- BA15d socket integrated in the base
- Optimum illumination
- Tube mounting
- Single hole mounting possible with cable gland

### TECHNICAL SPECIFICATIONS:

<b>Dimensions</b> (Ø x Height):	57 mm x 87 mm
<b>Housing:</b>	PA-GF, high impact
<b>Lens:</b>	PC, transparent
	Ring: PC
<b>Connection:</b>	CAGE CLAMP® technology max. 2.5 mm <sup>2</sup>
<b>Cable entry:</b>	Cable diameter max. 11 mm
<b>Fixing:</b>	Tube mounting M25 x 1.5 mm
<b>Operating voltage:</b>	Max. 250 V
<b>Bulb socket:</b>	BA15d, 7 Watt max.
<b>Bulb change:</b>	Via removal of lens

Bulb not included in assembly.

### ORDER SPECIFICATIONS:

Voltage	12-240 V
red	209 100 00
green	209 200 00
yellow	209 300 00
clear	209 400 00
blue	209 500 00

### ACCESSORIES:

Base with integrated tube,  
M25 x 1.5 mm **975 209 01**

Cable gland  
M25 x 1.5 mm **975 209 02**

Bulb BA15d, 5 W  
total length 42 mm

Voltage	12 V	24 V	30 V	115 V	230 V
	<b>955 840 34</b>	<b>955 840 35</b>	<b>955 840 32</b>	<b>955 840 57</b>	<b>955 840 38</b>


LED bulb BA15d  
total length 42 mm

Voltage	24 V AC/DC	115 V AC	230 V AC
Current consumption	< 45 mA	< 15 mA	< 15 mA
red	<b>956 100 75</b>	<b>956 100 67</b>	<b>956 100 68</b>
green	<b>956 200 75</b>	<b>956 200 67</b>	<b>956 200 68</b>
yellow	<b>956 300 75</b>	<b>956 300 67</b>	<b>956 300 68</b>
white	<b>956 400 75</b>	<b>956 400 67</b>	<b>956 400 68</b>
blue	<b>956 500 75</b>	<b>956 500 67</b>	<b>956 500 68</b>

### TECHNICAL DIAGRAMS:

see page 299

See note  
on page 347



Accessories

### Sizes of Permanent Beacons

