



Permanent Beacon 210 (base mounting)



Permanent Beacon 213 with integrated mounting bracket

- Safe CAGE CLAMP® technology
- BA15d socket integrated in the base
- Optimum illumination
- Available for base or bracket mounting
- Connection without the need to disassemble the product

TECHNICAL SPECIFICATIONS:

Housing:	PA-GF, high impact
Lens:	PC, transparent
Connection:	CAGE CLAMP® technology max. 2.5 mm ²
Cable entry:	Cable diameter max. 10 mm (210) Cable diameter 3-6 mm (213)

PERMANENT BEACON	210	213
Fixing:	Base mounting with flat seal	Bracket mounting incl. cable gland M12 x 1.5 mm
Dimensions (Ø x Height):	57 mm x 81 mm	57 mm x 107 mm
Operating voltage:	Max. 250 V	Max. 250 V
Bulb socket:	BA15d, 10 Watt max.	BA15d, 10 Watt max.
Bulb change:	Via removal of lens	Via removal of lens
Bulb not included in assembly.		

ORDER SPECIFICATIONS:

	Base mounting 210	Bracket mounting 213
Voltage	12-240 V	12-240 V
red	210 100 00	213 100 00
green	210 200 00	213 200 00
yellow	210 300 00	213 300 00
clear	210 400 00	213 400 00
blue	210 500 00	213 500 00

ACCESSORIES:

Bulb BA15d, 7 W total length 54 mm					
Voltage	12 V	24 V	48 V	115 V	230 V
	955 015 34	955 015 35	955 015 36	955 015 37	955 015 38

LED bulb BA15d total length 42 mm			
Voltage	24 V AC/DC	115 V AC	230 V AC
Current consumption	< 45 mA	< 15 mA	< 15 mA
red	956 100 75	956 100 67	956 100 68
green	956 200 75	956 200 67	956 200 68
yellow	956 300 75	956 300 67	956 300 68
white	956 400 75	956 400 67	956 400 68
blue	956 500 75	956 500 67	956 500 68

TECHNICAL DIAGRAMS: see page 300

Sizes of Permanent Beacons



Accessories

See note on page 347

Base mounting

Bracket mounting

