



850



851



852

- Available with grey or black housing

### TECHNICAL SPECIFICATIONS:

<b>Dimensions</b> (Ø x Height):	57 mm x 88 mm (850) 57 mm x 108 mm (851) 57 mm x 101 mm (852)
<b>Housing:</b>	ABS (85X XXX 38) PC/ABS-Blend (85X XXX 08)
<b>Lens:</b>	PC, transparent
<b>Fixing:</b>	850: Base mounting 851: Bracket mounting 852: Tube mounting M25 x 1.5 mm
<b>Socket:</b>	BA15d max. 7 Watt
<b>Connection:</b>	Screw terminal max. 1.5 mm <sup>2</sup>
<b>Cable entry:</b>	Cable diameter max. 8.5 mm (850) Cable diameter max. 7 mm (851) Cable diameter max. 10 mm (852)

Bulb not included in assembly.

### ORDER SPECIFICATIONS:

Base mounting 850		12-250 V		12-250 V	
Black housing	red	<b>850 100 08</b>	Grey housing	red	<b>850 100 38</b>
	green	<b>850 200 08</b>		green	<b>850 200 38</b>
	yellow	<b>850 300 08</b>		yellow	<b>850 300 38</b>
	clear	<b>850 400 08</b>		clear	<b>850 400 38</b>
Bracket mounting 851		12-250 V		12-250 V	
Black housing	red	<b>851 100 08</b>	Grey housing	red	<b>851 100 38</b>
	green	<b>851 200 08</b>		green	<b>851 200 38</b>
	yellow	<b>851 300 08</b>		yellow	<b>851 300 38</b>
	clear	<b>851 400 08</b>		clear	<b>851 400 38</b>
Tube mounting 852		12-250 V		12-250 V	
Black housing	red	<b>852 100 08</b>	Grey housing	red	<b>852 100 38</b>
	yellow	<b>852 300 08</b>		yellow	<b>852 300 38</b>

Further colours and voltages on request.

### ADDITIONAL INFORMATION:

Please also see the beacon series 209, 210, 213, 219 with additional advantages (see page 148 onwards)

- High protection rating IP 65
- BA15d socket integrated in the base
- Safe CAGE CLAMP® connection
- Optimum illumination
- Connection without product disassembly



### ACCESSORIES: see next page

See note on page 347

