

220/223

Permanent Beacon



Permanent Beacon 220
(base mounting)



Permanent Beacon 223 with
integrated mounting bracket



Housing with
CAGE CLAMP® connection

Sizes of Permanent Beacons



- Safe CAGE CLAMP® technology
- BA15d socket integrated in the base
- Optimum illumination
- Available for base or bracket mounting
- Connection without the need to disassemble the product



TECHNICAL SPECIFICATIONS:

Housing:	PA-GF, high impact
Lens:	PC, transparent; Ring: PC/ABS-Blend
Connection:	CAGE CLAMP® technology max. 2.5 mm ²
Cable entry:	Cable diameter max. 10 mm (220) Cable diameter 3-6 mm (223)

PERMANENT BEACON	220	223
Fixing:	Base mounting with flat seal	Bracket mounting incl. cable gland M12 x 1.5 mm
Dimensions (Ø x Height):	75 mm x 79 mm	75 mm x 105 mm
Operating voltage:	Max. 250 V	Max. 250 V
Bulb socket:	BA15d, 10 Watt max.	BA15d, 10 Watt max.
Bulb change:	Via removal of lens	Via removal of lens
Bulb not included in assembly.		



ORDER SPECIFICATIONS:

	Base mounting 220	Bracket mounting 223
Voltage	12-240 V	12-240 V
red	220 100 00	223 100 00
green	220 200 00	223 200 00
yellow	220 300 00	223 300 00
clear	220 400 00	223 400 00
blue	220 500 00	223 500 00

Further colours and voltages on request.



ACCESSORIES:

Bulb BA15d, 7 W
total length 54 mm

Voltage	12 V	24 V	48 V	115 V	230 V
	955 015 34	955 015 35	955 015 36	955 015 37	955 015 38

LED bulb BA15d
total length 42 mm

Voltage	24 V AC/DC	115 V AC	230 V AC
Current consumption	< 45 mA	< 15 mA	< 15 mA
red	956 100 75	956 100 67	956 100 68
green	956 200 75	956 200 67	956 200 68
yellow	956 300 75	956 300 67	956 300 68
white	956 400 75	956 400 67	956 400 68
blue	956 500 75	956 500 67	956 500 68



TECHNICAL DIAGRAMs: see page 301

See note
on page 347

Base
mounting

Bracket
mounting

