



Base/Bracket mounting



Tube mounting



Accessories

- Multi-functional LED beacon
- Interchangeable light effects
- Shock-proof and vibration resistant
- Tube mounting solution suitable for Ø 25 mm and 1/2" NPT tubes

i TECHNICAL SPECIFICATIONS:

Dimensions (Ø x Height):	98 mm x 137 mm (Base/Bracket mounting) 98 mm x 200 mm (Tube mounting)
Cable entry:	Cable diameter 5-7 mm
Housing:	PC/ABS-Blend
Lens:	PC, transparent
Connection:	Screw terminal with wire protection 0.5 mm ² - 2.5 mm ²

Life duration up to 50,000 hrs

LED PERMANENT/BLINKING BEACON (INTERCHANGEABLE LIGHT EFFECT)

Blink frequency:	C. 1.5 Hz
Operating voltage:	24 V DC

LED PERMANENT BEACON

Operating voltage:	115 V AC	230 V AC
---------------------------	----------	----------

ORDER SPECIFICATIONS:

LED PERMANENT/BLINKING	Base/Bracket mounting	Tube mounting
Voltage	24 V DC	24 V DC
Current consumption	≤ 150 mA	≤ 150 mA
red	829 100 55	829 107 55
green	829 200 55	829 207 55
yellow	829 300 55	829 307 55
blue	829 500 55	829 507 55

LED PERMANENT	Base/Bracket mounting		Tube mounting	
Voltage	115 V AC	230 V AC	115 V AC	230 V AC
Current consumption	≤ 30 mA	≤ 30 mA	≤ 30 mA	≤ 30 mA
red	829 130 67	829 130 68	829 137 67	829 137 68
green	829 230 67	829 230 68	829 237 67	829 237 68
yellow	829 330 67	829 330 68	829 337 67	829 337 68
blue	829 530 67	829 530 68	829 537 67	829 537 68

ACCESSORIES:

Plastic bracket for wall mounting	975 826 05
Wire guard, galvanised, only for base mounting	975 826 03
Tube Ø 25 mm, all anodized aluminium, 100 mm long	975 845 10
Base for tube, plastic	975 840 90
Base for tube, metal	975 840 91

TECHNICAL DIAGRAMS:

see page 317

Sizes of Permanent Beacons



Base/Bracket mounting See note on page 347 Base/Bracket mounting Tube mounting

