



- Large signal beacon for powerful signal effect
- With a multitude of symbols
- High light intensity thanks to optimised lens



TECHNICAL SPECIFICATIONS:

Dimensions (Ø x Height):	150 mm x 148 mm
Housing:	PC/ABS-Blend, grey
Lens:	PC, transparent
Socket:	E27 max. 25 W 2 sockets E14 each with max. 15 W with adhesive stickers E27 max. 15 W
Fixing:	Base mounting, tube mounting and fixing bracket (accessory)
Cable entry:	From top or bottom with cable gland M20 x 1.5 mm or from the back with rubber grommet Ø 6-12 mm
Connection:	Screw-free clamp mechanism max. 1.5 mm ²



ORDER SPECIFICATIONS:

Voltage	12-240 V AC/DC
red	895 100 00
green	895 200 00
yellow	895 300 00
clear	895 400 00
blue	895 500 00
Bulb not included in assembly.	

PERMANENT LIGHT WITH TWO SOCKETS (incl. reflector)

Voltage	12-240 V AC/DC
red	895 110 00



ACCESSORIES:

Fixing bracket, additional reflector, Bulbs and LED Bulbs, Adhesive Stickers see Permanent/Traffic Light Beacon (page 176).



TECHNICAL DIAGRAMS:

see page 326



Audible addition:
The Multi-Tone Sounder 190 with 110 dB (see page 253)

See note on page 347

