



Base/Bracket Mounting



Tube mounting



Accessories

- Tube mounting solution suitable for Ø 25 mm and 1/2" NPT tubes
- Simple mounting
- Removal of the lens only possible with tools

TECHNICAL SPECIFICATIONS:

Dimensions (Ø x Height):	98 mm x 137 mm (Base/Bracket mounting) 98 mm x 200 mm (Tube mounting)		
Cable entry:	Cable diameter 5-7 mm		
Housing:	PC/ABS-Blend		
Lens:	PC, transparent		
Connection:	Screw terminal with wire protection max. 2,5 mm ²		
Bulb:	Max. 25 W		
Blinking frequency:	1.5 Hz		
Starting current:	24 V AC/DC	115 V AC	230 V AC
	3 A	0,6 A	0,35 A
Socket:	BA15d		
Bulb included in assembly.			

ORDER SPECIFICATIONS:

Base/Bracket mounting			
Voltage	24 V AC/DC	115 V AC/DC	230 V AC/DC
red	827 100 75	827 100 77	827 100 78
yellow	827 300 75	827 300 77	827 300 78
Tube mounting			
Voltage	24 V AC/DC	115 V AC/DC	230 V AC/DC
red	827 110 75	827 110 77	827 110 78
yellow	827 310 75	827 310 77	827 310 78

ACCESSORIES:

Plastic bracket for wall mounting	975 826 05
Wire guard, galvanised, only for base mounting	975 826 03
Tube Ø 25 mm, all anodized aluminium, 100 mm long	975 845 10
Base for tube, plastic	975 840 90
Base for tube, metal	975 840 91
Bulb BA15d, 25 W, total length max. 55 mm	
Voltage	24 V AC/DC 115 V AC/DC 230 V AC/DC
	955 827 35 955 827 37 955 827 38

TECHNICAL DIAGRAMS:

see page 316

Sizes of Flashing Beacons



See note on page 347

Base/Bracket mounting Tube mounting

