

Patent approved



Base mounting



Bracket mounting (accessory)

- Attention-grabbing flickering light
- Developed on a neurobiological basis
- Extremely powerful signal effect
- Random sequence of light signals prevents acclimatisation effect

i TECHNICAL SPECIFICATIONS:

Life duration up to 50,000 hrs

Dimensions (Ø x Height):	142 mm x 218 mm	
Housing:	PC/ABS-Blend	
Lens:	PC, transparent	
Fixing:	Base mounting, bracket mounting (accessory), tube mounting (accessory)	
Connection:	Screw terminal with wire protection max. 2.5 mm ²	
Cable entry:	Cable diameter 5-7 mm	
Duty cycle:	100 %	

ORDER SPECIFICATIONS:

Voltage	24 V DC	115-230 V AC
Current consumption	< 500 mA	< 350 mA
red	280 160 55	280 160 60
yellow	280 360 55	280 360 60
clear	280 460 55	280 460 60

ACCESSORIES:

Plastic bracket for wall mounting	975 883 06
Adaptor for tube mounting	975 883 09
Wire guard, only for base mounting	975 883 08

(Accessories see page 163)

ADDITIONAL INFORMATION:

* EVS = Enhanced Visibility System

Further Information can be found in the chapter "General Information" beginning on page 352.

Please note the photosensitive epilepsy warning on page 352.

TECHNICAL DIAGRAMS:

see page 303

Sizes of Flashing Beacons



See note on page 347

