



LED Permanent Light in combination with Multi-Tone Sounder



Quick and simple wall mounting without additional accessories thanks to integrated mounting bracket



Mounting holes integrated into the product rim allow easy mounting without having to remove the lens



- 32 tones can be set to meet the requirements of the application, one tone can be triggered externally
- Adjustable sound output
- Optical and audible warning can be separately triggered for two stage signalling
- Integrated bracket for simple wall mounting without additional accessories (432)

Life duration
up to 50,000 hrs (LED)
+ 5,000 hrs (Horn)

TECHNICAL SPECIFICATIONS:

Dimensions (Ø x Height):	146 mm x 171 mm (Base mounting) 134 mm x 235 mm (Wall mounting)
Housing:	Base mounting: PC, black Wall mounting: PC/ABS-Blend, grey
Lens:	PC, transparent
Connection:	Screw terminal with wire protection, max. 1.5 mm ²
Cable entry:	Cable diameter max. 11 mm
Fixing:	Base mounting (430), Wall mounting (432) Tube mounting (accessory, only for 430)
Installation position:	Sound outlet facing downwards
Tone type and frequency:	32 tones adjustable, see table on page 203.

ORDER SPECIFICATIONS:

Base mounting 430	24 V AC/DC	10-48 V AC/DC*	115-230 V AC*
Voltage	24 V AC/DC	10-48 V AC/DC*	115-230 V AC*
Current consumption MTS	190 mA	340 mA	55 mA
Current consumption LED	350 mA	700 mA	100 mA
	230 mA (red)	550 mA (red)	80 mA (red)
red	430 100 75	430 100 70	430 100 60
green	430 200 75	430 200 70	430 200 60
yellow	430 300 75	430 300 70	430 300 60
clear	430 400 75	430 400 70	430 400 60
blue	430 500 75	430 500 70	430 500 60
Wall mounting 432	24 V AC/DC	10-48 V AC/DC*	115-230 V AC*
Voltage	24 V AC/DC	10-48 V AC/DC*	115-230 V AC*
Current consumption MTS	190 mA	340 mA	55 mA
Current consumption LED	350 mA	700 mA	100 mA
	220 mA (red)	550 mA (red)	80 mA (red)
red	432 100 75	432 100 70	432 100 60
green	432 200 75	432 200 70	432 200 60
yellow	432 300 75	432 300 70	432 300 60
clear	432 400 75	432 400 70	432 400 60
blue	432 500 75	432 500 70	432 500 60

*Current consumption at 10 V / 115 V

ACCESSORIES:

Adaptor for tube mounting, plastic, for tube Ø 25 mm **975 430 01**

TECHNICAL DIAGRAMS:

see page 304

