



Award winning design Winner of the IF product design award 2012

- Maintenance-free, electronic horn with a long life duration of up to 5,000 hrs
- Sound output can be set to meet the requirements of the application
- Optical and audible warning can be separately triggered for two stage signalling
- Integrated bracket for simple wall mounting without additional accessories

Life duration up to 50,000 hrs (LED)

i TECHNICAL SPECIFICATIONS:

Dimensions (L x H x W):	134 mm x 407 mm x 144 mm
Housing:	PC/ABS-Blend, grey
Lens:	PC, transparent
Connection:	Screw terminal with wire protection, max. 1.5 mm ²
Cable entry:	Cable diameter max. 11 mm
Fixing:	Wall mounting, integrated mounting bracket
Installation position:	Sound outlet facing downwards
Tone frequency:	C. 110 Hz
Life duration:	Up to 50,000 h (LED), up to 5,000 h (Horn)

ORDER SPECIFICATIONS:

Voltage	24 V AC/DC	10-48 V AC/DC*	115-230 V AC*
Current consumption MTS	55 mA	210 mA	30 mA
Current consumption LED	350 mA	700 mA	100 mA
	230 mA (red)	550 mA (red)	80 mA (red)
red	434 100 75	434 100 70	434 100 60
green	434 200 75	434 200 70	434 200 60
yellow	434 300 75	434 300 70	434 300 60
clear	434 400 75	434 400 70	434 400 60
blue	434 500 75	434 500 70	434 500 60

*Current consumption at 10 V / 115 V

TECHNICAL DIAGRAMS:

see page 305



Quick and simple wall mounting without additional accessories thanks to integrated mounting bracket



Loud, long-life combination for a diverse range of applications

Size comparison

