



Surface housing double

- Various combinations possible
- High protection rating IP 65
- Versatile range of applications thanks to cable exit at side

i TECHNICAL SPECIFICATIONS:

Dimensions (W x H x D):	single:	80.5 mm x 55 mm x 82 mm
	double:	160 mm x 55 mm x 78 mm
	triple:	240 mm x 60 mm x 80 mm
Housing:	ABS and PC/ABS-Blend	
Cable entry:	Cable gland M16 x 1.5 mm for circular cable Ø 5-10 mm	

ORDER SPECIFICATIONS:



Single surface housing	975 109 02
Double surface housing for 1 beacon and 1 buzzer	975 109 03
Triple surface housing for 2 beacons and 1 buzzer	975 109 04

Assembly comprises of only the surface housing. Beacons 800-802, 815-817 (p. 107/109) and buzzers 109 and 110 (pages 229/237) have to be ordered additionally.



Single surface housing

TECHNICAL DIAGRAMS:

see page 330

single double triple

CE

