

- For the 22.5 mm control panel programme
- Low current consumption
- High protection rating IP 65



**i TECHNICAL SPECIFICATIONS:**

Dimensions (Ø x Height):	28 mm x 12 mm (Protrusion from panel)
Housing:	PA fibreglass, high-impact
Tone frequency:	C. 2,400 Hz / c. 3,200 Hz (12 V)
Tone type:	Continuous tone or pulse tone with approx. 1 Hz
Fixing:	Installation mounting for Ø 22.5 mm (M22)
Connection:	Connector plug with screw terminal max. 1.5 mm <sup>2</sup>
Life duration:	> 5,000 hrs

**ORDER SPECIFICATIONS:**

Voltage	12 V DC	24 V AC/DC	115 V AC/DC	230 V AC
Current Consumpt.	≤ 10 mA	≤ 8 mA	≤ 8 mA	≤ 8 mA
Continuous tone	<b>107 000 54</b>	<b>107 000 75</b>	<b>107 000 77</b>	<b>107 000 68</b>
Pulse tone	<b>107 010 54</b>	<b>107 010 75</b>	<b>107 010 77</b>	<b>107 010 68</b>

(12 V = / **107 000 54** and **107 010 54** without UL approval)



**TECHNICAL DIAGRAMS:**

see page 294



Simple connection by means of connector plug



High protection rating IP 65 for use in rough conditions



See note on page 347

