

860

AndonCONTROL for KombiSIGN 70 and 71



AndonCONTROL is a simple call system for a wide variety of applications



Instant status activated by push button



The four push buttons can be individually labelled

- Instant status display at the touch of a button to aid process optimisation
- Smart electronics enable the activation of up to eight different states
- For use with an integral signal tower
- Universal power supply and interchangeable adaptors enable worldwide use

i TECHNICAL SPECIFICATIONS:

Dimensions (Ø x Height):	KombiSIGN 70: 136 mm x 49.5 mm KombiSIGN 71: 136 mm x 45.5 mm
Housing:	Base: PC/ABS Terminal element: PA-GF, shock resistant
Fixing:	Base mounting, Bracket mounting (accessory)
Number of signal elements:	Max. 4 additional signal elements possible
Assembly:	AndonCONTROL, power supply unit with connection cable (length 1.8 m), interchangeable adaptors for EU, UK, North America, rubber feet, cable connection

🛒 ORDER SPECIFICATIONS:

Voltage power supply unit	100-240 V AC
Voltage signal elements	24 V DC
Current consumption	Max. 1 A
AndonCONTROL for KombiSIGN 70	860 840 07
AndonCONTROL for KombiSIGN 71	860 640 07

🏠 ACCESSORIES:

Mounting bracket, metal	975 883 01
-------------------------	-------------------

⚠️ ADDITIONAL INFORMATION:

The smart electronics in AndonCONTROL can activate up to eight different status conditions (permanent or blinking light). A signal tower mounted directly on the AndonCONTROL product can signal the different states.

Suitable for all KombiSIGN 70 and 71 signal towers.

Further information and order details for KombiSIGN 70 and 71 can be found in the chapter "modular signal towers" on page 29.

📐 TECHNICAL DIAGRAMS:

see page 324

See note on page 347

