



- Suitable for maritime applications
- Corrosion-proof aluminium housing

i TECHNICAL SPECIFICATIONS:

Dimensions (L x H x W):	132 mm x 340 mm x 139 mm		
Housing:	Aluminium alloy, corrosion-proof		
Connection:	Screw terminal max. 2.5 mm ²		
Cable entry:	Cable gland M20 x 1.5 mm Cable diameter 10-12 mm		
Fixing:	Wall mounting, sound outlet facing downwards		

🛒 ORDER SPECIFICATIONS:

Voltage	24 V DC	115 V AC (50 Hz/60 Hz)	230 V AC
Current consumption	350 mA	200 mA	70 mA
	571 052 55	571 052 67	571 052 68



📏 TECHNICAL DIAGRAMS: see page 307

See note
on page 347



- High Protection rating IP 65

i TECHNICAL SPECIFICATIONS:

Dimensions (L x H x W):	156 mm x 118 mm x 223 mm		
Housing:	Aluminium, grey varnish Cap: ABS		
Connection:	Screw terminal max. 2.5 mm ²		
Cable entry:	Cable gland at side, M20 x 1.5 mm Cable diameter 10-12 mm		
Fixing:	Wall mounting, sound outlet facing downwards		

🛒 ORDER SPECIFICATIONS:

Voltage	24 V DC	115 V AC (50 Hz/60 Hz)	230 V AC
Current consumption	350 mA	200 mA	70 mA
	572 000 55	572 000 67	572 000 68

Further voltages on request.



📏 TECHNICAL DIAGRAMS: see page 307

See note
on page 347

