



- Modern design
- Cable gland for strain relief
- Concealed fixing screws
- High protection rating IP 65

i TECHNICAL SPECIFICATIONS:

Dimensions (L x H x W):	178 mm x 104 mm x 207 mm
Fixing dimensions (L x H):	130 mm x 160 mm
Housing:	PC/ABS-Blend
Connection:	Screw terminal max. 2.5 mm ²
Cable entry:	Cable gland M16 x 1.5 mm Cable diameter 5-10 mm
Fixing:	Wall mounting, sound outlet facing downwards

ORDER SPECIFICATIONS:

Voltage	24 V DC	24 V AC	42-48 V AC	115 AC	230 V AC
		(50 Hz)	(50/60 Hz)	(50/60 Hz)	(50 Hz)
Current consumpt.	350 mA	500 mA	250 mA	200 mA	70 mA
	573 000 55	573 000 65	573 000 66	573 000 67	573 000 68



TECHNICAL DIAGRAMS:

see page 307



The Horn 573 is also available in an Ex version (see page 291)

See note on page 347

