



- Small horn with trumpet

TECHNICAL SPECIFICATIONS:

Dimensions (L x H x W):	70 mm x 172 mm x 77 mm
Housing:	ABS
Connection:	Screw terminal with wire protection, 1.0-1.5 mm ² fine strand, 1.0-2.5 mm ² single wire
Cable entry:	Cable diameter 9 mm
Fixing:	Wall mounting, sound outlet facing downwards

ORDER SPECIFICATIONS:

AC Version

Voltage	12 V AC	24 V AC	42 V AC	115 V AC	230 V AC
Current consumpt.	330 mA	190 mA	75 mA	15 mA	15 mA
	582 052 64	582 052 65	582 052 66	582 052 67	582 052 68

DC Version

Voltage	12 V DC	24 V DC
Current consumpt.	150 mA	70 mA
	582 052 54	582 052 55

Further voltages on request.

ADDITIONAL INFORMATION:

Please also see Horn 584 with additional advantages (see page 264)

- High protection rating IP 65
- Loud electronic horn
- High life duration up to 5,000 hrs
- Sound output 98 dB



TECHNICAL DIAGRAMS:

see page 308

