



- Loud electronic horn
- High life duration up to 5,000 hrs
- Integrated mounting bracket
- High protection rating IP 65

**TECHNICAL SPECIFICATIONS:**

Dimensions (L x H x W):	83 mm x 198 mm x 91.5 mm
Housing:	PC, PC/ABS-Blend, grey
Fixing:	Wall mounting
Installation position:	Sound outlet facing downwards
Connection:	Screw terminal with wire protection max. 1.5 mm ²
Cable entry:	Cable diameter max. 9 mm
Tone frequency:	C. 110 Hz
Life duration:	> 5,000 hrs
Duty cycle:	100 %

**ORDER SPECIFICATIONS:**

Voltage	24 V AC/DC	115 V AC	230 V AC
Current consumption	≤ 80 mA	≤ 70 mA	≤ 70 mA
	584 000 75	584 000 67	584 000 68

**TECHNICAL DIAGRAMS:**


see page 308



Horn in combination with Xenon Flash or LED Permanent Light see page 196 and 197



See note
on page 347



24 V

